

Complete Tech Tools Program



Professional Tech Tools



Wiha Precision Screwdrivers

Description	Page
 Precision Slotted Drivers	4-5
Precision Phillips Drivers	5
Precision Pozidriv® Drivers	6
Precision Hex Drivers	6
Precision Ball End Drivers	7
Precision Nut Drivers	8
Precision Torx® Drivers	9
 Precision Chip Lifters	9

Wiha Magnetizer/Demagnetizer

Description	Page
 Torque Cable Keys	7

Wiha Precision Screwdriver Accessories

Description	Page
 Precision Master Tech Set	9
 Precision Pocket Clip	9
 Precision Stand	9
 Precision Pouch	8,13

Wiha Precision PicoFinish Drivers

Description	Page
 PicoFinish Screwdrivers	10-13
Slotted, Phillips, Torx, TorxPlus, Hex, MagicSpring, Ball End Hex, Chip Lifter & Nut Drivers	

Wiha Magnetizer/Demagnetizer

Description	Page
 Magnetizer/Demagnetizer	13

Wiha Precision Protturn Drivers

Description	Page
 Protturn Drivers & Blade Sets	14
Slotted, Phillips, Torx, Chip Lifter	

Wiha ESD Safe Precision Handles/Blades

Description	Page
 SYSTEM 4 Handles/Blades	15-16
SYSTEM 4 Sets	17-19

Wiha ESD Safe Precision Handle & Blades

Description	Page
 SYSTEM 4 Drive-Loc Handle & Blades	17
 SYSTEM 4 Drive-Loc Set	17




ESD Safe Micro Bit Handles, Bits & Sets

DESCRIPTION	Page
 Micro Bits Handles/Bits/Sets	20-22
 ESD Safe Micro Bit Sets	23
 Micro Bit Storage Handle Sets	23

Precision Electronic Pliers/Cutters

Description	Page
 Electronic Diagonal Cutters Wide Pointed Head	24
 Electronic Diagonal Cutters Wide Shape w/Wire Holding Spring	24
 Electronic Diagonal Cutters Narrow Shape	24
 Electronic Diagonal Cutters Full Flush Cutters w/Wire Trapping Spring	25
 Electronic Diagonal Cutters 48° Front Cutter/Long Nose Pliers	25
 Electronic Diagonal Cutters Oblique 30° Cutting Nippers	25
 Electronic Diagonal Cutters Short Nose Precision Pliers	25
 Electronic Stripping Pliers	25

Wiha Professional Tweezers

Description	Page
 ESD Safe Tweezers	26-28
 Standard Tweezers	29-31
 SMD Tweezers	31
 Long Tweezers w/Long Tips	31
 Super Thin Tweezers	31
 Wafer Tweezers	32
 Cutting Tweezers	32
 Guide Pin Tweezers	33
 Self Closing Tweezers	34
 Microscopy Tweezers	35
 Isolated Tweezers	35
 Inspection Mirrors	36
 All Stainless Hooks	36
 All Stainless Excavators	37
 All Stainless Probes	37

Wiha Stripping Tools

Description	Page
 Self Adj. Cut & Strip Tools	38
 Adjustable Cable Stripper	39
 Adjustable Stripping Tool	39
 CATV/Satellite Stripper	39
 2 Step Stripping Tools	40
 3 Step Stripping Tools	41

Wiha ESD Safe Tech Tools

ESD Safe Precision Drivers
Slotted/Phillips/Torx®/
TorxPlus®/Hex/Nut Drivers/
Chip Lifter

ESD Safe Ceramic Drivers

ESD Safe SYSTEM 4
Handles/Blades/Sets

ESD Safe Drive-Loc
Handles/Blades/Sets

ESD Safe Pliers & Cutters



Catalog 99945.wo

Rotating cap

for precise
turning and control
with fingertip

Precision handle

high quality
plastic,
cadmium free

**Molded on
tapered handle**

allows rapid
rotation

**High performance
blades**

chrome-vanadium-
molybdenum steel,
Hard chrome finished

Tip

precision ground for
exact fit, hard chromed
non-slip surface

Wiha Long Life Precision Series

**260 Slotted Screwdriver, With Precision Handle**

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26008	.80	1/32	40	1.6	0.16	.01	120	4.7	.02	10
26010	1.0	.039	40	1.6	0.18	.01	120	4.7	.02	10
26012	1.2	3/64	40	1.6	0.20	.01	120	4.7	.02	10
26015	1.5	1/16	40	1.6	0.25	.01	120	4.7	.02	10
26018	1.8	.070	40	1.6	0.30	.01	120	4.7	.02	10
26020	2.0	5/64	40	1.6	0.40	.02	120	4.7	.02	10
26022	2.0	5/64	50	2.0	0.40	.02	145	5.7	.02	10
26023	2.0	5/64	100	3.9	0.40	.02	180	7.1	.03	10
26025	2.5	3/32	50	2.0	0.40	.02	145	5.7	.03	10
26027	2.5	3/32	100	3.9	0.40	.02	195	7.7	.03	10
26028	2.5	3/32	150	6.0	0.40	.02	245	9.6	.04	10
26030	3.0	1/8	50	2.0	0.50	.02	145	5.7	.03	10
26032	3.0	1/8	60	2.4	0.50	.02	170	6.7	.04	10
26033	3.0	1/8	100	3.9	0.50	.02	210	8.3	.04	10
26034	3.0	1/8	150	5.9	0.50	.02	260	10.2	.05	10
26035	3.5	9/64	60	2.4	0.60	.02	170	6.7	.05	10
26040	4.0	5/32	60	2.4	0.80	.03	170	6.7	.05	10
26041	4.0	5/32	100	3.9	0.80	.03	210	8.3	.06	10
26042	4.0	5/32	150	5.9	0.80	.03	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate

**26090 6 Piece Precision Slotted Set**

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.		lbs.
26090	Slotted:	
	1.5, 2.0 x 40mm	.27
	2.5, 3.0 x 50mm	
	3.5, 4.0 x 60mm	

**26099 8 Piece Precision Slotted Set**

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		lbs.
26099	Slotted: 1.0, 1.2, 1.5, 2.0 x 40mm	
	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54

Wiha Precision Slotted/Phillips Drivers



261 Phillips Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26102	000	40	1.6	2.0	.08	120	4.7	.02	10
26100	00	40	1.6	2.0	.08	120	4.7	.02	10
26101	00	75	3.0	2.0	.08	155	6.1	.02	10
26105	0	50	2.0	3.0	.12	145	5.7	.02	10
26108	0	75	3.0	3.0	.12	170	6.7	.03	10
26107	0	100	3.9	3.0	.12	195	7.6	.05	10
26109	0	150	5.9	3.0	.12	245	9.6	.06	10
26110	1	60	2.4	4.0	.16	170	6.7	.05	10
26113	1	80	3.1	4.0	.16	190	7.5	.05	10
26114	1	100	3.9	4.0	.16	210	8.2	.06	10
26115	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



26092 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26092	Slotted:	
	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
	Phillips:	
	0 x 75mm	



26190 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26190	Slotted:	
	1.5 x 40mm	.31
	2.0, 2.5 x 50mm	
	3.0 x 60mm	
	Phillips:	
	00 x 40mm	
	0 x 50mm, 1 x 60mm	



26194 4 Piece Precision Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished.

Item No.		lbs.
26194	Phillips: 000, 00 x 40mm	
	0 x 50mm, 1 x 60mm	.18



In canvas storage pouch

26199 8 Piece Precision Slotted/Phillips Set

Blade high alloy CVM steel, hard chrome finished.

Item No.		lbs.
26199	Slotted: 1.0, 2.0 x 40mm,	
	3.0 x 50mm, 4.0 x 60mm	.55
	Phillips: 000, 00 x 40mm,	
	0 x 50mm, 1 x 60mm	



26192 5 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26192	Slotted:	
	2.5, 3.0, 4.0 x 150mm	.44
	Phillips:	
	0, 1 x 150mm	

Wiha Pozidriv® Precision Series



262 Pozidriv® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26205	0	50	2.0	3.0	.12	145	5.7	.03	10
26210	1	60	2.4	4.0	.16	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Metric Precision Series



263 Metric Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
26307	.71	.028	40	1.6	120	4.7	.02	10	
26309	.89	.035	40	1.6	120	4.7	.02	10	
26313	1.27	.050	40	1.6	120	4.7	.02	10	
26315	1.5	-	50	2.0	145	5.7	.03	10	
26320	2.0	5/64	50	2.0	145	5.7	.03	10	
26325	2.5	-	60	2.4	170	6.7	.04	10	
26330	3.0	-	60	2.4	170	6.7	.04	10	
26340	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26390 7 Pc. Precision Hex Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26390	Hex Metric:	lbs.
	.71, .89, 1.27 x 40mm	.28
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	

Wiha Hex Inch Precision Series



263 Inch Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.	
26307	.028	.71	40	1.6	120	4.7	.02	10	
26309	.035	.89	40	1.6	120	4.7	.02	10	
26313	.050	1.27	40	1.6	120	4.7	.02	10	
26316	1/16	-	50	2.0	145	5.7	.03	10	
26320	5/64	2.0	50	2.0	145	5.7	.03	10	
26323	3/32	-	60	2.4	170	6.7	.04	10	
26327	7/64	-	60	2.4	170	6.7	.04	10	
26331	1/8	-	60	2.4	170	6.7	.04	10	
26333	9/64		60	2.4	170	6.7	.05	10	
26336	5/32		60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26391 8 Pc. Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26391	Hex Inch:	lbs.
	.028, .035, .050 x 1.6"	.32
	1/16, 5/64 x 2.0"	
	3/32, 7/64, 1/8 x 2.4"	




26399 8 Piece Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.
Hard chrome finished. In canvas storage pouch

Item No.		
26399	Hex Inch: .028, .035, .050 x 1.6"	lbs.
	1/16, 5/64 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.55

Wiha Ball End Precision Series



264 Inch Ball End Hex Inch Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	.050	40	1.6	120	4.7	.02	10
26416	1/16	50	2.0	145	5.7	.03	10
26419	5/64	50	2.0	145	5.7	.03	10
26423	3/32	50	2.0	145	5.7	.03	10
26427	7/64	60	2.4	170	6.7	.03	10
26431	1/8	60	2.4	170	6.7	.05	10
26436	9/64	60	2.4	170	6.7	.05	10
26439	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



264 Metric Ball End Hex Metric Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy CVM steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	1.27	.050	40	1.6	120	4.7	.02	10
26415	1.5	-	50	2.0	145	5.7	.03	10
26420	2.0	-	50	2.0	145	5.7	.03	10
26425	2.5	-	60	2.4	170	6.7	.04	10
26430	3.0	-	60	2.4	170	6.7	.05	10
26440	4.0	-	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26491 5 Piece Ball End Hex Driver Set - Metric

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum-steel.

Item No.	Ball End Hex Metric:	lbs.
26491	1.27 x 40mm	.25
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	



26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Hex Inch:	lbs.
26490	.050 x 1.6"	.28
	1/16, 5/64, 3/32 x 2.0"	
	7/64, 1/8, 9/64, 5/32 x 2.4"	



26499 8 Piece Ball End Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item No.	Ball End Hex Inch:	lbs.
26499	.050 x 1.6", 1/16, 5/64, 3/32 x 2.0"	.62
	7/64, 1/8, 9/64, 5/32 x 2.4"	

Wiha Torque Cable Keys



286 Torque Cable Key For Threaded Hex Connectors

For torque controlled fastening of cable plug connectors with Hex heads. Used with Wiha-TorqueControl Screwdrivers.

Item No.	Size	mm	mm	mm	Max Nm	pkg.	lbs.
28620	8mm	4.0	78	218	1.0	1	.06
28622	9mm	4.0	78	218	1.0	1	.06
28624	11mm	4.0	78	218	1.5	1	.06
28626	12mm	4.0	78	218	1.5	1	.06
28627	13mm	4.0	78	218	1.5	1	.06
28629	14mm	4.0	78	218	1.5	1	.06
28632	17mm	4.0	78	218	1.5	1	.06
28633	18mm	4.0	78	218	1.5	1	.06
28637	22mm	4.0	90	233	2.0	1	.10
28638	24mm	4.0	90	233	2.0	1	.10

28644 Torque Cable Key For Threaded Hex Connectors - Inch

Item No.	Size	mm	mm	mm	Max Nm	pkg.	lbs.
28644	1/2"	4.0	78	218	1.5	1	.06

Wiha Nut Driver Precision Series



26510 Metric Nut Driver With Precision Handle

Metric sizes. Blade CVM steel. Hard chrome finished.

Item No.	mm	mm	Inch	mm	Inch	mm	mm	lbs.	pkg.
26510	1.5	60	2.4	140	5.5	2.5	3.0	.03	10
26515	1.8	60	2.4	140	5.5	2.9	3.5	.03	10
26520	2.0	60	2.4	140	5.5	3.2	4.0	.04	10
26525	2.5	60	2.4	155	6.1	4.0	4.0	.04	10
26530	3.0	60	2.4	155	6.1	5.0	5.0	.05	10
26532	3.2	60	2.4	155	6.1	5.0	5.0	.05	10
26535	3.5	60	2.4	155	6.1	5.3	6.0	.05	10
26540	4.0	60	2.4	155	6.1	5.5	6.0	.05	10
26545	4.5	60	2.4	155	6.1	6.2	7.0	.05	10
26550	5.0	60	2.4	155	6.1	6.8	7.0	.05	10
26555	5.5	60	2.4	170	6.7	7.6	8.0	.06	10
26560	6.0	60	2.4	170	6.7	8.2	9.0	.06	10
26570	7.0	60	2.4	170	6.7	9.6	10.0	.06	10

*Metric dimensions actual - Inch dimensions approximate



26510 Inch Nut Driver With Precision Handle

Inch sizes. Blade CVM steel. Hard chrome finished.

Item No.	Inch	mm	Inch	mm	Inch	Inch	Inch	lbs.	pkg.
26523	3/32	60	2.4	155	6.1	.16	.16	.04	10
26527	7/64	60	2.4	155	6.1	.20	.20	.05	10
26531	1/8	60	2.4	155	6.1	.20	.20	.05	10
26536	9/64	60	2.4	155	6.1	.21	.24	.05	10
26539	5/32	60	2.4	155	6.1	.22	.24	.05	10
26547	3/16	60	2.4	155	6.1	.25	.28	.05	10
26556	7/32	60	2.4	170	6.7	.30	.32	.06	10
26563	1/4	60	2.4	170	6.7	.34	.36	.06	10

*Metric dimensions actual - Inch dimensions approximate



26591 8 Pc. Precision Nut Driver Set - Inch

Blade CVM steel.

Item No.	Inch Nut Drivers:	lbs.
26591	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	47



26592 Set 7 Pcs. Nut Driver Metric

Item No.	26592	1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
----------	-------	-------------------------------------

26590 8 Pc. Precision Nut Driver Set - Metric

Blade CVM steel.

Item No.	Metric Nut Drivers:	lbs.
26590	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0 x 60mm	.48



26599 8 Pc. Precision Nut Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.	Inch Nut Drivers:	lbs.
26599	3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72



26598 8 Pc. Precision Nut Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.	Metric Nut Drivers:	lbs.
26598	2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0 x 60mm	.70

Wiha Precision Chip Lifter



26810 Precision Chip Lifter

Blade chrome-vanadium-molybdenum steel, hardened, chrome-plated.

Precision handle high quality plastic, impact resistant. Standard handle

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26810	1	3.5	50	145	5.7	.07	1

*Metric dimensions actual - Inch dimensions approximate

Wiha TORX® Precision Series



267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26701	T1	40	1.6	120	4.7	.01	10
26702	T2	40	1.6	120	4.7	.02	10
26703	T3	40	1.6	120	4.7	.02	10
26704	T4	40	1.6	120	4.7	.02	10
26705	T5	40	1.6	120	4.7	.02	10
26706	T6	40	1.6	120	4.7	.02	10
26707	T7	40	1.6	120	4.7	.02	10
26708	T8	40	1.6	120	4.7	.03	10
26709	T9	50	2.0	145	5.7	.03	10
26710	T10	50	2.0	145	5.7	.03	10
26715	T15	60	2.4	170	6.7	.05	10
26720	T20	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26790 6 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26790	TORX®:	
	T6, T7, T8 x 40mm	.30
	T9, T10 x 50mm	
	T15 x 60mm	

26791 Set 8 Pcs. TORX® Screwdriver Set

Item No. 26791 T1, T2, T3, T4, T5, T6, T7, T8



26799 8 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		lbs.
26799	TORX®: T3, T4, T5, T6, T7, T8 x 40mm	
	T9 x T10 x 50mm	.50



26792 7 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.


Item No.		lbs.
26792	TORX®:	
	T5, T6, T7, T8 x 40mm	.33
	T9, T10 x 50mm	
	T15 x 60mm	



92190 Master Technicians Bench Top Set

Metal frame. Equipped with 50 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92190	Phillips: #000, #00, #0, #1
	TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 2.86	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter



92191 51 Piece Precision Tool Tray Set

Tool box tray. Equipped with 51 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92191	Phillips: #000, #00, #0, #1
	Torx®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 3.14	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0, 4.0
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter



26001 Pocket Clip for Precision Screwdrivers

Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

Item No.		lbs.	pkg.
26001	Fits all Precision handles	.0035	1



26000 Plastic Precision Tool Rack

Rack holds 6 precision screwdrivers, can be set on workbench. Also has holes for hanging. Made from high quality plastic.

Item No.		lbs.	pkg.
26000	Rack for 6 Precision screwdrivers	.08	1

Wiha Soft Grip PicoFinish Precision Screwdrivers

The Comfortable Precision Screwdriver



Color coded symbols on rotating cap gives easy recognition of individual styles & sizes

CVM tool steel blade, hardened, hard chrome finish



Soft Grip Handle



Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



260 Slotted Precision Screwdriver, With PicoFinish Handle

Blade CVM steel, hardened, hard chromed.

Item No.	mm	Inch	mm	Inch	mm	Inch	Pkg.
26050	0.8	.03	40	1.6	134	5.3	10
26051	1.0	.04	40	1.6	134	5.3	10
26052	1.2	.05	40	1.6	134	5.3	10
26053	1.5	.06	40	1.6	134	5.3	10
26054	1.5	.06	60	2.4	154	6.1	10
26055	1.8	.07	40	1.6	134	5.3	10
26056	1.8	.07	60	2.4	154	6.1	10
26060	2.0	.08	40	1.6	140	5.5	10
26061	2.0	.08	60	2.4	160	6.3	10
26063	2.0	.08	100	3.9	200	7.9	10
26065	2.5	.09	50	2.0	150	5.9	10
26066	2.5	.09	75	3.0	175	6.9	10
26068	2.5	.09	100	3.9	200	7.9	10
26070	3.0	.13	50	2.0	150	5.9	10
26072	3.0	.13	100	3.9	200	7.9	10
26073	3.0	.13	150	5.9	250	9.8	10
26074	3.5	.14	60	2.4	160	6.3	10
26076	4.0	.16	60	2.4	160	6.3	10
26079	4.0	.16	100	3.9	200	7.9	10
26080	4.0	.16	150	5.9	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



26093 8 Pc. Slotted Precision Screwdriver Set, With Soft

PicoFinish Handle In storage pouch

Item No.		lbs.
26093	Slotted: .8, 1.2, 1.5, 2.0 x 40mm 2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54



261 Phillips Precision Screwdriver, With Soft PicoFinish

Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	pkg.
26130	000	40	1.6	2.0	.08	134	5.3	10
26132	00	40	1.6	2.0	.08	134	5.3	10
26133	00	60	2.4	2.0	.08	154	6.1	10
26135	0	50	2.0	3.0	.12	150	5.9	10
26136	0	75	3.0	3.0	.12	175	6.9	10
26140	1	60	2.4	4.0	.16	160	6.3	10
26142	1	80	3.1	4.0	.16	180	7.1	10
26145	1	150	5.9	4.0	.16	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



26193 8 Pc. Slotted & Phillips Precision Driver Set, With Soft

PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26193	Slotted: 1.0, 1.5, 2.0 x 40mm 2.5 x 50mm, 3.5 x 60mm Phillips: 00 x 40mm 0 x 50mm, 1 x 60mm	.55

Wiha Pico Soft Grip TORX®



267 TORX® Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Size	mm	Inch	mm	Inch	pkg.
26732	T1	40	1.6	134	5.3	10
26733	T2	40	1.6	134	5.3	10
26735	T3	40	1.6	134	5.3	10
26736	T4	40	1.6	134	5.3	10
26737	T5	40	1.6	134	5.3	10
26739	T6	40	1.6	140	5.5	10
26741	T7	40	1.6	140	5.5	10
26743	T8	40	1.6	140	5.5	10
26745	T9	50	2.0	150	5.9	10
26747	T10	50	2.0	150	5.9	10
26749	T15	60	2.4	160	6.3	10
26751	T20	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



26793 8 Pc. TORX® Precision Driver Set, With Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26793	TORX® : T1, T2, T3, T4, T5, T6, T7, T8 x 40mm	.50



26796 8 Pc. TORX® Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26796	TORX® : T5, T6, T7, T8 x 40mm T9, T10 x 50mm, T15, T20 x 60mm	.57

Wiha Pico Soft Grip Screw Holding



267 MagicSpring Screw Holding TORX® Screwdriver, With Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26729	T10	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10

*Metric dimensions actual - Inch dimensions approximate



26798 6 Pc. MagicSpring Screw Holding TORX® Screwdriver Set, With Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips. In storage pouch

Item No.		lbs.
26798	MagicSpring TORX® : T6, T7, T8 x 40mm T9, T10, T15 x 50mm	.45

Pico Soft Grip Precision Chip Lifter



26815 Soft PicoFinish Precision Chip Lifter

Blade chrome-vanadium-molybdenum steel, hardened, hard chromed.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26815	1	3.5	50	150	5.9	.03	1

Standard Soft PicoFinish handle



91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

Pico Soft Grip Hex Inch & Metric



263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	pkg.
26341	.028(.71)	40	1.6	134	5.3	10
26343	.035(.89)	40	1.6	134	5.3	10
26345	.050(1.27)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

26392 8 Piece Hex Inch Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Inch:	lbs.
26392	.028, .035, .050 x 1.6"	lbs.
	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.24



263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26341	.71(.028)	40	1.6	134	5.3	10
26343	.89(.035)	40	1.6	134	5.3	10
26345	1.27(.050)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

26393 7 Piece Hex Metric Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	lbs.
26393	.71, .89, 1.27 x 40mm	lbs.
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	.22

Pico Soft Grip Ball End Inch & Metric



264 Ball End Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



26493 7 Piece Inch Ball End Hex Precision Driver Set, With Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Ball End Hex Inch:	lbs.
26493	1/16, 5/64, 3/32 x 2.0"	lbs.
	7/64, 1/8, 9/64, 5/32 x 2.4"	.27



264 Ball End Hex Metric Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26441	1.27	40	1.6	134	5.3	10
26443	1.5	50	2.0	150	5.9	10
26445	2.0	50	2.0	150	5.9	10
26447	2.5	60	2.4	160	6.3	10
26449	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Nut Drivers Inch & Metric



265 Inch Nut Drivers, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26571	3/32	2.4	60	6.3	160	10
26572	7/64	2.4	60	6.3	160	10
26573	1/8	2.4	60	6.3	160	10
26574	9/64	2.4	60	6.3	160	10
26575	5/32	2.4	60	6.3	160	10
26576	3/16	2.4	60	6.3	160	10
26577	7/32	2.4	60	6.3	160	10
26578	1/4	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



26593 8 Piece Inch Nut Driver Set, With Precision Soft

PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish. Chrom-Top finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26593	Inch Nut Drivers: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72



91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1



265 Metric Nut Drivers, With Precision PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26579	1.5	60	2.4	160	6.3	10
26581	2.0	60	2.4	160	6.3	10
26582	2.5	60	2.4	160	6.3	10
26583	3.0	60	2.4	160	6.3	10
26584	3.5	60	2.4	160	6.3	10
26585	4.0	60	2.4	160	6.3	10
26586	4.5	60	2.4	160	6.3	10
26587	5.0	60	2.4	160	6.3	10
26588	5.5	60	2.4	160	6.3	10
26589	6.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



26596 8 Piece Metric Nut Driver Set, With Precision Soft

PicoFinish Handle Blade high alloy CVM tool steel, hardened, hard chrome finish. Chrom-Top finish on tip for a perfect fit.

In storage pouch

Item No.		lbs.
26596	Metric Nut Drivers: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5 x 60mm	.66

Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.


Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item No.	Dimensions	lbs.
40010	2.1" x 2.0" x 1.1"	.30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

Wiha Protturn Precision Screwdrivers



95190 6 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	Slotted	mm	mm	Phillips	Size	mm	lbs.
95190	Slotted:	1.5mm	40	Phillips:	00	40	.27
		2.5mm	50		0	50	
		3.5mm	60		1	60	



65090 9 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	Slotted	mm	mm	mm	mm	Phillips	Size	mm
65090	Slotted:	1.5	40	3.0	60	Phillips:	00	40
		2.0	50	3.5	60		0	50
		2.5	60	4.0	60		1	60



96800 Protturn Precision Chip Lifter

Molded on precision handle. Blade chrome-vanadium-molybdenum tool steel, hardened, black finish.

Item No.	Size	mm	mm	Inch	lbs.	pkg.
96800	1.0	50	145	5.7	.07	1



62990 5 Piece Slotted & Phillips Pocket Pack Set Wiha Protturn precision ball retainer handle & 4 Wiha interchangeable blades.

62990 Set includes the following blades:

Slotted: 1.5, 2.0, 3.0, 4.0

Phillips: #000, #00, #0, #1

lbs. .15



62993 9 Piece Slotted/Phillips/TORX® Work Station Set Wiha Protturn precision ball retainer handle & 8 Wiha interchangeable blades.


62993 Set includes the following blades:

Slotted: 1.5, 2.0, 3.0, 4.0

Phillips: #000, #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15, T20

lbs. .64



62995 22 Piece Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack Wiha Protturn precision ball retainer handle & 21 Wiha interchangeable blades. Set in canvas storage pouch

62995 Set includes the following blades:

Slotted: 1.5, 2.0, 3.0, 4.0 Phillips: #000, #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15, T20

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .87

62994 14 Piece Inch/Metric Ball End Hex Work Tech Pack

Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .66 Set in canvas storage pouch

Wiha SYSTEM 4 Precision Handles and Blades



28000 ESD Safe Dissipative Precision Handle with rotating control cap. Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04



28001 ESD Safe Dissipative Precision Adjustable Handle with rotating control cap.
Advantages:

- Use in ESD sensitive applications. Surface resistant 10^6 - 10^9 Ohms.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28001	4.0	.1574	14.0	.55	.04



26900 SYS 4 Standard Precision Handle, with rotating control cap. Accepts all SYSTEM 4 interchangeable blades. Wiha Precision handle, tapered, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26900	4.0	.1574	14.0	.55	.04



26901 SYSTEM 4 Standard Precision Adjustable handle with rotating control cap.
Advantages:

- Allows adjustable blade from 15 to 95mm.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26901	4.0	.1574	14.0	.55	.06



269 SYSTEM 4 Combined Slotted/Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed.

Item					
No.	mm	Size	mm	Inch	lbs.
26971	1.5 + 000		120	4.7	.05
26972	2.0 + 00		120	4.7	.05
26973	3.0 + 0		120	4.7	.05
26974	4.0 + 1		120	4.7	.06



269 SYSTEM 4 Pozidriv® Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26922	0 + 1		120	4.7	.03



269 SYSTEM 4 Slotted Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	mm	mm	mm	Inch	lbs.
26903	1.5 + 3.0		120	4.7	.05
26904	2.0 + 3.5		120	4.7	.05
26905	2.5 + 4.0		120	4.7	.06



269 SYS 4 TORX® Reversible Blade High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item			
No.	Size	Size	lbs.
26951	T6 + T8		.03
26952	T7 + T9		.03
26953	T10 + T15		.03
26954	T15 + T20		.03



269 SYSTEM 4 Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item					
No.	Size	Size	mm	Inch	lbs.
26911	000 + 00		120	4.7	.03
26912	0 + 1		120	4.7	.03



269 SYSTEM 4 TORX® Interchangeable Blade High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL

Item		
No.	Size	lbs.
26955	T3	.03
26956	T4	.03
26957	T5	.03

Wiha SYSTEM 4 Precision Blades

269 SYSTEM 4 Inch Hex Sizes,

Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	Inch	mm	Inch	lbs.
26921	.050	120	4.7	.06
26923	1/16	120	4.7	.06
26924	5/64	120	4.7	.06
26925	3/32	120	4.7	.06
26926	7/64	120	4.7	.06
26927	1/8	120	4.7	.06
26928	9/64	120	4.7	.06
26929	5/32	120	4.7	.06

269 SYSTEM 4 Metric Hex Sizes,

Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item				
No.	mm	mm	Inch	lbs.
26913	.71	120	4.7	.06
26914	.89	120	4.7	.06
26915	1.27	120	4.7	.06
26916	1.5	120	4.7	.06
26917	2.0	120	4.7	.06
26918	2.5	120	4.7	.06
26919	3.0	120	4.7	.06
26920	4.0	120	4.7	.06

280 SYSTEM 4 Inch Ball End Hex

Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item				
No.	Inch	mm	Inch	lbs.
28021	.050	120	4.7	.06
28023	1/16	120	4.7	.06
28024	5/64	120	4.7	.06
28025	3/32	120	4.7	.06
28026	7/64	120	4.7	.06
28027	1/8	120	4.7	.06
28028	9/64	120	4.7	.06
28029	5/32	120	4.7	.06

280 SYSTEM 4 Metric Ball End Hex

Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item					
No.	mm	mm	Inch	lbs.	pkg.
28033	1.5	120	4.7	.06	1
28034	2.0	120	4.7	.06	1
28035	2.5	120	4.7	.06	1
28036	3.0	120	4.7	.06	1
28037	4.0	120	4.7	.06	1

269 SYS 4 Metric Ball End & Standard

Hex, Reversible Blade CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips. One side hex, other side ballpoint hex.

Item				
No.	mm	mm	Inch	lbs.
26932	1.27 + 1.27	120	4.7	.05
26933	1.5 + 1.5	120	4.7	.05
26934	2.0 + 2.0	120	4.7	.06
26935	2.5 + 2.5	120	4.7	.06
26936	3.0 + 3.0	120	4.7	.06
26937	4.0 + 4.0	120	4.7	.06

269 SYSTEM 4 Nut Driver Inch,

Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item				
No.	Inch	Inch	Inch	lbs.
26962	3/32	.16	.16	.04
26963	7/64	.20	.20	.04
26964	1/8	.20	.20	.04
26965	9/64	.21	.24	.04
26966	5/32	.22	.24	.04
26967	3/16	.26	.28	.04
26968	7/32	.30	.32	.04
26969	1/4	1.34	.36	.04

269 SYSTEM 4 Nut Driver Metric,

Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item				
No.	mm	mm	Inch	lbs.
26940	1.5 + 1.8	.12	.12	.03
26941	2.0 + 2.5	.16	.16	.03
26938	1.5 -	.11	.11	.04
26939	1.8 -	.12	.12	.04
26949	2.0 -	.13	.13	.06
26950	2.5 -	.16	.16	.06
26942	3.0 -	.20	.20	.06
26943	3.2 -	.20	.20	.06
26944	3.5 -	.22	.24	.06
26945	4.0 -	.22	.24	.06
26946	4.5 -	.25	.28	.06
26947	5.0 -	.27	.28	.06
26948	5.5 -	.30	.32	.06

Wiha SYSTEM 4 Drive-Loc Precision Locking Tools



26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



269 SYSTEM 4 Slotted Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item			
No.	mm	mm	lbs.
26958	1.5 + 3.0		.02
26959	2.0 + 3.5		.02
26960	2.5 + 4.0		.02



269 SYSTEM 4 Phillips Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item			
No.	Size	Size	lbs.
26975	000 + 00		.02
26976	0 + 1		.02



269 SYSTEM 4 TORX® Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item			
No.	Size	Size	lbs.
26977	T1 + T2		.02
26978	T3 + T4		.02
26979	T5 + T6		.02
26980	T6 + T8		.02
26981	T7 + T9		.02
26982	T10 + T15		.02



280 SYSTEM 4 Pozidriv® Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item			
No.	Size	Size	lbs.
28002	0 + 1		.02



280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28003	1.3 + 1.3		.02
28004	1.5 + 1.5		.02
28005	2.0 + 2.0		.02
28006	2.5 + 2.5		.02
28007	3.0 + 3.0		.02
28008	4.0 + 4.0		.02



280 SYSTEM 4 Metric Nut Drivers Drive-Loc Reversible

Locking Blades On 4mm Hex blades

Item			
No.	mm	mm	lbs.
28009	1.5 + 1.8		.02
28010	2.0 + 2.5		.02
28011	3.0 + 3.0		.02
28012	3.2 + 3.2		.02
28013	3.5 + 3.5		.02
28014	4.0 + 4.0		.02
28015	4.5 + 4.5		.02
28016	5.0 + 5.0		.02
28017	5.5 + 5.5		.02



26985 12 Piece SYSTEM 4 Precision ESD Drive-Loc Set

In storage pouch

Item No.

26985 ESD Safe Drive-Loc Handle

Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0

lbs. .44 Phillips: 000x00, 0x1

TORX®: T1xT2, T3xT4, T5xT6, T6xT8, T7xT9, T10xT15

Wiha Canvas Pouch Sets



Canvas Pouch

26990 4 Piece Slotted & Phillips Precision Interchangeable Blade Set


Wiha ESD Safe precision collet lock handle and 3 Wiha interchangeable blades.

26990 Set includes the following blades:

● **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

📦 lbs. .17



Canvas Pouch

26991 6 Piece Slotted & Phillips Precision Interchangeable Blade Set


Wiha ESD Safe precision collet lock handle and 5 Wiha interchangeable blades. In canvas pouch.

26991 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

📦 lbs. .29



Canvas Pouch

26992 17 Pc. Slotted, Phillips and Ball End Hex Metric/Inch Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 15 Wiha interchangeable blades.

26992 Set include the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

● **Ball End Hex Inch:** .050, 1/16, 5/64, 7/64, 3/32, 1/8"

● **Ball End Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

Protorn Chip Lifter - #96800

📦 lbs. .63



Canvas Pouch

28080 22 Piece Slotted, Phillips, TORX® & Hex Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 20 Wiha interchangeable blades.

28080 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⚙ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15


● **Hex:** .028, .035

● **Ball Hex:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Protorn Chip Lifter - #96800

📦 lbs. .33

ESD Technicians Kit Precision Screwdrivers & Tweezers



Canvas Pouch

44590 12 Pc. Slotted, Phillips and TORX® Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle, 7 Wiha interchangeable blades & 4 ESD Safe Tweezers.

44590 Set includes the following blades:

● **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

⚙ **TORX®:** T6, T7, T8, T9, T10, T15

ESD Safe Precision Tweezers:

44501 Fine Point - AA SA


44509 Extra Fine Point - 5 SA

44505 Flat and Blunt - 2a SA

44510 Curved Fine Point - 7a SA

📦 lbs. .60

Slotted, Phillips, TORX® Set In Steel Box



28094 11 Piece Slotted, Phillips & TORX® Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 10 Wiha interchangeable blades.


28094 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⚙ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

📦 lbs. 1.51



26993 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 5 Wiha interchangeable blades.


26993 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

📦 lbs. .87

ESD Anti-Static Vinyl Pouch Set



28091 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha-ESD Safe  precision collet lock handle and 5 Wiha interchangeable blades.

28091 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↔ **lbs.** .25

ESD Safe



28097 9 Piece Slotted, Phillips and TORX Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 8 Wiha Interchangeable blades.

28097 Set includes the following blades:


↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⊗ **TORX:** T5, T6, T7, T8, T9, T10, T15

↔ **lbs.** .33

ESD Safe



28084 13 Piece Slotted, Phillips and Ball End Hex Inch Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 12 Wiha interchangeable blades.

28084 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **Ball End Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .44

ESD Safe



28087 8 Piece TORX Precision Interchangeable Blade Set

Wiha-ESD Safe  precision collet lock handle and 7 Wiha interchangeable blades.

28087 Set includes the following blades:


⊗ **TORX Sizes on standard blades:** T3, T4, T5

⊗ **TORX Sizes on reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .29

ESD Safe



26996 5 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 4 Wiha interchangeable blades.

26996 ⊕ **Phillips:** 000, 00, 0, 1

↓  **Slotted:** 1.5, 2.0, 3.0, 3.5mm

↔ **lbs.** .54



26997 9 Pc. Slotted, Phillips and TORX Precision Interchangeable Blade Set

Wiha ESD Safe  precision collet lock handle and 8 Wiha Interchangeable blades.

26997 ⊕ **Phillips:** 000, 00, 0, 1

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊗ **TORX:** T6, T7, T8, T9, T10, T15

↔ **lbs.** .64



26999 9 Piece Hex Metric Precision Blade Set

Wiha ESD Safe  precision collet lock handle and 8 Wiha interchangeable blades.

26999 ⬢ **Hex Metric:** .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm

↔ **lbs.** .66



26989 9 Piece Hex Inch Precision Blade Set

Wiha ESD Safe  precision collet lock handle and 8 Wiha interchangeable blades.

26989 ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .64



26995 5 Piece TORX Precision Blade Set

Wiha ESD Safe  precision collet lock handle and 4 interchangeable blades.

26995 ⊗ **TORX:** T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .52



26987 8 Piece TORX Precision Blade Set

Wiha ESD Safe  precision collet lock handle and 7 interchangeable blades.

26987 Set includes the following blades:

⊗ **TORX standard blades:** T3, T4, T5

⊗ **TORX reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .62

Wiha SYSTEM 4 Micro Bits

SYSTEM 4 Handles & Micro Bits

Tips

Exact fit,
precision
machined

Rotating Cap
for precise
turning and
control

Tapered Handle
allows rapid rotation,
requires less clearance

Bits CVM steel,
hardened

Use bits directly in handle or with 4" bit extension



750 SYSTEM 4 Slotted Micro Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75008	0.8	28	1.1	.01
75012	1.2	28	1.1	.01
75015	1.5	28	1.1	.01
75018	1.8	28	1.1	.01
75020	2.0	28	1.1	.01
75025	2.5	28	1.1	.01
75030	3.0	28	1.1	.01
75035	3.5	28	1.1	.01
75040	4.0	28	1.1	.01



751 SYSTEM 4 Phillips Micro Bits

High alloy chrome-vanadium-molybdenum steel, hardened, on 4 mm hex stock.

Item				
No.	Size	mm	Inch	lbs.
75105	000	28	1.1	.01
75110	00	28	1.1	.01
75115	0	28	1.1	.01
75120	1	28	1.1	.01



753 SYSTEM 4 Hex Metric Micro Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75307	.71	28	1.1	.01
75309	.89	28	1.1	.01
75313	1.27	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01



753 SYSTEM 4 Hex Inch Micro Bits

High alloy chrome-vanadium-molybdenum steel, hardened, on 4 mm hex stock.

Item				
No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



75800 SYSTEM 4 Standard Precision Bit Handle

Rotating control cap for precise turning and control. Wiha Precision handle, tapered, high quality plastic, impact resistant, ball retainer. Accepts all SYSTEM 4 Series bits. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle

with rotating control cap. Wiha precision handle, tapered, high quality plastic, impact resistant. 110mm/4.3" OAL

Advantages:

- For working in ESD sensitive applications
Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item					
No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06

SYSTEM 4 Micro Bit Extension Blades



75900 Extension Blade For SYSTEM 4 Micro Bits

Shaft CVM steel, hardened, corrosion protected.
Ball retainer bit extension for 4mm bits.

Item				
No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07



75901 Magnetic Bit Extension Blade For SYSTEM 4 Micro Bits

Shaft Chrome-vanadium-molybdenum steel, hardened, corrosion protected. Magnetic bit holder.

Item				
No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04

Wiha SYSTEM 4 Micro Bits



757 SYSTEM 4 TORX® Micro Bits

High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



757 SYSTEM 4 Security TORX® Micro Bits

High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75727	T7s	28	1.1	.01
75728	T8s	28	1.1	.01
75729	T9s	28	1.1	.01
75735	T10s	28	1.1	.01
75739	T15s	28	1.1	.01
75742	T20s	28	1.1	.01



753 SYSTEM 4 Metric Security Hex Micro Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75322	2.0	28	1.1	.01
75327	2.5	28	1.1	.01
75332	3.0	28	1.1	.01
75342	4.0	28	1.1	.01

753 SYSTEM 4 Security Hex Inch Micro Bits

Item				
No.	Inch	mm	Inch	lbs.
75362	5/64	28	1.1	.01
75364	3/32	28	1.1	.01
75366	7/64	28	1.1	.01
75368	1/8	28	1.1	.01
75370	9/64	28	1.1	.01
75372	5/32	28	1.1	.01

Micro Bit 1/4" Drive Power Tool Adapter




75902 Micro Bit 1/4" Drive Power Tool Adapter

Shaft CVM steel, hardened, corrosion protected.

For 4mm bits. 2.3" OAL

Item				
No.	Size	mm	mm	lbs.
75902	4.0	60	4.0	.07

Protturn Precision Power Driver Bit Set



75989 SYSTEM 4 Protturn Precision Power Screwdriver Set W/Micro Bits, 40 Pcs. In Storage Box.

Includes Wiha precision handle, Protturn Power Screwdriver & 38 interchangeable Micro bits.

Item SYSTEM 4

No. Combination Bit Set

75989 Set with System 4 Standard Precision Handle

Set includes the following bits:

- ⬮ Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⬮ Phillips: 000, 00, 0, 1
- ⬮ TORX®: T3, T4, T5, T6, T7, T8, T9, T10, T15
- ⬮ Hex Metric: 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬮ Hex Inch: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬮ lbs. 1.18

SYSTEM 4 Interchangeable Bit Set

75990 SYSTEM 4 Interchangeable Bit Set,

40 Pcs. In Canvas Pouch. Includes Wiha precision handle, bit extension & 38 interchangeable bits.


Item SYSTEM 4

No. Combination Bit Set

75990 Set with ESD Safe Precision Handle

Set includes the following bits:

- ⬮ Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⬮ Phillips: 000, 00, 0, 1
- ⬮ TORX®: T3, T4, T5, T6, T7, T8, T9, T10, T15
- ⬮ Hex Metric: 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬮ Hex Inch: .028(.7), .035(.9), .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬮ 100mm Bit Extension
- ⬮ lbs. .65



40 Pc. Set



Wiha SYS 4 Micro Bits & Compact Bit Sets

75999 **SYSTEM 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set, 26 Pcs. In Compact Fold Out Box.** Wiha precision handle, bit extension & 24 interchangeable bits.

Item No. Combination Bit Set

75999 Set with Standard Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
-  **Phillips:** 000, 00, 0, 1
-  **Hex Metric:** .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm
-  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
-  **100mm Bit Extension**
-  **lbs. .64**



26 Pc. Set

75792 **SYSTEM 4 TORX® Precision Interchangeable Bit Set, 11 Pcs. In Compact Fold Out Box.**

Sets includes Wiha precision handle, bit extension and 9 Wiha interchangeable bits.

Item SYSTEM 4 TORX® Bit Set

No. Set with ESD Safe Precision Handle

75792 and the following bits:

-  **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
-  **100mm Bit Extension**
-  **lbs. .54**



11 Pc. Set

75395 **SYSTEM 4 Hex Inch & Metric Precision Interchangeable Bit Set, 18 Pcs. In Compact Fold Out Box.** Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

Item No. Combination Bit Set

75395 Set with Standard Precision Handle

Includes the following bits:

-  **Hex Metric:** .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm
-  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
-  **100mm Bit Extension**
-  **lbs. .58**



18 Pc. Set

759 sets **SYSTEM 4 Slotted/Phillips/Hex Inch/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.** Sets include your choice of Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

Item Handle Options for SYSTEM 4


No. Combination Bit Sets

75991 Set with Standard Precision Handle

75992 Set with ESD Safe Precision Handle

Sets include the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
-  **Phillips:** 000, 00, 0, 1
-  **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
-  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
-  **100mm Bit Extension**
-  **lbs. .64**



27 Pc. Set

75996 **SYSTEM 4 Interchangeable Bit Set, 40 Pcs. In Storage Box.** Includes Wiha precision handle, bit extension & 38 interchangeable bits.


Item SYSTEM 4

No. Combination Bit Set

75996 Set with ESD Safe Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
-  **Phillips:** 000, 00, 0, 1
-  **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
-  **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
-  **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
-  **100mm Bit Extension**
-  **lbs. 1.04**



40 Pc. Set

75994 **SYSTEM 4 Slotted/Phillips/Hex Metric/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.**

Set includes Wiha precision handle, bit extension and 25 Wiha interchangeable bits.


Item SYSTEM 4

No. Combination Bit Set

75994 Set with ESD Safe Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
-  **Phillips:** 000, 00, 0, 1
-  **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
-  **Hex Metric:** .71, .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm
-  **100mm Bit Extension**
-  **lbs. .64**



27 Pc. Set

Technicians MicroBit Sets

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension

Rotation cap

Light weight & compact

Handle tapered for precise control

Surface resistance of handles is $10^6 - 10^9$ Ohms

Bits hardened for extreme durability



75093 SYSTEM 4 Slotted, Phillips, TORX® Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75093 Set with ESD Safe Precision Handle

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⊗ **TORX®:** T6, T7, T8, T9, T10, T15, T20

○ **100mm Bit Extension**

↔ **lbs.** .17



75094 SYSTEM 4 Slotted, Phillips, Hex Inch Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75094 Set with ESD Safe Precision Handle

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⬢ **Hex Inch:** .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8"

○ **100mm Bit Extension**

↔ **lbs.** .17



75095 SYSTEM 4 Slotted, Phillips, Hex Metric Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75095 Set with ESD Safe Precision Handle

↓  **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⬢ **Hex Metric:** .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↔ **lbs.** .17



75096 SYSTEM 4 Hex Inch & Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75096 Set with ESD Safe Precision Handle

⬢ **Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

⬢ **Hex Metric:** .89, 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↔ **lbs.** .17

Micro Bit Handle Storage Sets

Micro precision bits on 4mm hex drive

Storage handle

Bits of exclusive CRM-72 tool steel

Bits hardened for extreme durability



75981 Micro Bit Handle Storage Slotted & Phillips Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75981 ↓  **Slotted:** 1.2, 1.5, 2.0mm

⊕ **Phillips:** 000, 00, 0

↔ **lbs.** .08



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75983 ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8"

↔ **lbs.** .08



75985 Micro Bit Handle Storage TORX® Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75985 ⊗ **TORX®:** T3, T4, T5, T6, T7, T8

↔ **lbs.** .08

Wiha Precision Electronic Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.

C70 tool steel HR60 hardness

Glare free
black finish

Precision ground
cutting edges for
smooth cuts



The Comfortable Precision Pliers & Cutters




Velvet soft ergonomically
designed multi component
handle

Lay-on, riveted
precision joint

Light weight design for maximum
user comfort in production work

Electronic Diagonal Cutters



Full Flush


56818 Precision Electronic Diagonal Cutters, Wide Pointed Head

Cutting edge - full flush. With return spring. C70 special tool steel.

For an absolutely flush cut of copper wire.

#56818	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	5	.22

Electronic Diagonal Cutters



Semi Flush


56815 Precision Electronic Diagonal Cutters, Wide Pointed Head

Cutting edge - semi flush. With return spring. C70 special tool steel.

Universal small diagonal cutter for cutting copper wires.

Item No.	Cut		Medium		Pkg.	lbs.
#56815	mm	Inch	Capacity	Hard Wire		
	138	5.5	2.0mm/12AWG	0.8	5	.23

Electronic Diagonal Cutters



Full Flush

Wire Holding Spring


56825 Precision Electronic Diagonal Cutters, Wide Shape With

Wire Holding Spring Wide, Pointed head. Cutting edge - full flush.

With return spring & fixture for holding ends of wires that have been cut off. C70 special tool steel. For an absolutely flush cut of copper wire.

#56825	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	5	.23

Electronic Diagonal Cutters



Full Flush

56812 Precision Electronic Diagonal Cutters, Narrow Shape

Extra narrow, short head for working in particularly restricted spaces.


Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56812	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.8mm/20AWG	5	.19

Electronic Diagonal Cutters



Wire Holding Spring




Full Flush

56813 Precision Electronic Diagonal Full Flush Cutters With Wire Trapping Spring Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56813	mm	Inch	Cut Capacity	Pkg.	lbs.
	128	5.0	1.0mm/18AWG	5	.19

Electronic Oblique 48° Cutter




Full Flush

56833 Electronic Oblique 48° Cutter

Wide pointed head. Cutting edge - full flush. With cutting edge at 48° for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56833	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	5	.22

Narrow Front Cutter/Long Nose Pliers




Full Flush

56830 Electronic Narrow 30° Front Cutter / Long Nose Pliers

Extremely narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. Edge at 30° to face end of pliers for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56830	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.6mm/22AWG	5	.19

Electronic Pointed Pliers




56801 Electronic Short Nose Precision Pliers

Narrow, short head. Smooth jaws. Width at tip is only 1.2mm. C70 special tool steel. For holding small components as well as for holding and angling wires.

#56801	mm	Inch	Pkg.	lbs.
	138	5.5	5	.23

Electronic Stripping Pliers



56871 Electronic Stripping Pliers

Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	Pkg.	lbs.
	180	7.0	0.81-2.59	20-10	5	.15





Professional Quality ESD Tweezers

ESD SAFE • STATIC DISSIPATIVE • HYPO ALLERGENIC COATED • TEXTURED GRIPPING SURFACE



Universal Fine Point Tweezers

Item No.	Description	wt.
44501	AA SA ESD - 130mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Fine Round Points For Assembly

Item No.	Description	wt.
44506	3 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Sturdy Long, Fine Round Points

Item No.	Description	wt.
44502	GG SA ESD - 130mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Fine Round Points Shorter

Item No.	Description	wt.
44507	3c SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Long Narrow Body Low Force

Item No.	Description	wt.
44503	SS SA ESD - 135mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Very Fine Points/Tapered To Tip

Item No.	Description	wt.
44508	4 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Reduced Body To Medium Point

Item No.	Description	wt.
44504	2 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Extra Fine Points/Tapered To Tip

Item No.	Description	wt.
44509	5 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Flat Round Tip Smooth Sides

Item No.	Description	wt.
44505	2a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.



Curved Extra Fine Rounded Tips

Item No.	Description	wt.
44510	7a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

Wiha Professional Quality ESD Safe Tweezers



Holds 0.8 to 2mm Diameter

Item No.	Description	wt.
44511	50 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Narrow Rounded Tip Serrated, Guide Pin

Item No.	Description	wt.
44518	22 SA ESD - 150mm	.10

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Holds 1.5 to 3mm Diameter

Item No.	Description	wt.
44512	51 SA ESD - 130mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Universal Blunt Tip Serrated

Item No.	Description	wt.
44520	40 SA ESD - 145mm	.11

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Holds 3.5 to 7mm Diameter

Item No.	Description	wt.
44513	52 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



MicroTip 45° Hook 1x1x2mm

Item No.	Description	wt.
44521	12 SA-SMD ESD - 120mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Holds 6.5 to 10mm Diameter

Item No.	Description	wt.
44514	53 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



MicroTip For Chips Angled 1.6 x 1 x 1mm

Item No.	Description	wt.
44522	13 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Angled 3.5 to 7mm Diameter

Item No.	Description	wt.
44515	54 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.



Long Rounded to 1.0mm Wide No Serration

Item No.	Description	wt.
44523	PSF SA ESD - 125mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy. Special stainless steel, anti-magnetic and acid resistant.

Wiha Professional Quality ESD Safe Tweezers



Flat Bent 35°, 3mm Diameter Grip

Item No.	Description	wt.
44524	58 SA-SMD ESD - 117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



MicroTip Bent 30° 1.6mm

Item No.	Description	wt.
44529	8b SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Curved Extra Fine, 3mm Long Straight Tip

Item No.	Description	wt.
44525	7abb SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Flat Bent 35° - 2mm Diameter Grip Radius

Item No.	Description	wt.
44530	59 SA-SMD ESD - 117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Narrow Body Low Force Bent 35° - 3mm Tip

Item No.	Description	wt.
44526	SSbb SA ESD - 140mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



ESD Safe General Purpose Fine Point

Item No.	Description	wt.
44531	1 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Angled Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
44527	5abb SA ESD - 117mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Heavy Duty Strong Tweezers Tapered To Strong Point

Item No.	Description	wt.
44532	00 SA ESD - 120mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
44528	5bb SA ESD - 107mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.



Angled & Slightly Bent With Extra Fine Tips

Item No.	Description	wt.
44533	7 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommaloy.
Special stainless steel, anti-magnetic and acid resistant.

Professional Quality Tweezers In Standard & Special Sizes



Blunt Tip, Serrated

Item No.	Description	wt.
43010	40 - 145mm	.11

Carbon steel tweezers. Nickel-plated finish.



Narrow Body Low Force Bent 35° - 3mm Long Tip

Item No.	Description	wt.
46971	SSbb SA - 140mm	.10

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Heavy Duty Forming Tweezers

Item No.	Description	wt.
43800	8 SA - 120mm	.10

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Extra Fine Points Bent 30° - 3mm Long Tip

Item No.	Description	wt.
46972	5bb SA - 107mm	.07

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Long Tapered to Fine Tip Serrated

Item No.	Description	wt.
45010	30 - 145mm	.09

Carbon steel tweezers. Nickel-plated finish.



Fine Hooked & Tapered Tips

Item No.	Description	wt.
46987	6 SA - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Curved Extra Fine, 3mm Long Angled Tip

Item No.	Description	wt.
46950	7abb SA - 120mm	.07

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Blunt 1mm Wide Tip Serrated

Item No.	Description	wt.
49185	PSF - 125mm	.08

Carbon steel tweezers. Nickel-plated finish.



Fine Points Angled With 40° - Tip Bend

Item No.	Description	wt.
46970	5abb SA - 117mm	.07

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Flat Round Tip Bent 30° Smooth Sides

Item No.	Description	wt.
49368	2ab SA - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.

Professional Quality Tweezers In Standard & Special Sizes



Angled Upward Extra Fine Tips

Item No.	Description	wt.
49375	7 SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Fine Points for Assembly

Item No.	Description	wt.
49383	3 SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Flat Round Tip Smooth Sides

Item No.	Description	wt.
49378	2a SA - 120mm	.07
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Blunt Tips - 1.0mm Wide Serrated

Item No.	Description	wt.
49385	PSF SA - 125mm	.09
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Reduced Body to Medium Point

Item No.	Description	wt.
49381	2 SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Long Narrow Body Low Force

Item No.	Description	wt.
49387	SS SA - 140mm	.07
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Strong, Long Tapered Fine Tips

Item No.	Description	wt.
49388	GG SA - 130mm	.09
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Flat and Broad Tips 3mm Wide

Item No.	Description	wt.
49382	F SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Flat Round Tip Smooth Sides

Item No.	Description	wt.
49478	2a SA T - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Teflon finish tweezers made from Vomalloy.		

Professional Quality Tweezers In Standard & Special Sizes



Longer Narrow Body Low Force

Item No.	Description		wt.
49487	SSL SA - 160mm		.10

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Very Fine Round Points & Tapered To Tip

Item No.	Description		wt.
49779	4 SA - 110mm		.08

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Fine Round Points Shorter

Item No.	Description		wt.
49783	3c SA - 110mm		.08

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.



Very Fine Points Tapered Long

Item No.	Description		wt.
49879	4L SA - 140mm		.08

Stainless steel, anti-magnetic and acid resistant.
Brushed finish tweezers made from Vommaloy.

Professional SMD Tweezers

COMPONENT POSITIONING & DESOLDERING TWEEZERS



Flat Bent 35° 3mm Dia. Milled Slot

Item No.	Description		wt.
42142	58 SA SMD - 117mm		.08

Stainless steel, anti-magnetic and acid resistant.
Brushed Finish tweezers made from Vommaloy.



Holds 6.5 to 10mm Diameter

Item No.	Description		wt.
42150	53 SA - 120mm		.08

Stainless steel, anti-magnetic and acid resistant.
Brushed Finish tweezers made from Vommaloy.



Vertical Long, Holds 2.5 to 5mm Diameter

Item No.	Description		wt.
43414	64 SA - 145mm		.10

Stainless steel, anti-magnetic and acid resistant.
Brushed Finish tweezers made from Vommaloy.



Bent Long, Holds 3.5 to 7mm Diameter

Item No.	Description		wt.
43419	63 SA - 145mm		.10

Stainless steel, anti-magnetic and acid resistant.
Brushed Finish tweezers made from Vommaloy.

Super Thin Foil Tweezers



Blunt, Thin .035", Very Low Force

Item No.	Description		wt.
49215	112 SA - 100mm		.05

Stainless steel, anti-magnetic and acid resistant.
Polished finish tweezers made from Vommaloy.

Professional Quality Wafer Tweezers



Back Stop, Top 2.4 Bottom 7mm

Item No.	Description	wt.
43799	37 SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



16mm Wide With Back Stop

Item No.	Description	wt.
44159	49 SA - 125mm	.09
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



9mm Wide With Back Stop Pins

Item No.	Description	wt.
43948	89 SA - 125mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Bent Large 20mm Wide, Back Stop

Item No.	Description	wt.
46069	61 SA - 125mm	.11
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



12mm Wide With Back Stop Pins

Item No.	Description	wt.
43949	89a SA - 125mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Long Flat Straight 5mm Wide

Item No.	Description	wt.
49584	39 SA - 125mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		



Angled 4 Pin 12mm Wide

Item No.	Description	wt.
44149	16 SA - 125mm	.08
Stainless steel, anti-magnetic and acid resistant. Wafer tweezers made from Vomalloy.		



Flat Angled 5mm Wide

Item No.	Description	wt.
49587	38a SA - 103mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vomalloy.		

Cutting Tweezers



End Cutting Tweezers

Item No.	Description	wt.
46500	D - 95mm	.11
Carbon steel. UnPlated finish.		



Curved Very Fine Cutting Tweezers

Item No.	Description	wt.
48307	C7 - 115mm	.08
Carbon steel made from Vomalloy. Brushed finish.		

Professional Quality Guide Pins Tweezers



Fine Tip Straight, Guide Pin, Fine Serrated

Item No.	Description	wt.
42012	17 - 120mm	.08
Carbon steel. Nickel-plated finish.		



Narrow Body, Bent, Long, Guide Pin, Serrated Tweezers

Item No.	Description	wt.
49154	22b S - 155mm	.09
Stainless steel. Natural finish.		



Bent, Long, Guide Pin, Fine Serrated Tweezers

Item No.	Description	wt.
45113	33b - 165mm	.10
Carbon steel. Nickel-plated finish.		



Narrow Body, Straight, Long, Guide Pin, Serrated Tweezers

Item No.	Description	wt.
49159	22 SA - 155mm	.10
Stainless steel, anti-magnetic and acid resistant. Brushed finish tweezers made from Vommaloy.		



Universal Straight Guide Pin, Fine Serrated

Item No.	Description	wt.
45212	35 SA - 120mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vommaloy.		

Isolated Tweezers With Dipped Handles



Fine Bent, Guide Pin, Serrated

Item No.	Description	wt.
45213	35B SA - 145mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vommaloy.		



Universal Pointed Tip Isolated

Item No.	Description	wt.
48100	AA isol - 130mm	.10
Carbon steel. Nickel-plated finish.		



Long Pointed, Angled Tip, Guide Pin & Lock

Item No.	Description	wt.
49150	20S - 150mm	.10
Stainless steel. Polished finish.		



Narrow Pointed & Straight Isolated Serrated

Item No.	Description	wt.
49158	22 isol - 155mm	.10
Carbon steel. Nickel-plated finish.		

Professional Quality Self Closing Tweezers



Long Straight Tweezers

Item No.	Description	wt.
43270	R29 S - 160mm	.11
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		



Reverse 3 Fine Round Points For Assembly

Item No.	Description	wt.
45803	R3 SA - 115mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		



Long Bent Tweezers

Item No.	Description	wt.
43271	R29b SA - 160mm	.12
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		



Chip Holding Curved Fine Micro Tip

Item No.	Description	wt.
46610	R10 SA SMD - 117mm	.07
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		



Pointed Self Closing Long Straight

Item No.	Description	wt.
43272	R29 - 160mm	.11
Carbon steel. Nickel-plated finish.		



Straight Flat Square End 5mm Wide

Item No.	Description	wt.
48050	R50 SA - 105mm	.07
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		



Long Bent Tweezers

Item No.	Description	wt.
43273	R29b - 160mm	.12
Carbon steel. Nickel-plated finish.		



Strong With Square Ends Deep Serrated

Item No.	Description	wt.
48075	R30 - 160mm	.13
Carbon steel. Nickel-plated finish.		



Reverse 2 Flat Round Tip Smooth Sides

Item No.	Description	wt.
45802	R2a SA - 115mm	.08
Stainless steel, anti-magnetic and acid resistant. Brushed Finish tweezers made from Vomalloy.		

Microscopy Tweezers



MicroTip 30° Bend & 0.5mm Slot Milled

Item No.	Description	wt.
46611	11SA SMD - 117mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.



MicroTip Straight & 0.5mm Slot Milled

Item No.	Description	wt.
46615	8SA SMD - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.



MicroTip 40° Hook 1x1x2mm Long

Item No.	Description	wt.
46612	12SA SMD - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.



Uncoated

MicroTip Bent 30° - 1.6mm

Item No.	Description	wt.
46616	8b SA SMD - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.



MicroTip 40° Hook 1.6x1x1mm Wide

Item No.	Description	wt.
46613	13SA SMD - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.




MicroTip 30° Bent & Angled With 0.5 Slot

Item No.	Description	wt.
46619	19 SA SMD - 120mm	.08

Stainless steel, anti-magnetic and acid resistant.
 Brushed finish tweezers made from Vomalloy.

Mirrors-Clean Room Quality

For Visual Checks and Fault Finding at Inaccessible Locations



Magnifying,
Boilable



40410 - #0



40420 - #3

Inspection Mirror - Stainless 20mm

Item No.	Description	wt.
40420	#3 IM - 205mm	.09



40426 - #6

Inspection Mirror - Stainless 26mm

Item No.	Description	wt.
40426	#6 IM - 215mm	.10



40422 - #4

Inspection Mirror - Stainless 22mm Short Stem

Item No.	Description	wt.
40422	#4 IM - 175mm	.10



40430 - #8

Inspection Mirror - Stainless 30mm

Item No.	Description	wt.
40430	#8 IM - 215mm	.10



40414 - #0

Inspection Mirror - Stainless 14mm

Item No.	Description	wt.
40414	#0 IM - 200mm	.09



40424 - #5

Inspection Mirror - Stainless 24mm Short Stem

Item No.	Description	wt.
40424	#5 IM - 175mm	.10




Disposable Inspection Mirrors

Item No.	Description	wt.
40425	5 Pack - Plastic	.10

Set includes: White disposable inspection mirror
 #5 Inspection Mirrors - 24mm x 146mm

Quality Excavators & Probes

One Piece All Stainless Probes



All Stainless Single Piece Construction-Clean Room Quality



Stainless Steel Probe

Item No.	Description	wt.
43221	3220.1-07 Probe - 170mm	.08
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43225	3220.5-09 Probe - 170mm	.07
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43222	3220.2-06 Probe - 170mm	.07
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43226	3220.6-10 Probe - 170mm	.07
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43223	3220.3-05 Probe - 170mm	.07
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43228	3220.8-02 Probe - 170mm	.08
Stainless steel, polished finish.		



Stainless Steel Probe

Item No.	Description	wt.
43224	3220.4-16 Probe - 170mm	.07
Stainless steel, polished finish.		

Probes-Clean Room Quality

Stainless Steel, For Work on PCB's, Modeling, Polished Finish

For Levering & Removing Components

Stainless Steel Straight Probe

Item No.	Description	wt.
43229	3220.9-11 Probe - 170mm	.07

One Piece All Stainless Hooks

Sculpting & Scribing Hooks-Clean Room Quality

- Sharp Hooks For Cutting & Marking
- Surgical Stainless Steel
- Natural Finish
- For Work on PCB's, Modeling
- All Stainless Single Piece Construction



Approx. 5mm Wide Short Tapered & Curved

Item No.	Description	wt.
43236	3230.6-60 Hook - 155mm	.10



Approx. 4mm Wide Squared & Curved

Item No.	Description	wt.
43235	3230.5-59 Hook - 155mm	.10

One Piece All Stainless Excavators

Excavators-Clean Room Quality

- Can Be Used as Mini-Spatulas
- For Work on PCB's, Modeling
- Surgical Stainless Steel, Polished Finish
- Single Piece Construction



#43251

1mm Excavator

Item No.	Description	wt.
43251	3225.1-39 - 165mm	.09



#43252

2mm Excavator

Item No.	Description	wt.
43252	3225.2-35 - 165mm	.09



#43253

2.5mm Excavator

Item No.	Description	wt.
43253	3225.3-31 - 165mm	.10

Wiha Ratchet Crimpers

Ratchet End Sleeve Crimper



5 die nests
side entry
crimp



43612 Ratchet End Sleeve Crimper

Crimps Insulated & non-insulated end sleeves. 6 crimp positions range AWG 26-18, 18-16, 14, 12, 10, 8. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43612	220mm/8.6"	26-8	1.18	1

Ratchet Crimper Push On Terminals



Crimp Profile
"F"/"B"



43624 Ratchet Crimper Push On Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 22-20, 20-16, 16-14, 12-10. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43624	220mm/8.6"	22-10	1.06	1

Ratchet Crimper For Standard Connectors



Crimp Profile



43618 Ratchet Crimper For Standard Connectors

Crimps Insulated & non-insulated connectors. 3 crimp positions range AWG 20-16 red, 16-14 blue, 12-10 yellow. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43618	220mm/8.6"	20-10	1.06	1

Ratchet Crimper For Eye Terminals



Self adjusting
side entry crimp



43643 Ratchet Crimper For Eye Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 26-20, 20-14, 12-10, 8-6. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43643	220mm/8.6"	26-6	1.02	1

Automatic Stripping Tool



Interchangeable stripping blade cassettes



Cuts & strips up to 10mm²/8 AWG - Strips PVC, THHW, TEFLON insulations



Ergonomic design with non-slip two component handles



Easy/snag free wire removal from tool - jaws stay open after strip

Self Adjusting Cut & Strip Tool



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



Cables: Conduit wire, Flex mains cable, Equipment wire, Flat modplug cable etc.

34-8 AWG

44212 Self Adjusting Cutting & Stripping Tool

Easily interchangeable stripping cassettes enables a wide range of insulations from PVC to PTFE. Light weight soft grip handle qualified for high volume production and portable/field usage.

#44212	mm	Inch	AWG	Strip Dim.	lbs.	Pkg.
	191	7.5	34 - 8	0.02-10mm²	.30	1

Replaceable Cassette - Straight Blade



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



Straight

34-8 AWG

44214 Straight Blade Cassette, PVC Insulations

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44214	AWG	Strip Range	lbs.	Pkg.
	34 - 8	0.02-10mm²	.02	1

Replaceable Cassette - 4-16mm²



Stripping Range
4-16mm²



Radius Blade

10-5 AWG

44269 Replaceable Cassette, 4-16mm Stripping Range


Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44269	AWG	Strip Range	lbs.	Pkg.
	10 - 5	4-16mm²	.02	1

Replaceable Cassette - "V" Blade



"V" Blade Stripping Range
0.1 - 4mm²



VBC for PTFE


28-12 AWG

44213 Replaceable VBC or PTFE Cassette, "V" Blade

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44213	AWG	Strip Range	lbs.	Pkg.
	28 - 12	0.1-4mm²	.02	1

Heavy Duty Adjustable Cable Stripper



Circular + Straight
Window Strip
Circular + Spiral Strip



Cables: Power cable. Multi-conductor control, fiber optic and copper trunk cables

44217 Jacket Stripper - Heavy Duty Adjustable

Professional stripping tool for cables of all insulations types. Positive locking positions for circular, lengthways and spiral strips. Interchangeable cable retention hooks give cable stripping capacity of up to 40mm/1.57 inch diameter. Replacement cutting blades can be stored within the tool.

#44217	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	168	6.6	4.5-40mm ²	0-4.5mm	.26	1

Replacement Blade



Replacement cutting blades can be stored within the tool



44218 Replacement Blade For 44217 Stripper

Interchangeable cable retention hooks give cable stripping capacity of up to 40mm/1.57 inch diameter. Replacement cutting blades can be stored within the tool.

#44218	Replacement Blade For	lbs.	Pkg.
	44217 Stripper	.01	1

Precision Adjustable Stripping Tool



Replaceable Blade



Cables: Multi core cable, Modplug cable. Fiber optic cable etc.



44220 Precision Adjustable Stripping Tool

Professional stripping tool removes the outer cable jacket from signal, telephone, audiovisual, instrumentation and data transmission copper and fiber optic cables up to 11mm/0.43" diameter. The tool features a 9 position indexed blade height adjustment wheel ensuring accurate & repeatable stripping results. Simply squeeze together to open the stripping cavity - insert cable, rotate once and pull off the scrap insulation. Smooth, Lightweight and pocket size. No open blade, replacement blades encased within cassette.

#44220	mm	Inch	Strip Range	Strip Range	lbs.	Pkg.
	90.5	3.6	2.5-11mm	.10"/0.43"	.06	1

Replacement Blade



Replacement Blade



44221 Replacement Blade For 44220 Stripper

Stripping capacity of up to 2.5-11mm/0.43" diameter.

#44221	Strip Range	Strip Dim.	lbs.	Pkg.
	2.5-11mm	11mm/0.43"	.01	1

CATV/Satellite Stripper



Strips: RG59 & RG6 CATV coaxial cables



44206 CATV/Satellite Stripper

Quickly & simply strips RG59 & RG6 coaxial cables for CATV "F" type connectors giving industry standard strip lengths of 6.35mm/.25" for both the braid and the conductor. Patented spring-like action and built-in stop eliminates the need for manual adjustment for different cables.

#44206	mm	Inch	Strip Length	lbs.	Pkg.
	83	3.3"	6.35mm/.25" Braid/Conductor	.05	1



Adjustable Screw
For Precise Blade
Positioning



4 Cable V-blocks



Reversible
Cassettes
Long Life



Stepped Stripping
Depth For
Reduced Friction

2 Step				
	A	B		
	44237	44238	44239	44240
	Blue	Red	Yellow	Orange
"B" mm	6.8	6.0	12.0	9.2
"B" Inch	0.27"	0.24"	0.47"	0.36"
"A"	User adjusted			

Blue Cassette Stripping Tool Kit



2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Red Cassette Stripping Tool Kit



2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Yellow Cassette Stripping Tool Kit




2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Replacement Stripping Cassettes



Cables: RG
58/59/62/174/180/
188/195/316/6/
Belden 8281



Stripping Tool - No Cassette



44200 Cassette Hand-Stripping Tool Accurate & versatile coaxial hand-stripping tool. Holds all 2 or 3 step cassettes.

#44200	lbs.	Pkg.
	.07	1

44227 Blue Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44227	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	6.8mm	.09	1
			0.10"-0.30"	0.27"		

44222 2 Step Red Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 6.0mm/.24". Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44222	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	6.0mm	.09	1
			0.10"-0.30"	0.24"		

44224 2 Step Yellow Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 12.0mm/.47". Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44224	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	12.0mm	.09	1
			0.10"-0.30"	0.47"		

442 2 Step Replacement Stripping Cassettes High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	Color	Strip Range	Strip Dim.	lbs.	Pkg.
44237	Blue	1.87-7.6mm	6.8(0.27")	.01	1
44238	Red	1.87-7.6mm	6.0(0.24")	.01	1
44239	Yellow	1.87-7.6mm	12.0(0.47")	.01	1
44240	Orange	1.87-7.6mm	9.2(0.36")	.01	1

Stripping Tool Set



44290 10 Piece Set, Cassette Hand-Stripping Tool

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Universal tool body accepts all cassettes.

#44290	Set includes: Stripping Tool, L-key, 4 Cable V-blocks & 4 Stripping Cassettes	lbs.	Pkg.
		.10	1



Adjustable Screw
For Precise Blade
Positioning



4 Cable V-blocks




Reversible
Cassettes
Long Life



Stepped Stripping
Depth For Reduce
Friction

3 Step



	44251	44255	44259	44260	44261
	Brown	Green	White	Dk. Brown	Black
"C" mm	8.3	6.0	6.8	7.5	5.5
"B" mm	2.7	6.0	2.5	3.5	5.5
"A"	User adjusted				

3 Step Brown Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8282



44241 3 Step Brown Cassette Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44241	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	8.3mm(B)	.08	1
			0.10"-0.30"	2.7mm(C)		

3 Step Green Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8283



44245 3 Step Green Cassette Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44245	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	6.0mm(B)	.08	1
			0.10"-0.30"	6.0mm(C)		

3 Step White Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8284



44249 3 Step White Cassette Kit


Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

#44249	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
	90	3.54	1.87-7.6mm	6.8mm(B)	.08	1
			0.10"-0.30"	2.5mm(C)		

3 Step Replacement Stripping Cassettes



Cables: RG
58/59/62/174/180/188/
195/316/6




442 3 Step Replacement Stripping Cassettes

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	Color	Strip B	Strip C	lbs.	Pkg.
44251	Brown	2.7mm/.11"	8.3mm/.33"	.01	1
44255	Green	6.0mm/.24"	6.0mm/.24"	.01	1
44259	White	2.5mm/.10"	6.8mm/.27"	.01	1
44260	Dk.Brown	3.5mm/.14"	7.5mm/.30"	.01	1
44261	Black	5.5mm/.22"	5.5mm/.22"	.01	1

Stripping Tool Set



44292 11 Piece Set, Cassette Hand-Stripping Tool

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Universal tool body accepts all cassettes.

#44292	Set includes: Stripping Tool, L-key,	lbs.	Pkg.
	4 Cable V-blocks, 5 Stripping Cassettes	.11	1

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
26000 9	26135 10	26449 12	26702 9	26927 16	26993 18
26001 9	26136 10	26455 12	26703 9	26928 16	26995 19
26008 4	26140 10	26457 12	26704 9	26929 16	26996 19
26010 4	26142 10	26459 12	26705 9	26932 16	26997 19
26012 4	26145 10	26461 12	26706 9	26933 16	26999 19
26015 4	26190 5	26463 12	26707 9	26934 16	28000 15
26018 4	26192 5	26465 12	26708 9	26935 16	28001 15
26020 4	26193 10	26467 12	26709 9	26936 16	28002 17
26022 4	26194 5	26490 7	26710 9	26937 16	28003 17
26023 4	26199 5	26491 7	26715 9	26938 16	28004 17
26025 4	26205 6	26493 12	26720 9	26939 16	28005 17
26027 4	26210 6	26499 7	26721 11	26940 16	28006 17
26028 4	26307 6	26510 8	26723 11	26941 16	28007 17
26030 4	26309 6	26515 8	26725 11	26942 16	28008 17
26032 4	26313 6	26520 8	26727 11	26943 16	28009 17
26033 4	26315 6	26523 8	26729 11	26944 16	28010 17
26034 4	26316 6	26525 8	26731 11	26945 16	28011 17
26035 4	26320 6	26527 8	26732 11	26946 16	28012 17
26040 4	26323 6	26530 8	26733 11	26947 16	28013 17
26041 4	26325 6	26531 8	26735 11	26948 16	28014 17
26042 4	26327 6	26532 8	26736 11	26949 16	28015 17
26050 10	26330 6	26535 8	26737 11	26950 16	28016 17
26051 10	26331 6	26536 8	26739 11	26951 15	28017 17
26052 10	26333 6	26539 8	26741 11	26952 15	28021 16
26053 10	26336 6	26540 8	26743 11	26953 15	28023 16
26054 10	26340 6	26545 8	26745 11	26954 15	28024 16
26055 10	26341 12	26547 8	26747 11	26955 15	28025 16
26056 10	26343 12	26550 8	26749 11	26956 15	28026 16
26060 10	26345 12	26555 8	26751 11	26957 15	28027 16
26061 10	26347 12	26556 8	26790 9	26958 17	28028 16
26063 10	26349 12	26560 8	26791 9	26959 17	28029 16
26065 10	26351 12	26563 8	26792 9	26960 17	28033 16
26066 10	26353 12	26570 8	26793 11	26961 17	28034 16
26068 10	26363 12	26571 13	26796 11	26962 16	28035 16
26070 10	26367 12	26572 13	26798 11	26963 16	28036 16
26072 10	26369 12	26573 13	26799 9	26964 16	28037 16
26073 10	26371 12	26574 13	26810 9	26965 16	28080 18
26074 10	26390 6	26575 13	26815 11	26966 16	28084 19
26076 10	26391 6	26576 13	26900 15	26967 16	28087 19
26079 10	26392 12	26577 13	26901 15	26968 16	28091 19
26080 10	26393 12	26578 13	26903 15	26969 16	28094 18
26090 4	26399 6	26579 13	26904 15	26971 15	28097 19
26092 5	26413 7	26581 13	26905 15	26972 15	28620 7
26093 10	26415 7	26582 13	26911 15	26973 15	28622 7
26099 4	26416 7	26583 13	26912 15	26974 15	28624 7
26100 5	26419 7	26584 13	26913 16	26975 17	28626 7
26101 5	26420 7	26585 13	26914 16	26976 17	28627 7
26102 5	26423 7	26586 13	26915 16	26977 17	28629 7
26105 5	26425 7	26587 13	26916 16	26978 17	28632 7
26107 5	26427 7	26588 13	26917 16	26979 17	28633 7
26108 5	26430 7	26589 13	26918 16	26980 17	28637 7
26109 5	26431 7	26590 8	26919 16	26981 17	28638 7
26110 5	26436 7	26591 8	26920 16	26982 17	28644 7
26113 5	26439 7	26592 8	26921 16	26985 17	40010 13
26114 5	26440 7	26593 13	26922 15	26987 19	40410 35
26115 5	26441 12	26596 13	26923 16	26989 19	40414 35
26130 10	26443 12	26598 8	26924 16	26990 18	40420 35
26132 10	26445 12	26599 8	26925 16	26991 18	40422 35
26133 10	26447 12	26701 9	26926 16	26992 18	40424 35

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Notes:
40425	35	44261	41	49150	33	75325	20	
40426	35	44269	38	49154	33	75327	21	
40430	35	44290	40	49158	33	75330	20	
42012	33	44292	41	49159	33	75332	21	
42142	31	44501	26	49185	29	75340	20	
42150	31	44502	26	49215	33	75342	21	
43010	29	44503	26	49368	29	75350	20	
43221	36	44504	26	49375	30	75352	20	
43222	36	44505	26	49378	30	75354	20	
43223	36	44506	26	49381	30	75356	20	
43224	36	44507	26	49382	30	75358	20	
43225	36	44508	26	49383	30	75360	20	
43226	36	44509	26	49385	30	75362	21	
43228	36	44510	26	49387	30	75364	21	
43229	36	44511	27	49388	30	75366	21	
43235	36	44512	27	49478	30	75368	21	
43236	36	44513	27	49487	31	75370	21	
43251	36	44514	27	49584	32	75372	21	
43252	36	44515	27	49587	32	75395	22	
43253	36	44518	27	49779	31	75703	21	
43270	34	44520	27	49783	31	75704	21	
43271	34	44521	27	49879	31	75705	21	
43272	34	44522	27	56801	25	75706	21	
43273	34	44523	27	56812	24	75707	21	
43414	31	44524	28	56813	25	75708	21	
43419	31	44525	28	56815	24	75709	21	
43612	37	44526	28	56818	24	75710	21	
43618	37	44527	28	56825	24	75715	21	
43624	37	44528	28	56830	25	75720	21	
43643	37	44529	28	56833	25	75727	21	
43799	32	44530	28	56871	25	75728	21	
43800	29	44531	28	62990	14	75729	21	
43948	32	44532	28	62993	14	75735	21	
43949	32	44533	28	62994	14	75739	21	
44149	32	44590	18	62995	14	75742	21	
44159	32	45010	29	65090	14	75792	22	
44200	40	45113	33	75008	20	75800	20	
44206	39	45212	33	75012	20	75801	20	
44212	38	45213	33	75015	20	75900	20	
44213	38	45802	34	75018	20	75901	20	
44214	38	45803	34	75020	20	75902	21	
44217	39	46069	32	75025	20	75981	23	
44218	39	46500	32	75030	20	75983	23	
44220	39	46610	34	75035	20	75985	23	
44221	39	46611	35	75040	20	75989	21	
44222	40	46612	35	75093	23	75990	21	
44224	40	46613	35	75094	23	75991	22	
44227	40	46615	35	75095	23	75992	22	
44237	40	46616	35	75096	23	75994	22	
44238	40	46619	35	75105	20	75996	22	
44239	40	46950	29	75110	20	75999	22	
44240	40	46970	29	75115	20	91118	8,13	
44241	41	46971	29	75120	20	92190	9	
44245	41	46972	29	75307	20	92191	9	
44249	41	46987	29	75309	20	95190	14	
44251	41	48050	34	75313	20	96800	14	
44255	41	48075	34	75315	20			
44259	41	48100	33	75320	20			
44260	41	48307	32	75322	21			

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:

Catalog Item No. 99006.wi
 version - 5/15/13

Subject to change without notice

©2013 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.




99060.wi - Product Guide



99004.wi - Shop Tools Catalog



99914.wi - TORX Catalog



99002.wi - Screwdrivers Catalog




99951.wi - Bits Catalog



99001.wi - TorqueControl Catalog



99934.wi - Hex Tools Catalog



99919.wi - Insulated Catalog



99945.wi - ESD Catalog



99977.wi - Pliers/Crimpers Catalog