



**Dimensions (In.)**

**Specifications:**

- Type: standard "AA"
- Color: black
- Number of cells: 10
- Mini snaps: spaced .50"; 4 prong;  
male = .225" (O.D.), female = .205" x (I.D.)
- Body: polypropylene
- Hardware: nickel plated
- Spring: 0.7mm 65c spring wire
- Temperature rating: -5°C ~ +95°C