



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
ARITHMETICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. SEALING CODE 0 - UNSEALED
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS ALLOWED, BUT NOT LIMITED TO LOW MARKS, COLOR
BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DNP-4.7-CS-0
4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
5. PART IS MANUFACTURED TO GEOMETRIC TOLERANCES. CENTERLINE
DIMENSIONS ARE FOR REFERENCE ONLY.

32-34863	01	-	107	33232645	13968717	15512515			
15512462	05	-	106	15512460	13968717	15512515	A		
15512465	05	105	15512459	13968717	15512515		F		
15512444	05	-	104	15512458	13968717	15512515	D		
15512443	05	-	103	15512457	13968717	15512515	C		
15512462	05	AA	102	15512456	13968717	15512515	B		
15512461	05	AA	101	15512455	13968717	15512515	A		
PART	NO	REV	NA	TYPE	CONNECTOR	PLR	CPA	USCAR	OPTION

		N/A		PROCESS SENSITIVE DIMENSIONS			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED							
DIMENSIONAL RANGE (MM)		CHART					
FROM	TO	> 0	> 30	> 70	> 100		
		> 20	> 30	> 150	> 250		
TOLERANCE LESS OR OTHERWISE SPECIFIED							
+0.15	+0.2	+0.3	+0.4	+0.6	+0.8		
IN ALL TOLERANCES							

[illegible]