











1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

15512462	05	AA	102	15512456	13968717	15512515	B
15512461	05	AA	101	15512455	13968717	15512515	A
PART NO	REV	N/P	TYPE	CONNECTOR	PLR	CPA	USCAR OPTION

DIMENSIONAL RANGE (MM)										CHART	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300			
TOLERANCE UNLESS OTHERWISE SPECIFIED											
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.5	±2	±3
ANGULAR TOLERANCE ±2°											

[illegible]