

3M™ Dyna-Couplers – 3", 4.5" and 6"

For use with all model 3M™ Dynatel™ Locators

3M now offers multiple Dyna-coupler accessory sizes to meet almost any locating need with the addition of the new 4.5" coupler to our current line of Dyna-couplers (including the 3" and 6"). 3M Dyna-couplers (all sizes) can be used on all models of 3M Dynatel Cable/Pipe Locators and permit coupling of RF trace tone to large diameter pipes, bundle cables and cables enclosed in accessible non-metallic ducts.

Physical Specifications:	3" Dyna-coupler	4.5" Dyna-coupler	6" Dyna-coupler
Length:	8.25" (21 cm)	10.75" (27.3 cm)	13.75" (35 cm)
Width:	4.3" (10.9 cm)	6.4" (16.3 cm)	8.5" (21.6 cm)
Thickness:	1.41" max (3.6 cm)	1.52" max (3.9 cm)	1.71" (4.35 cm)
Weight:	0.59 lb. (0.27kg)	1.2 lb. (0.54kg)	0.94 lb. (0.43kg)
Closed internal diameter	3.18" (8.1 cm)	4.72" (12 cm)	7" (17.8 cm)
Material:	All are high impact plastic (ABS)		

Note: Length includes the phone plug.
Width measured at midpoint outer diameter.
Thickness includes the hinge hardware.

Environmental Specifications:	
Operating Temperature:	-4°F to 122°F (-20°C to 50°C)
Storage Temperature:	-4°F to 158°F (-20°C to 70°C)
Water Resistant:	Short time immersion permissible, allow to drain before storage

Ordering Information:

Product Description	Stock No.
3001 Dyna-Coupler, 3"	80-6100-7468-6
4001 Dyna-Coupler, 4.5"	80-6113-2583-0
1196 Dyna-Coupler w/Pouch, 6"	80-6104-1118-5
3019 Locator Coupler Accessory Kit, 3" (Includes 3" Coupler, 9011 Coupler Cable & Coupler Pouch)	80-6107-6471-6
4519 Locator Coupler Accessory Kit, 4.5" (Includes 4.5" Coupler, 9011 Coupler Cable & Coupler Pouch)	80-6113-3520-1
1196/C Locator Coupler Accessory Kit, 6" (Includes 6" Coupler, 9011 Coupler Cable & Coupler Pouch)	80-6113-1249-9



3M™ Dyna-Couplers, Model 3001-3" (top), Model 4001-4.5" (middle) and Model 1196-6" (bottom)



3M and Dynatel are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Conditional Lifetime Warranty

This product will be free from defects in material and manufacture for a period of ninety (90) days after purchase. This warranty does not extend to any of 3M's products which have been subjected to misuse, neglect, accident or improper applications, nor shall it extend to products which have been repaired or substantially altered outside 3M's manufacturing or repair facility, nor to any associated instruments, equipment or apparatus. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.**



Track and Trace Solutions

6801 River Place Blvd.
Austin, TX 78726-9000
800/426 8688
Fax 800/626 0329
www.3M.com/dynatel

Please recycle. Printed in USA.
© 3M 2009. All rights reserved.
75-4700-3001-8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[3001](#) [7000006221](#) [7000031490](#) [7000031716](#) [7000057744](#) [7000058326](#)