




APEX 2.8 mm Terminals & Cavity Plug

FEMALE




FEMALE TERMINAL PART NUMBER	WIRE GAGE	TERMINAL MATERIAL	TERMINAL PLATING
54002200	22	CuTeSn/CuBe	Sn
54001800	18-20	CuTeSn/CuBe	Sn
54001400	14-16	CuTeSn/CuBe	Sn
54001000	10-12	CuTeSn/CuBe	Sn
54002203	22	CuTeSn/CuBe	NiPdAu
54001803	18-20	CuTeSn/CuBe	NiPdAu
54001403	14-16	CuTeSn/CuBe	NiPdAu
54001003	10-12	CuTeSn/CuBe	NiPdAu

Note: The Nickel/Palladium/Gold plating is recommended for diesel engine applications.

Nyogel 8917 low friction insertion grease available on female terminal.


NYE 7606 grease available on female terminal for dry circuit applications.

MALE



MALE TERMINAL PART NUMBER	WIRE GAGE	TERMINAL MATERIAL	TERMINAL PLATING
54002201	22	CuTeSn	Sn
54001801	18-20	CuTeSn	Sn
54001401	14-16	CuTeSn	Sn
54001001	10-12	CuTeSn	Sn
54002230	22	CuTeSn	NiPdAu
54001818	18-20	CuTeSn	NiPdAu
54001441	14-16	CuTeSn	NiPdAu
54002229	22	CuTeSn	NiAu
54001819	18-20	CuTeSn	NiAu

APEX 2.8 mm Cavity Plug



Part No. 54200005

Note: Locks on seal retainers.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[54001000RWC](#) [54001001](#) [54001001RWC](#) [54001003RWC](#) [54001400RWA](#) [54001400RWC](#) [54001401](#)
[54001401RWA](#) [54001401RWC](#) [54001403RWC](#) [54001441](#) [54001441RWC](#) [54001800RWA](#) [54001800RWC](#)
[54001801](#) [54001801RWA](#) [54001801RWC](#) [54001803RWA](#) [54001803RWC](#) [54001818](#) [54001818RWC](#)
[54002200RWC](#) [54002201](#) [54002201RWA](#) [54200005](#) [54002230RWC](#) [54002230](#) [54001441RWA](#) [54002200RWA](#)
[54001403RWA](#) [54002230-L](#) [54002201RWC](#) [54001000RWA](#) [54001001RWA](#) [54200005-B](#) [54001800-L](#) [54001401-L](#)
[54001801-L](#) [54002230RWA](#) [54001803-L](#) [54001818RWA](#) [54002203RWA](#) [54002203RWC](#) [54002202-L](#)