

## P4KE SERIES

### GLASS PASSIVATED JUNCTION TRANSIENT VOLTAGE SUPPRESSOR POWER 400 Watt

#### BREAK DOWN VOLTAGE

6.8 to 440 Volt

#### DO-41



Unit : inch(mm)

#### FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-O
- Excellent clamping capability
- Low zener impedance
- Fast response time: typically less than 1 ps from 0 volts to BV min
- ESD IEC-61000-4-2 Air  $\pm 30$ kV, Contact  $\pm 30$ kV
- Lead free in compliance with EU RoHS 2011/65/EU directive

#### MECHANICAL DATA

- Case: JEDEC DO-41 Molded plastic
- Terminals: Axial leads, solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end
- Weight: 0.012 ounce, 0.336 gram



### MAXIMUM RATINGS AND CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

### DEVICES FOR BIPOLAR APPLICATIONS

For Bidirectional use C or CA Suffix for types  
Electrical characteristics apply in both directions.

| Rating                                                                                       | Symbol          | Value                | Units                       |
|----------------------------------------------------------------------------------------------|-----------------|----------------------|-----------------------------|
| Peak Power Dissipation at $T_A=25^\circ\text{C}$ , $t_p=1\text{ms}$ (Notes 1)                | $P_{PP}$        | 400                  | Watts                       |
| ESD IEC-61000-4-2 (Air)<br>ESD IEC-61000-4-2 (Contact)                                       | $V_{ESD}$       | $\pm 30$<br>$\pm 30$ | kV                          |
| Typical Thermal Resistance Junction to Air Lead Lengths 0.375", (9.5mm)<br>(Notes 2)         | $R_{\theta JA}$ | 60                   | $^\circ\text{C} / \text{W}$ |
| Peak Pulse Current on $t_p=10/1000\mu\text{s}$ waveform (Notes 1)                            | $I_{PPM}$       | see Table            | Amps                        |
| Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load (Notes 3) | $I_{FSM}$       | 40                   | Amps                        |
| Operating Junction and Storage Temperature Range                                             | $T_J, T_{STG}$  | -65 to +175          | $^\circ\text{C}$            |

#### NOTES :

1. Non-repetitive current pulse, per Fig. 3 and derated above  $T_A=25^\circ\text{C}$  per Fig. 2.
2. Mounted on Copper Leaf area of  $1.57\text{ in}^2$  ( $40\text{mm}^2$ ).
3. 8.3ms single half sine-wave, duty cycle= 4 pulses per minutes maximum.
4. A transient suppressor is selected according to the working peak reverse voltage ( $V_{RWM}$ ), which should be equal to or greater than the DC or continuous peak operating voltage level.



## P4KE SERIES


| Part Number                       |           | Reverse Stand-off Voltage     | Breakdown Voltage                |      | Test Current   | Reverse Leakage                   |      | Max. Clamp Voltage<br>10/1000μs  | Peak Pulse Current<br>10/1000μs | Marking Code |           |
|-----------------------------------|-----------|-------------------------------|----------------------------------|------|----------------|-----------------------------------|------|----------------------------------|---------------------------------|--------------|-----------|
|                                   |           | V <sub>RWM</sub><br>(Notes 4) | V <sub>BR</sub> @ I <sub>T</sub> |      | I <sub>T</sub> | I <sub>R</sub> @ V <sub>RWM</sub> |      | V <sub>C</sub> @ I <sub>PP</sub> | I <sub>PP</sub>                 |              |           |
|                                   |           |                               | Min.                             | Max. |                | UNI                               | BI   |                                  |                                 |              |           |
| UNI                               | BI        | V                             | V                                | V    | mA             | μA                                | μA   | V                                | A                               | UNI          | BI        |
| 400W Transient Voltage Suppressor |           |                               |                                  |      |                |                                   |      |                                  |                                 |              |           |
| P4KE6.8                           | P4KE6.8C  | 5.5                           | 6.12                             | 7.48 | 10             | 1000                              | 2000 | 10.8                             | 38                              | P4KE6.8      | P4KE6.8C  |
| P4KE6.8A                          | P4KE6.8CA | 5.8                           | 6.45                             | 7.14 | 10             | 1000                              | 2000 | 10.5                             | 40                              | P4KE6.8A     | P4KE6.8CA |
| P4KE7.5                           | P4KE7.5C  | 6.05                          | 6.75                             | 8.25 | 10             | 500                               | 1000 | 11.7                             | 36                              | P4KE7.5      | P4KE7.5C  |
| P4KE7.5A                          | P4KE7.5CA | 6.4                           | 7.13                             | 7.88 | 10             | 500                               | 1000 | 11.3                             | 37                              | P4KE7.5A     | P4KE7.5CA |
| P4KE8.2                           | P4KE8.2C  | 6.63                          | 7.38                             | 9.02 | 10             | 200                               | 400  | 12.5                             | 33                              | P4KE8.2      | P4KE8.2C  |
| P4KE8.2A                          | P4KE8.2CA | 7.02                          | 7.79                             | 8.61 | 10             | 200                               | 400  | 12.1                             | 35                              | P4KE8.2A     | P4KE8.2CA |
| P4KE9.1                           | P4KE9.1C  | 7.37                          | 8.19                             | 10   | 1              | 50                                | 100  | 13.8                             | 30                              | P4KE9.1      | P4KE9.1C  |
| P4KE9.1A                          | P4KE9.1CA | 7.78                          | 8.65                             | 9.5  | 1              | 50                                | 100  | 13.4                             | 31                              | P4KE9.1A     | P4KE9.1CA |
| P4KE10                            | P4KE10C   | 8.1                           | 9                                | 11   | 1              | 10                                | 20   | 15                               | 28                              | P4KE10       | P4KE10C   |
| P4KE10A                           | P4KE10CA  | 8.55                          | 9.5                              | 10.5 | 1              | 10                                | 20   | 14.5                             | 29                              | P4KE10A      | P4KE10CA  |
| P4KE11                            | P4KE11C   | 8.9                           | 9.9                              | 12.1 | 1              | 5                                 | 10   | 16.2                             | 26                              | P4KE11       | P4KE11C   |
| P4KE11A                           | P4KE11CA  | 9.4                           | 10.5                             | 11.6 | 1              | 5                                 | 10   | 15.6                             | 27                              | P4KE11A      | P4KE11CA  |
| P4KE12                            | P4KE12C   | 9.72                          | 10.8                             | 13.2 | 1              | 1                                 | 1    | 17.3                             | 24                              | P4KE12       | P4KE12C   |
| P4KE12A                           | P4KE12CA  | 10.2                          | 11.4                             | 12.6 | 1              | 1                                 | 1    | 16.7                             | 25                              | P4KE12A      | P4KE12CA  |
| P4KE13                            | P4KE13C   | 10.5                          | 11.7                             | 14.3 | 1              | 1                                 | 1    | 19                               | 22                              | P4KE13       | P4KE13C   |
| P4KE13A                           | P4KE13CA  | 11.1                          | 12.4                             | 13.7 | 1              | 1                                 | 1    | 18.2                             | 23                              | P4KE13A      | P4KE13CA  |
| P4KE15                            | P4KE15C   | 12.1                          | 13.5                             | 16.5 | 1              | 1                                 | 1    | 22                               | 19                              | P4KE15       | P4KE15C   |
| P4KE15A                           | P4KE15CA  | 12.8                          | 14.3                             | 15.8 | 1              | 1                                 | 1    | 21.2                             | 20                              | P4KE15A      | P4KE15CA  |
| P4KE16                            | P4KE16C   | 12.9                          | 14.4                             | 17.6 | 1              | 1                                 | 1    | 23.5                             | 18                              | P4KE16       | P4KE16C   |
| P4KE16A                           | P4KE16CA  | 13.6                          | 15.2                             | 16.8 | 1              | 1                                 | 1    | 22.5                             | 19                              | P4KE16A      | P4KE16CA  |
| P4KE18                            | P4KE18C   | 14.5                          | 16.2                             | 19.8 | 1              | 1                                 | 1    | 26.5                             | 16                              | P4KE18       | P4KE18C   |
| P4KE18A                           | P4KE18CA  | 15.3                          | 17.1                             | 18.9 | 1              | 1                                 | 1    | 25.2                             | 17                              | P4KE18A      | P4KE18CA  |
| P4KE20                            | P4KE20C   | 16.2                          | 18                               | 22   | 1              | 1                                 | 1    | 29.1                             | 14                              | P4KE20       | P4KE20C   |
| P4KE20A                           | P4KE20CA  | 17.1                          | 19                               | 21   | 1              | 1                                 | 1    | 27.7                             | 15                              | P4KE20A      | P4KE20CA  |
| P4KE22                            | P4KE22C   | 17.8                          | 19.8                             | 24.2 | 1              | 1                                 | 1    | 31.9                             | 13                              | P4KE22       | P4KE22C   |
| P4KE22A                           | P4KE22CA  | 18.8                          | 20.9                             | 23.1 | 1              | 1                                 | 1    | 30.6                             | 14                              | P4KE22A      | P4KE22CA  |
| P4KE24                            | P4KE24C   | 19.4                          | 21.6                             | 26.4 | 1              | 1                                 | 1    | 34.7                             | 12                              | P4KE24       | P4KE24C   |
| P4KE24A                           | P4KE24CA  | 20.5                          | 22.8                             | 25.2 | 1              | 1                                 | 1    | 33.2                             | 13                              | P4KE24A      | P4KE24CA  |
| P4KE27                            | P4KE27C   | 21.8                          | 24.3                             | 29.7 | 1              | 1                                 | 1    | 39.1                             | 11                              | P4KE27       | P4KE27    |
| P4KE27A                           | P4KE27CA  | 23.1                          | 25.7                             | 28.4 | 1              | 1                                 | 1    | 37.5                             | 11.2                            | P4KE27A      | P4KE27CA  |
| P4KE30                            | P4KE30C   | 24.3                          | 27                               | 33   | 1              | 1                                 | 1    | 43.5                             | 10                              | P4KE30       | P4KE30C   |
| P4KE30A                           | P4KE30CA  | 25.6                          | 28.5                             | 31.5 | 1              | 1                                 | 1    | 41.4                             | 10                              | P4KE30A      | P4KE30CA  |
| P4KE33                            | P4KE33C   | 26.8                          | 29.7                             | 36.3 | 1              | 1                                 | 1    | 47.7                             | 9                               | P4KE33       | P4KE33C   |
| P4KE33A                           | P4KE33CA  | 28.2                          | 31.4                             | 34.7 | 1              | 1                                 | 1    | 45.7                             | 9                               | P4KE33A      | P4KE33CA  |
| P4KE36                            | P4KE36C   | 29.1                          | 32.4                             | 39.6 | 1              | 1                                 | 1    | 52                               | 8                               | P4KE36       | P4KE36C   |
| P4KE36A                           | P4KE36CA  | 30.8                          | 34.2                             | 37.8 | 1              | 1                                 | 1    | 49.9                             | 8.4                             | P4KE36A      | P4KE36CA  |
| P4KE39                            | P4KE39C   | 31.6                          | 35.1                             | 42.9 | 1              | 1                                 | 1    | 56.4                             | 7.4                             | P4KE39       | P4KE39C   |
| P4KE39A                           | P4KE39CA  | 33.3                          | 37.1                             | 41   | 1              | 1                                 | 1    | 53.9                             | 7.8                             | P4KE39A      | P4KE39CA  |
| P4KE43                            | P4KE43C   | 34.8                          | 38.7                             | 47.3 | 1              | 1                                 | 1    | 61.9                             | 6.8                             | P4KE43       | P4KE43C   |
| P4KE43A                           | P4KE43CA  | 36.8                          | 40.9                             | 45.2 | 1              | 1                                 | 1    | 59.3                             | 7.1                             | P4KE43A      | P4KE43CA  |
| P4KE47                            | P4KE47C   | 38.1                          | 42.3                             | 51.7 | 1              | 1                                 | 1    | 67.8                             | 6.2                             | P4KE47       | P4KE47C   |
| P4KE47A                           | P4KE47CA  | 40.2                          | 44.7                             | 49.4 | 1              | 1                                 | 1    | 64.8                             | 5                               | P4KE47A      | P4KE47CA  |
| P4KE51                            | P4KE51C   | 41.3                          | 45.9                             | 56.1 | 1              | 1                                 | 1    | 73.5                             | 5.7                             | P4KE51       | P4KE51C   |




## P4KE SERIES

| Part Number                       |           | Reverse Stand-off Voltage     | Breakdown Voltage                |      | Test Current   | Reverse Leakage                   |    | Max. Clamp Voltage<br>10/1000µs  | Peak Pulse Current<br>10/1000µs | Marking code |           |
|-----------------------------------|-----------|-------------------------------|----------------------------------|------|----------------|-----------------------------------|----|----------------------------------|---------------------------------|--------------|-----------|
|                                   |           | V <sub>RWM</sub><br>(Notes 4) | V <sub>BR</sub> @ I <sub>T</sub> |      | I <sub>T</sub> | I <sub>R</sub> @ V <sub>RWM</sub> |    | V <sub>C</sub> @ I <sub>PP</sub> | I <sub>PP</sub>                 |              |           |
|                                   |           |                               | Min.                             | Max. |                | UNI                               | BI |                                  |                                 |              |           |
| UNI                               | BI        | V                             | V                                | V    | mA             | µA                                | µA | V                                | A                               | UNI          | BI        |
| 400W Transient Voltage Suppressor |           |                               |                                  |      |                |                                   |    |                                  |                                 |              |           |
| P4KE51A                           | P4KE51CA  | 43.6                          | 48.5                             | 53.6 | 1              | 1                                 | 1  | 70.1                             | 6                               | P4KE51A      | P4KE51CA  |
| P4KE56                            | P4KE56C   | 45.6                          | 50.4                             | 61.6 | 1              | 1                                 | 1  | 80.5                             | 5.2                             | P4KE56       | P4KE56C   |
| P4KE56A                           | P4KE56CA  | 47.8                          | 53.2                             | 58.8 | 1              | 1                                 | 1  | 77                               | 5.5                             | P4KE56A      | P4KE56CA  |
| P4KE62                            | P4KE62C   | 50.2                          | 55.8                             | 68.2 | 1              | 1                                 | 1  | 89                               | 4.7                             | P4KE62       | P4KE62C   |
| P4KE62A                           | P4KE62CA  | 53                            | 58.9                             | 65.1 | 1              | 1                                 | 1  | 85                               | 5                               | P4KE62A      | P4KE62CA  |
| P4KE68                            | P4KE68C   | 55.1                          | 61.2                             | 74.8 | 1              | 1                                 | 1  | 98                               | 4.3                             | P4KE68       | P4KE68C   |
| P4KE68A                           | P4KE68CA  | 58.1                          | 64.6                             | 71.4 | 1              | 1                                 | 1  | 92                               | 4.6                             | P4KE68A      | P4KE68CA  |
| P4KE75                            | P4KE75C   | 60.7                          | 67.5                             | 82.5 | 1              | 1                                 | 1  | 108                              | 3.9                             | P4KE75       | P4KE75C   |
| P4KE75A                           | P4KE75CA  | 64.1                          | 71.3                             | 78.8 | 1              | 1                                 | 1  | 103                              | 4.1                             | P4KE75A      | P4KE75CA  |
| P4KE82                            | P4KE82C   | 66.4                          | 73.8                             | 90.2 | 1              | 1                                 | 1  | 118                              | 3.6                             | P4KE82       | P4KE82C   |
| P4KE82A                           | P4KE82CA  | 70.1                          | 77.9                             | 86.1 | 1              | 1                                 | 1  | 113                              | 3.7                             | P4KE82A      | P4KE82CA  |
| P4KE91                            | P4KE91C   | 73.7                          | 81.9                             | 100  | 1              | 1                                 | 1  | 131                              | 3.2                             | P4KE91       | P4KE91C   |
| P4KE91A                           | P4KE91CA  | 77.8                          | 86.5                             | 95.5 | 1              | 1                                 | 1  | 125                              | 3.4                             | P4KE91A      | P4KE91CA  |
| P4KE100                           | P4KE100C  | 81                            | 90                               | 110  | 1              | 1                                 | 1  | 144                              | 2.9                             | P4KE100      | P4KE100C  |
| P4KE100A                          | P4KE100CA | 85.5                          | 95                               | 105  | 1              | 1                                 | 1  | 137                              | 3.1                             | P4KE100A     | P4KE100CA |
| P4KE110                           | P4KE110C  | 89.2                          | 99                               | 121  | 1              | 1                                 | 1  | 158                              | 2.7                             | P4KE110      | P4KE110C  |
| P4KE110A                          | P4KE110CA | 94                            | 105                              | 116  | 1              | 1                                 | 1  | 152                              | 2.8                             | P4KE110A     | P4KE110CA |
| P4KE120                           | P4KE120C  | 97.2                          | 108                              | 132  | 1              | 1                                 | 1  | 173                              | 2.4                             | P4KE120      | P4KE120C  |
| P4KE120A                          | P4KE120CA | 102                           | 114                              | 126  | 1              | 1                                 | 1  | 165                              | 2.5                             | P4KE120A     | P4KE120CA |
| P4KE130                           | P4KE130C  | 105                           | 117                              | 143  | 1              | 1                                 | 1  | 187                              | 2.2                             | P4KE130      | P4KE130C  |
| P4KE130A                          | P4KE130CA | 111                           | 124                              | 137  | 1              | 1                                 | 1  | 179                              | 2.3                             | P4KE130A     | P4KE130CA |
| P4KE150                           | P4KE150C  | 121                           | 135                              | 165  | 1              | 1                                 | 1  | 215                              | 2                               | P4KE150      | P4KE150C  |
| P4KE150A                          | P4KE150CA | 128                           | 143                              | 158  | 1              | 1                                 | 1  | 207                              | 2                               | P4KE150A     | P4KE150CA |
| P4KE160                           | P4KE160C  | 130                           | 144                              | 176  | 1              | 1                                 | 1  | 230                              | 1.8                             | P4KE160      | P4KE160C  |
| P4KE160A                          | P4KE160CA | 136                           | 152                              | 168  | 1              | 1                                 | 1  | 219                              | 1.9                             | P4KE160A     | P4KE160CA |
| P4KE170                           | P4KE170C  | 138                           | 153                              | 187  | 1              | 1                                 | 1  | 244                              | 1.7                             | P4KE170      | P4KE170C  |
| P4KE170A                          | P4KE170CA | 145                           | 162                              | 179  | 1              | 1                                 | 1  | 234                              | 1.8                             | P4KE170A     | P4KE170CA |
| P4KE180                           | P4KE180C  | 146                           | 162                              | 198  | 1              | 1                                 | 1  | 258                              | 1.6                             | P4KE180      | P4KE180C  |
| P4KE180A                          | P4KE180CA | 154                           | 171                              | 189  | 1              | 1                                 | 1  | 246                              | 1.7                             | P4KE180A     | P4KE180CA |
| P4KE200                           | P4KE200C  | 162                           | 180                              | 220  | 1              | 1                                 | 1  | 287                              | 1.5                             | P4KE200      | P4KE200C  |
| P4KE200A                          | P4KE200CA | 171                           | 190                              | 210  | 1              | 1                                 | 1  | 274                              | 1.5                             | P4KE200A     | P4KE200CA |
| P4KE220                           | P4KE220C  | 175                           | 198                              | 242  | 1              | 1                                 | 1  | 344                              | 1.2                             | P4KE220      | P4KE220C  |
| P4KE220A                          | P4KE220CA | 185                           | 209                              | 231  | 1              | 1                                 | 1  | 328                              | 1.2                             | P4KE220A     | P4KE220CA |
| P4KE250                           | P4KE250C  | 202                           | 225                              | 275  | 1              | 1                                 | 1  | 360                              | 1.1                             | P4KE250      | P4KE250C  |
| P4KE250A                          | P4KE250CA | 214                           | 237                              | 263  | 1              | 1                                 | 1  | 344                              | 1.2                             | P4KE250A     | P4KE250CA |
| P4KE300                           | P4KE300C  | 243                           | 270                              | 330  | 1              | 1                                 | 1  | 430                              | 0.9                             | P4KE300      | P4KE300C  |
| P4KE300A                          | P4KE300CA | 256                           | 285                              | 315  | 1              | 1                                 | 1  | 414                              | 1                               | P4KE300A     | P4KE300CA |
| P4KE350                           | P4KE350C  | 284                           | 315                              | 385  | 1              | 1                                 | 1  | 504                              | 0.8                             | P4KE350      | P4KE350C  |
| P4KE350A                          | P4KE350CA | 300                           | 332                              | 368  | 1              | 1                                 | 1  | 482                              | 0.8                             | P4KE350A     | P4KE350CA |
| P4KE400                           | P4KE400C  | 324                           | 360                              | 440  | 1              | 1                                 | 1  | 574                              | 0.7                             | P4KE400      | P4KE400C  |
| P4KE400A                          | P4KE400CA | 342                           | 380                              | 420  | 1              | 1                                 | 1  | 548                              | 0.7                             | P4KE400A     | P4KE400CA |
| P4KE440                           | P4KE440C  | 356                           | 396                              | 484  | 1              | 1                                 | 1  | 631                              | 0.7                             | P4KE440      | P4KE440C  |
| P4KE440A                          | P4KE440CA | 376                           | 418                              | 462  | 1              | 1                                 | 1  | 600                              | 0.7                             | P4KE440A     | P4KE440CA |


## P4KE SERIES




**Fig.1 PEAK PULSE POWER RATING PULSE TIME CURVE**




**Fig.2 PULSE DERATING CURVE**



**Fig.3 PULSE WAVEFORM**



**Fig.5 MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT**



**Fig.4 TYPICAL JUNCTION CAPACITANCE UNIDIRECTIONAL**

## P4KE SERIES

### Part No\_packing code\_Version

P4KE6.8\_AY\_00001

P4KE6.8\_AY\_10001

P4KE6.8\_B0\_00001

P4KE6.8\_B0\_10001

P4KE6.8\_R2\_00001

P4KE6.8\_R2\_10001

For example :

RB500V-40\_R2\_00001

Part No.

Serial number

Version code means HF

Packing size code means 13"

Packing type means T/R

| Packing Code XX                      |                      |                                  |                      | Version Code XXXXX |                      |                                       |
|--------------------------------------|----------------------|----------------------------------|----------------------|--------------------|----------------------|---------------------------------------|
| Packing type                         | 1 <sup>st</sup> Code | Packing size code                | 2 <sup>nd</sup> Code | HF or RoHS         | 1 <sup>st</sup> Code | 2 <sup>nd</sup> ~5 <sup>th</sup> Code |
| Tape and Ammunition Box (T/B)        | A                    | N/A                              | 0                    | HF                 | 0                    | serial number                         |
| Tape and Reel (T/R)                  | R                    | 7"                               | 1                    | RoHS               | 1                    | serial number                         |
| Bulk Packing (B/P)                   | B                    | 13"                              | 2                    |                    |                      |                                       |
| Tube Packing (T/P)                   | T                    | 26mm                             | X                    |                    |                      |                                       |
| Tape and Reel (Right Oriented) (TRR) | S                    | 52mm                             | Y                    |                    |                      |                                       |
| Tape and Reel (Left Oriented) (TRL)  | L                    | PANASERT T/B CATHODE UP (PBCU)   | U                    |                    |                      |                                       |
| FORMING                              | F                    | PANASERT T/B CATHODE DOWN (PBCD) | D                    |                    |                      |                                       |



## P4KE SERIES

---

### Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[P4KE39C\\_AY\\_10001](#) [P4KE39C\\_B0\\_00001](#) [P4KE39C\\_R2\\_00001](#) [P4KE39C\\_R2\\_10001](#) [P4KE39C\\_AY\\_00001](#)  
[P4KE39C\\_B0\\_10001](#)