

The miniature ECS-3225S is a miniature SMD HCMOS Tight Stability Crystal Oscillator. The 3.2 x 2.5 x 0.9 mm ceramic package is ideal for wireless and IOT application where stability is critical.

Request a Sample

### OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS



- Low Profile
- 3.2 x 2.5 mm Footprint
- Extended Temp Range
- RoHS Compliant

PARAMETERS	CONDITIONS	ECS-3225S			UNITS
		MIN	TYP	MAX	
Frequency Range		2.500		55.000	MHz
Frequency Stability *	EN (-40 ~ +85°C)			± 15	ppm
	FN (-40 ~ +85°C)			± 10	ppm
Power Supply	Vdd ±10%	+1.8, +2.5, +3.0, +3.3			V DC
Current Consumption				7	mA
Standby Current				10	µA
Output	HCMOS		15		pF
Output voltage Level	VOL:10%Vdd max./VOH:90%Vdd min.V DC				
Rise & Fall time	10%Vdd – 90%Vdd			5	ns
Startup Time				10	ms
Duty Cycle	@ ½ Vdd			45/55	%
Phase Noise	@ 10 KHz offset		-145		dBc/Hz
Operating Temp		-40		+85	°C
Storage Temp		-55		+125	°C

### DIMENSIONS (mm)





Figure 1) Top, Side, and Bottom views



PAD CONNECTIONS	
1	Tri-state
2	No Connect
3	Ground
4	Output
5	No Connect
6	Vdd

Tri State Function	
Pin 1	Output
High or NC	Active
Low	High Impedance




Figure 2) Suggested Land Pattern


### PART NUMBERING GUIDE: Example ECS-3225S33-250-FN-TR

ECS - SERIES	Voltage	FREQUENCY ABBREVIATION	STABILITY	TEMP RANGE	PACKAGING
3225S 3.2 x 2.5 mm	18 = +1.8V 25 = +2.5V 30 = +3.0V 33 = +3.3V	250 = 25.000 MHz See Developed Frequencies Pg.2	E = ±15 ppm F = ± 10 ppm	N = -40 ~ +85°C	TR = Tape & Reel 1K/Reel


**FREQUENCY ABBREVIATIONS**

FREQUENCY MHz	CODE
5.000	050
10.000	100
12.000	120
16.000	160
20.000	200
24.000	240
25.000	250
26.000	260
27.000	270
32.000	320
40.000	400
44.000	440
50.000	500

SOLDER PROFILE
Peak solder Temp +260°C Max 10 sec Max.
2 Cycles Max.
MSL 1, Lead Finish Au



**POCKET TAPE DIMENSIONS (mm)**



A	B	C	D	F	J	L	M	Reel Dia.	Qty/Reel
3.5	2.8	8.0	3.5	4.0	1.0	0.25	1.4	180	1000pcs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ECS:

[ECS-3250SS-270-3B-TR](#) [ECS-3250SS-400-3B-TR](#) [ECS-3250SS-540-3B-TR](#) [ECS-3225S33-050-FN-TR](#) [ECS-3225S33-100-FN-TR](#) [ECS-3225S33-120-FN-TR](#) [ECS-3225S33-160-FN-TR](#) [ECS-3225S33-200-FN-TR](#) [ECS-3225S33-240-FN-TR](#) [ECS-3225S18-440-EN-TR](#) [ECS-3225S18-500-EN-TR](#) [ECS-3225S18-240-EN-TR](#) [ECS-3225S18-250-EN-TR](#) [ECS-3225S18-260-EN-TR](#) [ECS-3225S18-270-EN-TR](#) [ECS-3225S18-320-EN-TR](#) [ECS-3225S18-40.000-EN-TR](#) [ECS-3225S25-500-EN-TR](#) [ECS-3225S18-050-EN-TR](#) [ECS-3225S18-100-EN-TR](#) [ECS-3225S18-120-EN-TR](#) [ECS-3225S18-160-EN-TR](#) [ECS-3225S18-200-EN-TR](#) [ECS-3225S25-250-EN-TR](#) [ECS-3225S25-260-EN-TR](#) [ECS-3225S25-270-EN-TR](#) [ECS-3225S25-320-EN-TR](#) [ECS-3225S25-40.000-EN-TR](#) [ECS-3225S25-440-EN-TR](#) [ECS-3225S25-050-EN-TR](#) [ECS-3225S25-100-EN-TR](#) [ECS-3225S25-120-EN-TR](#) [ECS-3225S25-160-EN-TR](#) [ECS-3225S25-200-EN-TR](#) [ECS-3225S25-240-EN-TR](#) [ECS-3225S30-260-EN-TR](#) [ECS-3225S30-270-EN-TR](#) [ECS-3225S30-320-EN-TR](#) [ECS-3225S30-40.000-EN-TR](#) [ECS-3225S30-440-EN-TR](#) [ECS-3225S30-500-EN-TR](#) [ECS-3225S30-100-EN-TR](#) [ECS-3225S30-120-EN-TR](#) [ECS-3225S30-160-EN-TR](#) [ECS-3225S30-200-EN-TR](#) [ECS-3225S30-240-EN-TR](#) [ECS-3225S30-250-EN-TR](#) [ECS-3225S33-270-EN-TR](#) [ECS-3225S33-320-EN-TR](#) [ECS-3225S33-40.000-EN-TR](#) [ECS-3225S33-440-EN-TR](#) [ECS-3225S33-500-EN-TR](#) [ECS-3225S30-050-EN-TR](#) [ECS-3225S33-120-EN-TR](#) [ECS-3225S33-160-EN-TR](#) [ECS-3225S33-200-EN-TR](#) [ECS-3225S33-240-EN-TR](#) [ECS-3225S33-250-EN-TR](#) [ECS-3225S33-260-EN-TR](#) [ECS-3225S18-320-FN-TR](#) [ECS-3225S18-40.000-FN-TR](#) [ECS-3225S18-440-FN-TR](#) [ECS-3225S18-500-FN-TR](#) [ECS-3225S33-050-EN-TR](#) [ECS-3225S33-100-EN-TR](#) [ECS-3225S18-160-FN-TR](#) [ECS-3225S18-200-FN-TR](#) [ECS-3225S18-240-FN-TR](#) [ECS-3225S18-250-FN-TR](#) [ECS-3225S18-260-FN-TR](#) [ECS-3225S18-270-FN-TR](#) [ECS-3225S25-40.000-FN-TR](#) [ECS-3225S25-440-FN-TR](#) [ECS-3225S25-500-FN-TR](#) [ECS-3225S18-050-FN-TR](#) [ECS-3225S18-100-FN-TR](#) [ECS-3225S18-120-FN-TR](#) [ECS-3225S25-200-FN-TR](#) [ECS-3225S25-240-FN-TR](#) [ECS-3225S25-250-FN-TR](#) [ECS-3225S25-260-FN-TR](#) [ECS-3225S25-270-FN-TR](#) [ECS-3225S25-320-FN-TR](#) [ECS-3225S30-440-FN-TR](#) [ECS-3225S30-500-FN-TR](#) [ECS-3225S25-050-FN-TR](#) [ECS-3225S25-100-FN-TR](#) [ECS-3225S25-120-FN-TR](#) [ECS-3225S25-160-FN-TR](#) [ECS-3225S30-240-FN-TR](#) [ECS-3225S30-250-FN-TR](#) [ECS-3225S30-260-FN-TR](#) [ECS-3225S30-270-FN-TR](#) [ECS-3225S30-320-FN-TR](#) [ECS-3225S30-40.000-FN-TR](#) [ECS-3225S33-500-FN-TR](#) [ECS-3225S30-050-FN-TR](#) [ECS-3225S30-100-FN-TR](#) [ECS-3225S30-120-FN-TR](#) [ECS-3225S30-160-FN-TR](#)