



MATERIALS:

Screws: 2 ea. #2-56 x 3/16" Pan Head, Steel

Cover: Phenolic Plate. Color: Black

Molded Housing: Electrical grade Phenolic. Color: Black

Marking: POMONA ELECTRONICS CALIF.

RATINGS):

Operating Temperature: +150°C. (+302°F.) Max.

ORDERING INFORMATION: Model 2105

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2105](#)