



FEATURES:

- Accepts .080 pin tip plugs
- Mounts in panels up to .250" thick.

MATERIAL:

Insulation – Polycarbonate - Molded to pin tip jack body
 Lockwasher, #8 Internal Tooth – Steel - Nickel plated
 Hex Nut, #8-32 – Brass – Nickel plated
 Pin Tip Jack Body: Brass – Gold plated

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.
 Operating Voltage: 1500 VDC
 Current: 5 Amperes.

ORDERING INFORMATION: Model 3542-*

*=Color Code – See Tabulation Block
 Sold in packages of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
 Technical Assistance: 800-241-2060

PomonaACCESS 90193 (800) 444-6785 or (425) 446-6010
 More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3542-8](#) [3542-1](#) [3542-7](#)