



FEATURES:

- Meets requirements of MIL-P-55149/1A.

MATERIALS:

Binding Post Body, Nuts, Lockwasher: Gold Plated Brass
 Insulation: Nylon MIL-P-20693
 Flat Washer: Brass
 Insulator: Nylon
 Hex Nut: Steel

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.
 Hands free testing in controlled voltage environments: 1500 VRMS
 Operating Temperature: +80°C (+176°F) Max.
 Current: 30 Amperes

ORDERING INFORMATION: Model 5018-*
 *=Color, -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
 Ordering Example: 5018-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Pomona[®]

Model 5018
Hex Head Binding Post

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

6/9/99

SY/EH/LS

T:\Release\DataSheets\FlukeDataSheet's5018_1_01.doc

Sales: 909-469-2900 Fax: 909-629-3317
Technical Assistance: 800-241-2060

PomonaACCESS 90294 (800) 444-6785 or (949) 253-3858
More drawings available at www.pomonaelectronics.com

Page 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5018-0](#) [5018-4](#) [5018-5](#) [5018-6](#) [5018-9](#) [5018-2](#)