




STANDARD WECO/BNC ADAPTER (4X MODEL 5008)



MINI WECO/BNC ADAPTER (4X MODEL 6519)



TRUE 75 BNC CABLE, RED (MODEL 6510-V-72-2)



TRUE 75 BNC CABLE, BLUE (MODEL 6510-V-72-6)

### FEATURES:

- Test, monitor, patch and cross connect DSX-3 signals in the central office and outside plant
- Adapters quickly convert BNC cables to Mini-Weco or Standard Weco (.090 diameter pin) interfaces
- Kit reduces the need for multiple cables to service DSX-3 panels
- Includes a 9 1/4" (L) x 6" (W) x 2 1/4" (D) Cordura shoulder carrying case with multiple zippered pockets for convenient accessory storage

### MATERIALS:

BNC, Mini-Weco & Standard Weco connectors

Bodies: Brass, nickel plated

Center Contacts: Brass, gold plated, BNC (F) Beryllium Copper, gold plated

Insulators: PTFE

Cable: Hi flex, RG59 type,

Color: Red (Receive), Blue (Transmit)

### ORDERING INFORMATION: Model 6568

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90939 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6568](#)