



Quality Products. Service Excellence.

## Steel Rack Panels *PBPS Series*

Also referred to as a Spacer Blank Panel

### Features:



- Constructed of 14-gauge steel.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Please be advised that the RAL9005 Semi-Gloss Black will be phased out effective January 3, 2025. The replacement is the RAL9005 Matte Black.

### Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel



Part No. RAL9005 Semi-Gloss Black	Part No. RAL9005 Matte Black	Part No. ANSI61 Dark Gray	Part No. RAL7035 Light Gray	Part No. RAL9003 Matte White	Panel Height		Qty of Mounting Points
					Rack Units	Panel Height	
PBPS19001BK2	PBPS19001BK	PBPS19001GY2	PBPS19001LG2	PBPS19001WH	1U	1.75	4
PBPS19003BK2	PBPS19003BK	PBPS19003GY2	PBPS19003LG2	PBPS19003WH	2U	3.50	4
PBPS19005BK2	PBPS19005BK	PBPS19005GY2	PBPS19005LG2	PBPS19005WH	3U	5.25	4
PBPS19007BK2	PBPS19007BK	PBPS19007GY2	PBPS19007LG2	PBPS19007WH	4U	7.00	4
PBPS19008BK2	PBPS19008BK	PBPS19008GY2	PBPS19008LG2	PBPS19008WH	5U	8.75	4
PBPS19010BK2	PBPS19010BK	PBPS19010GY2	PBPS19010LG2	PBPS19010WH	6U	10.50	8
PBPS19012BK2	PBPS19012BK	PBPS19012GY2	PBPS19012LG2	PBPS19012WH	7U	12.25	8
PBPS19014BK2	PBPS19014BK	PBPS19014GY2	PBPS19014LG2	PBPS19014WH	8U	14.00	8
PBPS19015BK2	PBPS19015BK	PBPS19015GY2	PBPS19015LG2	PBPS19015WH	9U	15.75	8
PBPS19017BK2	PBPS19017BK	PBPS19017GY2	PBPS19017LG2	PBPS19017WH	10U	17.50	8

Tags: Steel Flat Panel, Rack Blank, Blank Panel

Data subject to change without notice



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Hammond:

[PBPS19005BK2](#) [PBPS19017GY2](#) [PBPS19012BK2](#) [PBPS19003BK2](#) [PBPS19022GY2](#) [PBPS19022BK2](#)  
[PBPS19015GY2](#) [PBPS19007GY2](#) [PBPS19019GY2](#) [PBPS19028BK2](#) [PBPS19014GY2](#) [PBPS19031GY2](#)  
[PBPS19017BK2](#) [PBPS19015BK2](#) [PBPS19024GY2](#) [PBPS19026GY2](#) [PBPS19001GY2](#) [PBPS19008GY2](#)  
[PBPS19010BK2](#) [PBPS19019BK2](#) [PBPS19010GY2](#) [PBPS19021GY2](#) [PBPS19029GY2](#) [PBPS19021BK2](#)  
[PBPS19028GY2](#) [PBPS19008BK2](#) [PBPS19026BK2](#) [PBPS19005GY2](#) [PBPS19029BK2](#) [PBPS19031BK2](#)  
[PBPS19014BK2](#) [PBPS19001BK2](#) [PBPS19024BK2](#) [PBPS19003GY2](#) [PBPS19007BK2](#) [PBPS19012GY2](#)  
[PBPS19001LG2](#) [PBPS19007LG2](#) [PBPS19012LG2](#) [PBPS19021LG2](#) [PBPS19031LG2](#) [PBPS19003LG2](#)  
[PBPS19005LG2](#) [PBPS19008LG2](#) [PBPS19010LG2](#) [PBPS19015LG2](#) [PBPS19019LG2](#) [PBPS19024LG2](#)  
[PBPS19029LG2](#) [PBPS19014LG2](#) [PBPS19022LG2](#) [PBPS19028LG2](#) [PBPS19017LG2](#) [PBPS19001BK](#)  
[PBPS19003BK](#) [PBPS19005BK](#) [PBPS19007BK](#) [PBPS19001WH](#) [PBPS19003WH](#) [PBPS19005WH](#) [PBPS19007WH](#)  
[PBPS19008WH](#) [PBPS19010WH](#) [PBPS19012WH](#) [PBPS19014WH](#) [PBPS19015WH](#) [PBPS19017WH](#) [PBPS19019WH](#)  
[PBPS19021WH](#) [PBPS19022WH](#) [PBPS19024WH](#) [PBPS19026WH](#) [PBPS19028WH](#) [PBPS19029WH](#)  
[PBPS19031WH](#) [PBPS19026LG2](#) [PBPS19008BK](#) [PBPS19010BK](#) [PBPS19012BK](#) [PBPS19014BK](#) [PBPS19015BK](#)  
[PBPS19017BK](#)