




Quality Products. Service Excellence.

## Equipment Rack Cabinet *REFK Series*

Load rated to 1,000 lbs (454 kg)



This product is manufactured within North America and is Tariff-Free.

### Features

- C-channel struts provide cabinet strength, ease, and flexibility to adjust mounting rails.
- Solid non-removable side panels.
- Optional flush-mounted doors with quarter-turn locks can be mounted to swing on either side.
- Self-squaring design ships un-assembled (some assembly required).
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom.

### Specifications

- The cabinet frame is constructed in 16-gauge steel.
- Includes two (2) pairs of adjustable depth 10-32 threaded EIA-compliant **combination rails**. Constructed in 10-gauge steel, include rack unit indicators, and are Zinc-plated to provide superior surface areas for equipment grounding.
- Includes four (4) leveling feet.
- Removable gland plate - over 10" (254 mm) long x 1.5" (38 mm) high opening - with knockouts on the rear bottom of the rack for easy cable access.
- 1,000 lbs (454 kg) **static load rating**.
- Finished in textured RAL 9005 black or RAL 7035 light gray powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases. BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

### Accessories

- Rack Shelves
- We Manufacture PDUs and Outlet Strips
- Horizontal Lacing Strip
- Cable Management Arm
- Bonding and Grounding
- Mounting Rack Rails
- Rack and Cabinet Caster Set
- Rack Shelf Slide Block
- 10-32 Mounting Hardware
- Adjustable Depth Front-To-Rear Cable Manager
- Horizontal Steel Finger Cable Manager
- Rack Panels
- Ground Stud Kit
- Square Hole Punched Mounting Rail
- Rack Equipment Installation Tool

### REFK Active Sizes

| Part No.<br>RAL 9005<br>Black | Part No.<br>RAL 7035<br>Light Gray | Overall Dimensions |       |       | Rack<br>Units | Usable Mounting Dimensions |       |                       |
|-------------------------------|------------------------------------|--------------------|-------|-------|---------------|----------------------------|-------|-----------------------|
|                               |                                    | Height             | Width | Depth |               | Height                     | Depth | Depth<br>(With Doors) |
| REFK1903524BK1                | REFK1903524LG1                     | 40.19              | 21.34 | 24.50 | 20U           | 35.19                      | 23.50 | 23.00                 |
| REFK1904224BK1                | REFK1904224LG1                     | 47.19              | 21.34 | 24.50 | 24U           | 42.19                      | 23.50 | 23.00                 |
| REFK1905624BK1                | REFK1905624LG1                     | 61.19              | 21.34 | 24.50 | 32U           | 56.19                      | 23.50 | 23.00                 |
| REFK1906324BK1                | REFK1906324LG1                     | 68.19              | 21.34 | 24.50 | 36U           | 63.19                      | 23.50 | 23.00                 |
| REFK1907024BK1                | REFK1907024LG1                     | 75.19              | 21.34 | 24.50 | 40U           | 70.19                      | 23.50 | 23.00                 |
| REFK1903531BK1                | REFK1903531LG1                     | 40.19              | 21.34 | 31.50 | 20U           | 35.19                      | 28.50 | 28.00                 |
| REFK1904231BK1                | REFK1904231LG1                     | 47.19              | 21.34 | 31.50 | 24U           | 42.19                      | 28.50 | 28.00                 |
| REFK1906331BK1                | REFK1906331LG1                     | 68.19              | 21.34 | 31.50 | 36U           | 63.19                      | 28.50 | 28.00                 |
| REFK1907031BK1                | REFK1907031LG1                     | 75.19              | 21.34 | 31.50 | 40U           | 70.19                      | 28.50 | 28.00                 |

## REFK Clearance

| Part No.<br>RAL 9005<br>Black | Qty | Overall Dimensions |       |       | Rack<br>Units | Usable Mounting Dimensions |       |                       |
|-------------------------------|-----|--------------------|-------|-------|---------------|----------------------------|-------|-----------------------|
|                               |     | Height             | Width | Depth |               | Height                     | Depth | Depth<br>(With Doors) |
| REFK1903517BK1                | 2   | 40.19              | 21.34 | 17.50 | 20U           | 35.19                      | 16.50 | 16.00                 |
| REFK1907717BK1                | 4   | 82.19              | 21.34 | 17.50 | 44U           | 77.19                      | 16.50 | 16.00                 |

As of Feb 24, 2025

## REFK Locking Doors

| Solid Door<br>Part No.<br>Black | Solid Door<br>Part No.<br>RAL 7035 Light Gray | Louvered Door<br>Part No.<br>Black | Louvered Door<br>Part No.<br>RAL 7035 Light Gray | Window Door<br>Part No.<br>Black | Use With REFK Frame |          |             |
|---------------------------------|---|------------------------------------|--|----------------------------------|---------------------|----------|-------------|
|                                 |   |                                    |  | Height                           | Rack Units          | Part No. |             |
| RSDF19035BK1                    | RSDF19035LG1                                  | RSDL19035BK1                       | RSDL19035LG1                                     | REDFP19035BK1                    | 35.00               | 20U      | REFK19035XX |
| RSDF19042BK1                    | RSDF19042LG1                                  | RSDL19042BK1                       | RSDL19042LG1                                     | REDFP19042BK1                    | 42.00               | 24U      | REFK19042XX |
| RSDF19049BK1                    | RSDF19049LG1                                  | RSDL19049BK1                       | RSDL19049LG1                                     | REDFP19049BK1                    | 49.00               | 28U      | REFK19049XX |
| RSDF19056BK1                    | RSDF19056LG1                                  | RSDL19056BK1                       | RSDL19056LG1                                     | REDFP19056BK1                    | 56.00               | 32U      | REFK19056XX |
| RSDF19063BK1                    | RSDF19063LG1                                  | RSDL19063BK1                       | RSDL19063LG1                                     | REDFP19063BK1                    | 63.00               | 36U      | REFK19063XX |
| RSDF19070BK1                    | RSDF19070LG1                                  | RSDL19070BK1                       | RSDL19070LG1                                     | REDFP19070BK1                    | 70.00               | 40U      | REFK19070XX |
| -                               | -   | RSDL19077BK1                       | RSDL19077LG1                                     | -                                | 77.00               | 44U      | REFK19077XX |

Tags: knock-down, knock down

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[REFK1905617BK1](#) [REFK1907724BK1](#) [REFK1906331CG1](#) [REFK1904217CG1](#) [REFK1904924BK1](#)  
[REFK1904217BK1](#) [REFK1905631CG1](#) [REFK1904917BK1](#) [REFK1907024BK1](#) [REFK1906317CG1](#)  
[REFK1907017BK1](#) [REFK1903517BK1](#) [REFK1903524BK1](#) [REFK1904231BK1](#) [RSDF19022CG1](#) [REFK1907717BK1](#)  
[REFK1903531BK1](#) [REFK1905624BK1](#) [REFK1903531CG1](#) [REFK1907031BK1](#) [REFK1906317BK1](#)  
[REFK1904224BK1](#) [REFK1907731BK1](#) [REFK1906331BK1](#) [REFK1905631BK1](#) [REFK1906324BK1](#)  
[REFK1904931BK1](#) [REFK1907017CG1](#) [REFK1903524LG1](#) [REFK1904224LG1](#) [REFK1904924LG1](#)  
[REFK1905624LG1](#) [REFK1906324LG1](#) [REFK1907024LG1](#) [REFK1907724LG1](#) [REFK1904931LG1](#)  
[REFK1904217LG1](#) [REFK1904231LG1](#) [REFK1903517LG1](#) [REFK1903531LG1](#) [REFK1906317LG1](#)  
[REFK1907031LG1](#) [REFK1904917LG1](#) [REFK1905617LG1](#) [REFK1905631LG1](#) [REFK1906331LG1](#)  
[REFK1907017LG1](#) [REFK1907717LG1](#) [REFK1907731LG1](#)