

Han 4HC-Halterung




Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 9954
Specification	Han 4HC-Halterung
HARTING eCatalogue	https://b2b.harting.com/09110009954

Identification

Category	Accessories
Series of hoods/housings	Han [®] M
Type of accessory	Frame
Description of the accessory	for male inserts for female inserts 4x HC 350 contacts + 2x Han [®] Q 5/0 in a hood

Version

Size	48 B
------	------

Technical characteristics

Tightening torque	0.5 Nm Fixing screws M3 0.25 Nm Fixing screws Han [®] Q 5/0 1.5 Nm Cross-tying screws
-------------------	--

Material properties

Material (accessories)	Metal
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Commercial data

Packaging size	1
Net weight	77.1 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440210 Fixing element for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09110009954](#)