

## Han Q 2/0-f HV 1.5sqmm



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 002 2756
Specification	Han Q 2/0-f HV 1.5sqmm
HARTING eCatalogue	<a href="https://b2b.harting.com/09120022756">https://b2b.harting.com/09120022756</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> Q
Identification	2/0 High Voltage

### Version

Termination method	Axial screw termination
Gender	Female
Size	3 A
Number of contacts	2
PE contact	Yes
Pack contents	With heat shrink tube

### Technical characteristics

Conductor cross-section	1.5 ... 2.5 mm <sup>2</sup>
Rated current	40 A
Rated voltage	830 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤1 mΩ
Limiting temperature	-40 ... +125 °C



Pushing Performance

## Technical characteristics

Tightening torque	1.8 Nm
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	26.2 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09120022756](#)