

## Han RJ45 module, female gender changer




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 4721
Specification	Han RJ45 module, female gender changer
HARTING eCatalogue	<a href="https://b2b.harting.com/09140014721">https://b2b.harting.com/09140014721</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® RJ45 module
Description of the module	Gender changer for patch cable

### Version

Gender	Female
Number of contacts	8

### Technical characteristics

Rated current	1 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +70 °C
Mating cycles	$\geq 500$
Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz



Pushing Performance

## Material properties

Material (insert)	Polycarbonate (PC) Zinc die-cast, nickel-plated
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	1
Net weight	22.8 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140014721](#)