

## Han E F Crimp Contact Ag 0.5 mm<sup>2</sup>/ 20 AWG




Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6220
Specification	Han E F Crimp Contact Ag 0.5 mm <sup>2</sup> / 20 AWG
HARTING eCatalogue	<a href="https://b2b.harting.com/09330006220">https://b2b.harting.com/09330006220</a>

### Identification

Category	Contacts
Series	Han E <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
Contact identification	No groove
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.5 mm <sup>2</sup>
Conductor cross-section	AWG 20
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	100
Net weight	1.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09330006220](#)