

Han3A RJ45 Hybrid Cat5 PFT 8+4p plastic




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 225 1300
Specification	Han3A RJ45 Hybrid Cat5 PFT 8+4p plastic
HARTING eCatalogue	https://b2b.harting.com/09452251300

Identification

Category	Connectors
Series	RJ45 Hybrid
Element	Panel feed through
Specification	Straight

Version

Size	Han [®] 3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Additional contacts	4x 48 V

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
RoHS	compliant
ELV status	compliant



Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	44.5 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452251300](#)