




Profibus Kabel CU Hybrid  
 4x 1,5mm<sup>2</sup>  
 2x 0,3mm<sup>2</sup> verdrillt und geschirmt/  
*twisted and screened*



Belegungsplan/  
*cable assign:*



|                |       |
|----------------|-------|
| 20 88 651 0300 | 30,00 |
| 20 88 651 0150 | 15,00 |
| 20 88 651 0100 | 10,00 |
| 20 88 651 0050 | 5,00  |
| 20 88 651 0030 | 3,00  |
| 20 88 651 0015 | 1,50  |
| Art.-Nr.       | L /m  |

|   |                                |          |   |  |  |
|---|--------------------------------|----------|---|--|--|
| All Dimensions in mm<br>Original Size DIN A 4 | Techn. Character.              |          |   | Nicht tolerierte Masse/ Free size tolerances                     |  |
|   |                                | Dat.     | Name  | Massstab/Scale   |  |
|   | Detail.                        | 25.02.05 | Ste   | 1:1  |  |
|   | Insp.                          |          | Be  |  |  |
|   | Stand.                         |          |   |  |  |
| 411464  | HARTING Electric GmbH & Co. KG |          |   | TB 20 88 651 0... <span style="float: right;">Blatt/ page</span> |  |
| Mod.  | Dat.                           | Name     | D-32339 Espelkamp                                  Sub. |  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20886510015](#) [20886510030](#) [20886510050](#) [20886510100](#) [20886510150](#) [20886510300](#)