



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:
HOUSING: THERMOPLASTIC; COLOR: SEE CHART
CONTACT: COPPER ALLOY
2. MODIFICATIONS: PCB MOUNT
3. SPECIFICATIONS:
 - 3.1 CURRENT RATING: 13 AMPS
 - 3.2 OPERATING TEMPERATURE: -55°C TO +125°C
 - 3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
 - 3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
 - 3.6 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.7 RoHS COMPLIANT
4. MATING PART: AT06-4S* PLUG (* = MODIFICATIONS AND COLORS)
5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
6. POTTED CONNECTORS SPECIFIED FOR UP TO 5 P.S.I. APPLICATIONS.

AT04-4P-BMXX VARIANTS			
CONTACT PLATING	POTTING OR NOT IN RESERVOIR	COLOR	PART NUMBER
GOLD	NO POTTING	BLACK	AT04-4P-BM01
GOLD	POTTING	BLACK	AT04-4P-BM02
NICKEL	NO POTTING	BLACK	AT04-4P-BM03
NICKEL	POTTING	BLACK	AT04-4P-BM04
GOLD	NO POTTING	RED	AT04-4P-BM01RED
GOLD	POTTING	RED	AT04-4P-BM02RED
NICKEL	NO POTTING	RED	AT04-4P-BM03RED
NICKEL	POTTING	RED	AT04-4P-BM04RED
GOLD	NO POTTING	GREEN	AT04-4P-BM01GRN
GOLD	POTTING	GREEN	AT04-4P-BM02GRN
NICKEL	NO POTTING	GREEN	AT04-4P-BM03GRN
NICKEL	POTTING	GREEN	AT04-4P-BM04GRN

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE NEW PRODUCT	10AUG15	ORION	TOMMY
A2	-	ADDED RED AND GREEN COLORS	5DEC2019	JAH	DH
A3	-	REVISE DRAWING	10JUL20	JHEAD	DH

SEE PART NUMBER CHART				
PART NUMBER		DESCRIPTION		
QUANTITY	MATERIALS LIST			ITEM
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE
1) All dimensions are in metric (mm).		DRAWN: ORION LI		10AUG15
2) Tolerances are as follows:		CHECKED:		
1 PL DEC ±0.30 Fractions ±1/64		ENGINEER:		
2 PL DEC ±0.15 Angles ±1°		APPROVAL: TOMMY XIE		10AUG15
3 PL DEC ±0.08		CUSTOMER:		
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
PROCESS SPECIFICATIONS:		SCALE: NONE		
NEXT ASSY:		SIZE: B C-		DWG NO: AT04-4P-BMXX
		REVISION: A3		
		SHEET 1 OF 1		

TITLE: PCB MOUNT RECEPTACLE, PIN STRAIGHT, A SERIES
DWG NO: AT04-4P-BMXX
REV: A3
SH: 1
OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AT04-4P-BM03](#) [AT04-4P-BM01](#) [AT04-4P-BM02](#) [AT04-4P-BM04](#)