

“Stay Connected” with



HEYware Products


a PennEngineering® Company



HEYClip™ Nylon Push Screws

| Threaded Mounting Hole | PART NO. | | DESCRIPTION | PART DIMENSIONS | | | | | | | | | |
|------------------------|----------|--------|------------------|-----------------|-----|------------------|------|-----------------|------|--------------------|----|---------------------|-----|
| | Natural | Black | | A Head Height | | B Overall Length | | C Head Diameter | | Push In Force Max. | | Pull Out Force Min. | |
| | | | | in. | mm. | in. | mm. | in. | mm. | LB | N | LB | N |
| M3 | 11500 | 11500B | PS-M3X0.5X8.5MM | .10 | 2,5 | .33 | 8,5 | .22 | 5,5 | 7 | 30 | 11 | 50 |
| M4 | 11501 | 11501B | PS-M4X0.5X9.5MM | .12 | 3,0 | .37 | 9,5 | .29 | 7,3 | 8 | 35 | 20 | 90 |
| M5 | 11502 | 11502B | PS-M5X0.5X12.5MM | .14 | 3,5 | .49 | 12,5 | .33 | 8,5 | 8 | 35 | 22 | 100 |
| M6 | 11503 | 11503B | PS-M6X0.5X15.0MM | .18 | 4,5 | .59 | 15,0 | .39 | 10,0 | 8 | 35 | 27 | 120 |
| M8 | 11504 | 11504B | PS-M8X0.5X18.0MM | .22 | 5,5 | .71 | 18,0 | .51 | 13,0 | 9 | 40 | 31 | 140 |


- Installs like a traditional nylon push rivet but removable/reusable
- Remove by unscrewing like a traditional threaded fastener
- Saves time by installing with finger-tip pressure
- Low insertion force but high extraction force



HEYClip™ Barbed Push Fasteners

| WLL FIT THESE PANELS | | | | PART NO. | DESCRIPTION | PART DIMENSIONS | | | | | | | |
|----------------------|-----|---------------------------|-----|----------|-------------|-----------------|------------------------|-----|---------------|-----|-----------------|-----|------|
| MOUNTING HOLE DIA. | | ASSEMBLED PANEL THICKNESS | | | | Black | A Length | | B Head Height | | C Head Diameter | | |
| in. | mm. | in. | mm. | in. | mm. | | in. | mm. | in. | mm. | in. | mm. | |
| .157 | 4,0 | .08 | 2,1 | .17 | 4,3 | 11530 | HBPF 157-339-315 BLACK | .34 | 8,6 | .04 | 1,0 | .31 | 8,0 |
| | | .08 | 2,1 | .28 | 7,2 | 11531 | HBPF 157-437-315 BLACK | .44 | 11,1 | | | | |
| | | .22 | 5,7 | .42 | 10,7 | 11532 | HBPF 157-591-315 BLACK | .59 | 15,0 | | | | |
| | | .08 | 2,1 | .17 | 4,3 | 11533 | HBPF 157-339-472 BLACK | .34 | 8,6 | .06 | 1,5 | .47 | 12,0 |
| | | .08 | 2,1 | .28 | 7,2 | 11534 | HBPF 157-437-472 BLACK | .44 | 11,1 | | | | |
| | | .22 | 5,7 | .42 | 10,7 | 11535 | HBPF 157-591-472 BLACK | .59 | 15,0 | | | | |
| .187 | 4,8 | .08 | 2,1 | .17 | 4,3 | 11536 | HBPF 187-339-315 BLACK | .34 | 8,6 | .04 | 1,0 | .31 | 8,0 |
| | | .08 | 2,1 | .28 | 7,2 | 11537 | HBPF 187-437-315 BLACK | .44 | 11,1 | | | | |
| | | .22 | 5,7 | .42 | 10,7 | 11538 | HBPF 187-591-315 BLACK | .59 | 15,0 | | | | |
| .250 | 6,4 | .08 | 2,1 | .17 | 4,3 | 11539 | HBPF 250-339-472 BLACK | .34 | 8,6 | .06 | 1,5 | .47 | 12,0 |
| | | .08 | 2,1 | .28 | 7,2 | 11540 | HBPF 250-437-472 BLACK | .44 | 11,1 | | | | |
| | | .22 | 5,7 | .42 | 10,7 | 11541 | HBPF 250-591-472 BLACK | .59 | 15,0 | | | | |


- Saves time by installing with finger-tip pressure – no tools required!
- Low insertion force but high extraction force



HEYClip™ Fastener Plug

| WILL FIT THESE PANELS | | | | PART NO. | DESCRIPTION | PART DIMENSIONS | | | | | |
|-----------------------|-----|--------------------------------|-----|----------|-------------|-----------------|----------|-----|---------------|-----|-----------------|
| MOUNTING HOLE DIA. | | MAX. ASSEMBLED PANEL THICKNESS | | | | Black | A Length | | B Head Height | | C Head Diameter |
| in. | mm. | in. | mm. | in. | mm. | | in. | mm. | in. | mm. | in. |
| .150 | 3,8 | .311 | 7,9 | 9001 | FP 150-311 | .45 | 11,5 | .07 | 1,8 | .31 | 8,0 |

Standard color black. For other colors consult Heyco.



| | PS & HBPF | FP |
|---------------------|-------------------------------|-------------------------------|
| Material | Nylon 6/6 | Acetal (POM) |
| Flammability Rating | 94V-2 | 94-HB |
| Temperature Range | -40°F (-40°C) to 185°F (85°C) | -4°F (-18°C) to 220°F (104°C) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[9001](#) [11500](#) [11500B](#) [11501](#) [11501B](#) [11502](#) [11502B](#) [11538](#) [11539](#) [11540](#) [11541](#) [11532](#) [11533](#) [11534](#) [11535](#)
[11536](#) [11537](#) [11503](#) [11503B](#) [11504](#) [11504B](#) [11530](#) [11531](#)