




Heyco® Snap Bushings

Mounting Hole Diameter Range: 1.000" (25,4 mm) to 6.0" (152,4 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
in.	mm.	Black	White		A Inside Diameter		B Head Diameter		C Overall Height	
					in.	mm.	in.	mm.	in.	mm.
Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)										
1.000	25,4	2140	2141	SB 1000-12	.766	19,4	1.125	28,6	.453	11,5
1.093 - 1.125	27,8 - 28,6	2160	2161	SB 1093-13	.812	20,6	1.218	30,9	.453	11,5
		2163	2164	SB 1093-14	.875	22,2				
		2166	2167	SB 1093-15	.937	23,8				
1.187	30,2	2182	2183	SB 1187-15	.937	23,8	1.312	33,3	.453	11,5
1.250	31,8	2198	2199	SB 1250-15	.937	23,8	1.359	34,5	.453	11,5
		2201	2202	SB 1250-16	1.000	25,4				
1.375	34,9	2207	2208	SB 1375-14	.875	22,2	1.490	37,3	.453	11,5
		2210	2211	SB 1375-16	1.014	25,8				
		2233	2234	SB 1500-17	1.062	27,0				
1.500	38,1	2236	2237	SB 1500-18	1.125	28,6	1.609	40,9	.453	11,5
		2240	2241	SB 1500-21	1.312	33,3				
		2300	2301	SB 1750-22	1.375	34,9				
1.750	44,5	2400	2401	SB 2000-26	1.640	41,6	2.125	54,0	.453	11,5
		2406	2414	SB 2000-28	1.750	44,5				
Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)										
2.093	53,1	2415	2416	SB 2.093-29	1.813	46,0	2.350	59,7	.720	18,3
2.250	57,2	2417	2418	SB 2.250-29	1.860	47,1	2.480	63,1		
2.500	63,5	2420	2421	SB 2.500-31	1.970	50,0	2.660	67,5		
3.000	76,2	2461	2462	SB 3.000-39	2.470	62,7	3.150	80,0	.750	19,1
		2424	2425	SB 3.000-44	2.750	69,9	3.160	80,2	.720	18,3
3.375	85,7	2407	2408	SB 3.375-45	2.812	71,4	3.660	93,0	.720	18,3
3.500	88,9	2470	2471	SB 3.500-47	2.940	74,7				
4.000	101,6	2479	2480	SB 4.000-55	3.470	88,1	4.150	105,4	.740	18,8
5.000	127,0	2409	2410	SB 5.000-70	4.375	113,8	5.219	132,6		
6.000	152,4	2484	2485	SB 6.000-86	5.375	139,2	6.219	157,9		

- Converts raw-edged holes to smooth, neat, insulated holes.
- Insulates and mechanically protects electrical and telecommunications cables, tubing, hose, rope, and utility lines.
- Locking fingers snap into holes with fingertip pressure.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Withstands a push back force of 35 pounds.
- Available in multiple sizes for use in .250" (6,4 mm) to 6.00" (152,4 mm) diameter holes.
- We offer the following brass-colored parts for lamp and lighting applications:
Part No. 2012, SB 312-3 Brass
Part No. 2033, SB 375-4 Brass
Part No. 2041, SB 437-4 Brass

Standard colors black and white. Consult Heyco for other colors.



Material Nylon 6/6
 Certifications Recognized under the Component Program of Underwriters' Laboratories, File E15331
 Certified by Canadian Standards Association, File 8919
 Flammability Rating 94V-2
 Material Temperature Index 257°F (125°C)–Maximum temperature on part not to exceed 221°F (105°C)

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[2300](#) [2198](#) [2182](#) [2140](#) [2166](#) [2160](#) [2163](#) [2240](#) [2201](#) [2210](#) [2236](#) [2164](#) [2400](#) [2406](#) [2461](#) [2417](#) [2470](#) [2479](#)
[2161](#) [2167](#) [2199](#) [2207](#) [2208](#) [2233](#) [2234](#) [2237](#) [2401](#) [2409](#) [2415](#) [2241](#) [2416](#) [2471](#) [2424](#) [2484](#) [2301](#) [2211](#)
[2462](#) [2141](#) [2421](#) [2407](#) [2408](#) [2410](#) [2183](#) [2418](#) [2485](#) [2414](#) [2202](#) [2425](#) [2480](#)