

“Stay Connected” with



HEYware Products

a PennEngineering® Company



- Push mount design allows for fast installation.
- Releasable and reusable wire clip.
- Bayonet design allows from .02” (0,5 mm) panel thickness to .15” (3,8 mm).
- Bayonet snap locks into a .250” (6,3 mm) hole and will hold a 25 pound continuous load or a 50 pound impact load.
- Multiple sizes available for bundles from .19” (4,7 mm) to 1.00” (25,4 mm).



HEYClip™ Locking Releasable Wire Clips - Arrowhead Mount

| MAXIMUM BUNDLE DIAMETER | PART NO. | | DESCRIPTION | FOOTPRINT | | OVERALL HEIGHT | | CLAMP WIDTH | | MOUNTING HOLE DIA. | |
|-------------------------|----------|-------|-------------|-----------|---|----------------|-----|-------------|-----|--------------------|--|
| | Gray | Black | | A x B | C | D | in. | mm. | in. | mm. | |

| PMWC Series For Panels .02” (0,5 mm) to .08” (2,0 mm) thick | | | | | | | | | | | | |
|---|------|------|------|--------------|-------------|-------------|------|------|-----|------|------|-----|
| .19 | 4,7 | 3845 | 3870 | PMWC 187-20 | .54 x 1.01 | 13,7 x 25,7 | .39 | 9,9 | .38 | 9,7 | .250 | 6,4 |
| .25 | 6,4 | 3846 | 3871 | PMWC 250-20 | .58 x 1.01 | 14,7 x 25,7 | .45 | 11,4 | .41 | 10,4 | | |
| .38 | 9,5 | 3847 | 3872 | PMWC 375-20 | .65 x 1.01 | 16,5 x 25,7 | .53 | 13,5 | .50 | 12,7 | | |
| .50 | 12,7 | 3848 | 3906 | PMWC 500-20 | .75 x 1.20 | 19,1 x 30,5 | .73 | 18,5 | .59 | 15,0 | | |
| .75 | 19,1 | 3849 | 3908 | PMWC 750-20 | .88 x 1.38 | 22,4 x 35,1 | .99 | 25,1 | .67 | 17,0 | | |
| 1.00 | 25,4 | 3853 | 3909 | PMWC 1000-20 | 1.37 x 1.88 | 34,8 x 47,8 | 1.35 | 34,3 | .99 | 25,1 | | |


| For Panels .09” (2,3 mm) to .15” (3,8 mm) thick | | | | | | | | | | | | |
|---|------|------|------|--------------|-------------|-------------|------|------|-----|------|------|-----|
| .19 | 4,7 | 3880 | 3910 | PMWC 187-90 | .54 x 1.01 | 13,7 x 25,7 | .39 | 9,9 | .38 | 9,7 | .250 | 6,4 |
| .25 | 6,4 | 3881 | 3912 | PMWC 250-90 | .58 x 1.01 | 14,7 x 25,7 | .45 | 11,4 | .41 | 10,4 | | |
| .38 | 9,5 | 3882 | 3913 | PMWC 375-90 | .65 x 1.01 | 16,5 x 25,7 | .53 | 13,5 | .50 | 12,7 | | |
| .50 | 12,7 | 3883 | 3914 | PMWC 500-90 | .75 x 1.20 | 19,1 x 30,5 | .73 | 18,5 | .59 | 15,0 | | |
| .75 | 19,1 | 3884 | 3915 | PMWC 750-90 | .88 x 1.38 | 22,4 x 35,1 | .99 | 25,1 | .67 | 17,0 | | |
| 1.00 | 25,4 | 3885 | 3916 | PMWC 1000-90 | 1.37 x 1.88 | 34,8 x 47,8 | 1.35 | 34,3 | .99 | 25,1 | | |

Standard color gray or black.


Arrowhead Mount Instructions





Simply insert base of clip into .250” diameter hole.



HEYClip opens easily for access to bundle.




Unique lock/release feature operates easily and locks securely. When closed, HEYClip will not open until tab is released.



Release tab provides easy opening without forcing.

Barbed locking element ensures reliable retention.



Quick lock/release allows fast lock-up and easy access to wire bundle.

Unique design of push mount permits fast installation and provides high pull-out resistance.

Quick Specs

| | |
|---------------------|--|
| Material | Nylon 6/6 |
| Flammability Rating | 94V-2 |
| Temperature Range | 32°F (0°C) to 185°F (85°C) - Gray 32°F (0°C) to 221°F (105°C) - Black |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3848](#) [3882](#) [3883](#) [3884](#) [3853](#) [3881](#) [3847](#) [3912](#) [3914](#) [3880](#) [3845](#) [3870](#) [3872](#) [3910](#) [3906](#) [3913](#) [3871](#) [3849](#)
[3909](#) [3916](#) [3908](#)