



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7112	5.0	.021	.034	0.43	10,000	C-2R
7114	5.0	.060	.050	0.63	100,000	C-2R
7118	5.0	.115	.150	1.89	40,000	C-2R

NOTES:

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: NYLON OR EQUIVALENT.
3. BASE COLOR: WHITE.
4. PIN MATERIAL: NICKEL PLATED.
5. LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
6. FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
7. DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.

<p>THIRD ANGLE PROJECTION</p>	<p>METRIC</p> <p>DIMENSIONS ARE IN MILLIMETERS</p> <p>TOLERANCE UNLESS OTHERWISE SPECIFIED</p> <p>1 PL +/- 0.2</p> <p>2 PL +/- 0.20</p> <p>ANGLE +/- 0</p>	<p>JKL COMPONENTS CORPORATION</p>						
		<p>TITLE</p> <p>T-3/4 MICROMINIATURE BI-PIN BASED LAMPS</p>						
<p>A CHANGE PIN MATERIAL NOTE</p> <p>RELEASED - CANCEL SM-STDBP-T 3/4, 7810, 7111, BB23, 7113, 7115, 7116, 7119</p>	<p>7/28/08</p> <p>3/15/00</p>	<p>DRAWN BY</p> <p>L. WENGSTROM</p>	<p>APPVD BY DATE</p> <p>L.R. 7/28/08</p>	<p>SIZE</p> <p>A</p>	<p>FSCM NO.</p> <p>55335</p>	<p>DRAWING NO.</p> <p>BI-PIN T-3/4</p>		
<p>REV. NO.</p> <p>DESCRIPTION/ECO NUMBER</p> <p>APPVD DATE</p>		<p>- CAD DRAWING -</p> <p>MANUAL REVISIONS NOT PERMITTED</p>		<p>SCALE</p> <p>NONE</p>	<p>RELEASED DATE</p> <p>3/15/00</p>	<p>REVISION DATE</p> <p>7/28/08</p>	<p>REV. NO.</p> <p>A</p>	<p>SHEET</p> <p>1 OF 1</p>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[7112](#) [7114](#) [7118](#)