



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
48	2.0	.060	.04	0.50	1,000	S-2
41	2.5	.500	.50	6.29	3,000	C-2R
40	6.3	.150	.52	6.54	3,000	C-2R
46	6.3	.250	.90	11.31	3,000	C-2R
1487	14.0	.200	1.40	17.60	3,000	C-2F
1821	28.0	.170	3.50	44.00	500	C-2F
1832	37.5	.050	.65	8.17	3,000	C-2F

METRIC THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	JKL COMPONENTS CORPORATION				
		TITLE T-3 1/4 MINIATURE SCREW BASE				
B DELETE CANCELLED PART NO. RS22 A CORRECTION ON RS22 RATINGS RELEASE	7/22/05 2/21/01 2/8/01	DRAWN BY L. WENGSTROM	APPVD BY DATE J.K. 7/22/05	SIZE A	FSCM NO. 55335	DRAWING NO. SCREW BASE T-3 1/4
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 2/8/01	REVISION DATE 7/22/05	REV. NO. B	SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
----------	------------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[1487](#) [1821](#) [41](#) [46](#) [40](#) [1832](#)