

WINNIE-W-C

~50° spot beam with holder C compatible with LEDiL HEKLA

TECHNICAL SPECIFICATIONS:

Dimensions	Ø 50.0 mm
Height	19.5 mm
Fastening	tape
ROHS compliant	yes ⓘ




MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
WINNIE-W	Single lens	PMMA	clear	
WINNIE-HLD-C	Holder	PC	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CN15825_WINNIE-W-C	Single lens	364	84	28	0.0
» Box size:					




See also our general installation guide: www.ledil.com/installation_guide



PHOTOMETRIC DATA (MEASURED):




LED V4 HD
FWHM / FWTM 50.0° / 89.0°
Efficiency 84 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15253_HEKLA-SOCKET-A





LED V6 Gen6
FWHM / FWTM 53.0° / 91.0°
Efficiency 83 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15253_HEKLA-SOCKET-A



LED V6 HD
FWHM / FWTM 47.0° / 87.0°
Efficiency 84 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C





LED V9 HD
FWHM / FWTM 44.0° / 82.0°
Efficiency 83 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I





PHOTOMETRIC DATA (MEASURED):





LED VERO13
FWHM / FWTM 45.0° / 83.0°
Efficiency 78 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K





LED VERO18
FWHM / FWTM 52.0° / 92.0°
Efficiency 76 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K



LED Vesta DTW 13mm (21W)
FWHM / FWTM 46.0° / 84.0°
Efficiency 75 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour Tunable White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 491 Typ L8



LED Vesta TW 13mm (25W) CSP
FWHM / FWTM 44.0° / 81.0°
Efficiency 78 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 492 Typ L8





PHOTOMETRIC DATA (MEASURED):



LED Vesta TW 6mm DP
 FWHM / FWTM 38.0° / 77.0°
 Efficiency 79 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 504 Typ L8





LED Vesta TW 9mm (12W) CSP
 FWHM / FWTM 38.0° / 72.0°
 Efficiency 78 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K





CITIZEN

LED CLC020 Series (Dim-To-Warm)
 FWHM / FWTM 41.0° / 78.0°
 Efficiency 79 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K



CITIZEN



LED CLC030 Series (Dim-To-Warm)
 FWHM / FWTM 43.0° / 82.0°
 Efficiency 70 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K



PHOTOMETRIC DATA (MEASURED):



CITIZEN

LED CLL02x/CLU02x (LES10)
 FWHM / FWTM 48.0° / 88.0°
 Efficiency 79 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





CITIZEN

LED CLU7A2 (LES 4.2mm)
 FWHM / FWTM 48.0° / 90.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





CITIZEN

LED LCN-C01B (Tunable White)
 FWHM / FWTM 38.0° / 74.0°
 Efficiency 78 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 481 Typ L8



CREE LED



LED CMT14xx
 FWHM / FWTM 49.0° / 89.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C




PHOTOMETRIC DATA (MEASURED):





LED CMT19xx
FWHM / FWTM 48.0° / 86.0°
Efficiency 79 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I





LED CXA/B 13xx
FWHM / FWTM 52.0° / 92.0°
Efficiency 83 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15956_HEKLA-SOCKET-J



LED LUXEON CX Plus CoB L08 (Gen2)
FWHM / FWTM 48.0° / 86.0°
Efficiency 79 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 637a Hekla





LED LUXEON CoB 1202HD
FWHM / FWTM 50.0° / 89.0°
Efficiency 84 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G



PHOTOMETRIC DATA (MEASURED):



LUMILEDS

LED LUXEON CoB 1202s
 FWHM / FWTM 48.0° / 88.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15848_HEKLA-SOCKET-G





LUMILEDS

LED LUXEON CoB 1204HD
 FWHM / FWTM 46.0° / 85.0°
 Efficiency 84 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15858_HEKLA-SOCKET-H




LUMILEDS

LED LUXEON CoB 1205HD
 FWHM / FWTM 46.0° / 84.0°
 Efficiency 82 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15858_HEKLA-SOCKET-H



LUMILEDS


LED LUXEON CX Plus CoB - HD S01H4
 FWHM / FWTM 46.0° / 87.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 634c Hekla





PHOTOMETRIC DATA (MEASURED):





LED LUXEON CX Plus CoB - HD S01H6 / HD S02H6
 FWHM / FWTM 44.0° / 86.0°
 Efficiency 83 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 634c Hekla





LED LUXEON CX Plus CoB - HD S04H9
 FWHM / FWTM 48.0° / 88.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 634c Hekla



LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 FWHM / FWTM 46.0° / 85.0°
 Efficiency 80 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 637a Hekla





LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 FWHM / FWTM 45.0° / 85.0°
 Efficiency 82 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 641a Hekla





PHOTOMETRIC DATA (MEASURED):





LED LUXEON CX Plus CoB S01 (Gen2)
 FWHM / FWTM 45.0° / 86.0°
 Efficiency 84 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 634c Hekla





LED LUXEON Fusion 12-up (20x24)
 FWHM / FWTM 39.0° / 77.0°
 Efficiency 80 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 442 Typ L8



LED CxM-14 (19x19)
 FWHM / FWTM 48.0° / 86.0°
 Efficiency 78 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15859_HEKLA-SOCKET-I





LED CXM-4
 FWHM / FWTM 45.0° / 86.0°
 Efficiency 82 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





PHOTOMETRIC DATA (MEASURED):





LED CxM-9 (13.5x13.5)
 FWHM / FWTM 48.0° / 88.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





LED Fortimo SLM L09 CoB
 FWHM / FWTM 45.0° / 83.0°
 Efficiency 83 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15858_HEKLA-SOCKET-H



LED Fortimo SLM L13 CoB
 FWHM / FWTM 45.0° / 82.0°
 Efficiency 79 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 432 Typ L8





LED Fortimo SLM L15 CoB
 FWHM / FWTM 47.0° / 85.0°
 Efficiency 77 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 432 Typ L8



PHOTOMETRIC DATA (MEASURED):



SAMSUNG

LED LC003D / LC006D / LC009D / LC013D
 FWHM / FWTM 48.0° / 88.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





SAMSUNG

LED LC010C
 FWHM / FWTM 49.0° / 90.0°
 Efficiency 82 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15848_HEKLA-SOCKET-G





SAMSUNG

LED LC010C G2
 FWHM / FWTM 46.0° / 87.0°
 Efficiency 82 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C



SAMSUNG



LED LC016D / LC019D / LC026D / LC033D
 FWHM / FWTM 49.0° / 89.0°
 Efficiency 77 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15859_HEKLA-SOCKET-I



PHOTOMETRIC DATA (MEASURED):



SAMSUNG

LED LC020C
FWHM / FWTM 48.0° / 88.0°
Efficiency 82 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G





SAMSUNG

LED LC020C G2
FWHM / FWTM 44.0° / 84.0°
Efficiency 82 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I





TRIDONIC

LED SLE G7 LES09
FWHM / FWTM 48.0° / 87.0°
Efficiency 80 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



TRIDONIC



LED SLE G7 LES13
FWHM / FWTM 47.0° / 86.0°
Efficiency 78 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I



PHOTOMETRIC DATA (MEASURED):



TRIDONIC

LED SLE G7 LES15
 FWHM / FWTM 49.0° / 88.0°
 Efficiency 77 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15859_HEKLA-SOCKET-I





XICATO

LED XOB 14.5 mm
 FWHM / FWTM 49.0° / 88.0°
 Efficiency 78 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15859_HEKLA-SOCKET-I



XICATO


LED XOB 9.8 mm
 FWHM / FWTM 47.0° / 88.0°
 Efficiency 81 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C



PHOTOMETRIC DATA (SIMULATED):




LED VERO10
FWHM / FWTM 44.0° / 84.0°
Efficiency 85 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15616_HEKLA-SOCKET-F




CITIZEN


LED CLL03x/CLU03x
FWHM / FWTM 46.0° / 86.0°
Efficiency 77 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I



LED CXA/B 15xx
FWHM / FWTM 49.0° / 89.0°
Efficiency 85 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15256_HEKLA-SOCKET-D




LED CXA/B 1816 & CXA/B 1820 & CXA 1850
FWHM / FWTM 39.0° / 83.0°
Efficiency 88 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15254_HEKLA-SOCKET-B



PHOTOMETRIC DATA (SIMULATED):




LED NFSWE11A
 FWHM / FWTM 36.0° / 76.0°
 Efficiency 75 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 30
 Light colour White
 Required components:




SEOUL SEMICONDUCTOR

LED MJT COB LES 14.5
 FWHM / FWTM 52.0° / 92.0°
 Efficiency 79 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15859_HEKLA-SOCKET-I



SEOUL SEMICONDUCTOR

LED MJT COB LES 9.8
 FWHM / FWTM 49.0° / 90.0°
 Efficiency 83 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[CN15825_WINNIE-W-C](#)