

WDD 81V

Desoldering Station Digital 95 W, 230 V, Compressed Air or Inert Gas Operated
Product no.: T0053256699N



Benefits





Technical Data

Dimensions L x W x H (mm)	---
Dimensions L x W x H (inches)	---
Weight (approx.) in kg	---
Voltage	230 V, 50 Hz
Power	95 W
Channels	---
Temperature range (depends on tool) °C	---
Temperature range (depends on tool) °F	---
Temperature accuracy °C	9 °C
Temperature accuracy °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	Via a 3.5 mm jack bush (initial state-hard-grounded)
Display	---
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[T0053256699N](#)