




**Fig. 1**

- Series 3XX are available with straight and right angle solder tails.
- Series 350 & 399...009 use MM #3404 and #5011 pins. See pages 179 & 181 for details.
- Series 301, 310 & 399...003 use MM #0156, #1001 & #1103 receptacles. See pages 136 & 137 for details.
- Receptacles use Hi-Rel, 4 finger #30 BeCu contact rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.




**Fig. 2**

<b>Ordering Information</b>	
<b>Fig. 1</b>	<b>Series 350...006      Straight Pin Header</b>
	350-XX-1__-00-006000 Specify # of pins → 01-64
<b>Fig. 2</b>	<b>Series 399...009      Right Angle Pin Header</b>
	399-XX-1__-10-009000 Specify # of pins → 02-64




**Fig. 3**

<i>For Electrical, Mechanical &amp; Environmental Data, See pg. 4</i>	<b>XX=Plating Code See Below</b>	<i>For RoHS compliance select ◇ plating code.</i>
SPECIFY PLATING CODE XX=	10◇	90
Pin Plating	10μ" Au	200μ" Sn/Pb



**Fig. 4**

<b>Fig. 3</b>	<b>Series 310...001      Straight Socket</b>
	310-XX-1__-41-001000 Specify # of pins → 01-64
<b>Fig. 4</b>	<b>Series 301...056      Socket w/ Retention Pegs</b>
	301-XX-1__-41-560000 Specify # of pins → 01-64
<b>Fig. 5</b>	<b>Series 399...003      Right Angle Socket</b>
	399-XX-1__-10-003000 Specify # of pins → 01-64



**Fig. 5**

<i>For Electrical, Mechanical &amp; Environmental Data, See pg. 4</i>	<b>XX=Plating Code See Below</b>	<i>For RoHS compliance select ◇ plating code.</i>
SPECIFY PLATING CODE XX=	13◇	91
Sleeve (Pin)	10μ" Au	200μ" Sn/Pb
Contact (Clip)	30μ" Au	10μ" Au

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mill-Max:

[350-90-164-00-006000](#) [350-90-132-00-006000](#) [350-90-120-00-006000](#) [350-10-132-00-006000](#) [350-10-114-00-006000](#) [399-13-120-10-003000](#) [399-93-120-10-003000](#) [350-10-106-00-006000](#) [350-40-132-00-006000](#) [350-40-120-00-006000](#) [399-10-120-10-009000](#) [350-90-103-00-006000](#) [399-93-103-10-003000](#) [399-43-164-10-003000](#) [399-10-108-10-009000](#) [399-90-164-10-009000](#) [399-13-164-10-003000](#) [399-13-132-10-003000](#) [399-10-132-10-009000](#) [399-43-132-10-003000](#) [399-43-120-10-003000](#) [399-40-164-10-009000](#) [399-40-132-10-009000](#) [399-40-120-10-009000](#) [399-93-132-10-003000](#) [399-90-132-10-009000](#) [350-10-121-00-006000](#) [350-10-117-00-006000](#) [399-93-104-10-003000](#) [399-43-112-10-003000](#) [399-43-105-10-003000](#) [399-91-119-10-003000](#) [399-90-115-10-009000](#) [399-13-114-10-003000](#) [399-40-103-10-009000](#) [399-93-130-10-003000](#) [399-13-125-10-003000](#) [350-10-133-00-006000](#) [399-43-116-10-003000](#) [399-41-140-10-003000](#) [399-43-155-10-003000](#) [350-10-151-00-006000](#) [399-93-106-10-003000](#) [399-40-138-10-009000](#) [350-90-149-00-006000](#) [399-93-141-10-003000](#) [399-91-139-10-003000](#) [350-40-110-00-006000](#) [399-41-160-10-003000](#) [399-40-127-10-009000](#) [399-13-136-10-003000](#) [350-90-134-00-006000](#) [399-93-119-10-003000](#) [399-10-147-10-009000](#) [399-93-109-10-003000](#) [350-10-124-00-006000](#) [350-40-147-00-006000](#) [399-13-156-10-003000](#) [399-41-150-10-003000](#) [399-43-106-10-003000](#) [399-91-129-10-003000](#) [399-93-161-10-003000](#) [399-43-119-10-003000](#) [399-13-146-10-003000](#) [399-91-149-10-003000](#) [399-40-158-10-009000](#) [399-90-137-10-009000](#) [399-93-151-10-003000](#) [399-10-142-10-009000](#) [399-40-148-10-009000](#) [399-91-109-10-003000](#) [350-10-136-00-006000](#) [399-13-111-10-003000](#) [399-10-137-10-009000](#) [399-90-157-10-009000](#) [399-41-120-10-003000](#) [350-90-122-00-006000](#) [350-10-154-00-006000](#) [399-43-145-10-003000](#) [399-40-113-10-009000](#) [399-13-103-10-003000](#) [399-43-135-10-003000](#) [399-90-123-10-009000](#) [399-40-161-10-009000](#) [350-10-150-00-006000](#) [399-90-129-10-009000](#) [399-43-109-10-003000](#) [399-93-112-10-003000](#) [399-10-135-10-009000](#) [399-93-101-10-003000](#) [399-90-126-10-009000](#) [350-90-152-00-006000](#) [399-40-124-10-009000](#) [399-90-140-10-009000](#) [399-41-146-10-003000](#) [399-93-154-10-003000](#) [399-90-105-10-009000](#) [350-40-163-00-006000](#) [399-41-113-10-003000](#) [399-10-107-10-009000](#)