






10	9		8		7	6	5	4	3	2	1
CKTS	DIM A	DIM B	DIM C								
4	5.08	2.54	NA	0.10							
6	7.62	5.08	2.54	0.10							
8	10.16	7.62	5.08	0.10							
10	12.70	10.16	7.62	0.10							
12	15.24	12.70	10.16	0.10							
14	17.78	15.24	12.70	0.10							
16	20.32	17.78	15.24	0.10							
18	22.86	20.32	17.78	0.10							
20	25.40	22.86	20.32	0.10							
22	27.94	25.40	22.86	0.15							
24	30.48	27.94	25.40	0.15							
26	33.02	30.48	27.94	0.15							
28	35.56	33.02	30.48	0.15							
30	38.10	35.56	33.02	0.15							
32	40.64	38.10	35.56	0.15							
34	43.18	40.64	38.10	0.15							
36	45.72	43.18	40.64	0.15							
38	48.26	45.72	43.18	0.15							
40	50.80	48.26	45.72	0.15							
42	53.34	50.80	48.26	0.23							
44	55.88	53.34	50.80	0.23							
46	58.42	55.88	53.34	0.23							
48	60.96	58.42	55.88	0.23							
50	63.50	60.96	58.42	0.23							
52	66.04	63.50	60.96	0.23							
54	68.58	66.04	63.50	0.23							
56	71.12	68.58	66.04	0.23							
58	73.66	71.12	68.58	0.23							
60	76.20	73.66	71.12	0.23							
62	78.74	76.20	73.66	0.30							
64	81.28	78.74	76.20	0.30							
66	83.82	81.28	78.74	0.30							
68	86.36	83.82	81.28	0.30							
70	88.90	86.36	83.82	0.30							
72	91.44	88.90	86.36	0.30							
74	93.98	91.44	88.90	0.30							
76	96.52	93.98	91.44	0.30							
78	99.06	96.52	93.98	0.30							
80	101.60	99.06	96.52	0.30							
90	114.30	111.76	109.22	0.38							
100	127.00	124.46	122.06	0.38							



PEG OPTIONS
NO PEG
1.40 = SHORT PEG
3.30 = LONG PEG




PCB LAYOUT: COMPONENT SIDE
(FOR CKT 04,06 AND 08 REFER SHEET 2)





SOLDER PAD
FOR CKTS
WITHOUT PEGS

- NOTES:
- HOUSING MATERIAL: LCP, UL 94V-0 COLOR: BLACK
PIN MATERIAL: COPPER ALLOY
 - FINISH:
124 = BRIGHT TIN: 3.81 MICROMETERS MIN OVER MATTE NICKEL
207 = SELECT GOLD: 0.38 MICROMETERS MIN IN CONTACT AREA
SELECT BRIGHT TIN: 2.0 MICROMETERS MIN IN SMT TAIL
BOTH OVER NICKEL.
206 = SELECT GOLD: 0.75 MICROMETERS MIN IN CONTACT AREA
SELECT BRIGHT TIN: 2.0 MICROMETERS MIN IN SMT TAIL
BOTH OVER NICKEL.
197 = REFLOW MATTE TIN: 1.52 MICROMETERS MIN OVER MATTE NICKEL
222 = MATTE TIN: 2.54 MICROMETERS MIN OVER MATTE NICKEL
118 = BRIGHT TIN: 1.52 MICROMETERS MIN OVER NICKEL
 - PRODUCT SPECIFICATION: PS-71308
 - PACKAGING SPECIFICATION: SEE CHART
 - COSMETIC SPECIFICATION: PS-45499-002 CLASS B
 - SOLDERABILITY SPECIFICATION: SMES-152



DRAWING SHEET INDEX		
SHEET NO	PEG STYLE	DIM M MATING HEIGHT
2	NONE	6.10
3	NONE	6.10
4	NONE	8.13
5	LONG	6.10
6	LONG	8.13
7	SHORT	6.10
8	SHORT	8.13
9	PARTS WITH VOIDS	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex					
mm		3:1										
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 643267			CGRID HEADER ASSY VERTICAL DUAL ROW SMT					
ANGULAR TOL		± °		DRWN: ABABUPS 2020/05/29								
4 PLACES		±		CHK'D: MRAMAKRISHNA 2020/08/12								
3 PLACES		±		APPR: MRAMAKRISHNA 2020/08/12			PRODUCT CUSTOMER DRAWING					
2 PLACES		± 0.13		INITIAL REVISION:								
1 PLACE		± 0.25		DRWN: KSAMIEC 2017/09/07			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
0 PLACES		± 0.0		APPR: FSMITH 2018/07/03			713080000-SD		PSD	000	A6	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
						B-SIZE	71308					1 OF 10



10		9		8		7		6		5		4		3		2		1			
F	PLATING:	124 - BRIGHT TIN	124 - BRIGHT TIN	124 - BRIGHT TIN	207 - 0.38 SGOLD	207 - 0.38 SGOLD	207 - 0.38 SGOLD	206 - 0.76 SGOLD	206 - 0.76 SGOLD	206 - 0.76 SGOLD											
	PACKAGING:	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A	TUBE 713080001-PK	TUBE 713080002-PK	T&R 713080000-PK STYLE A											
	PICK AND PLACE CAPS	NO	YES	YES	NO	YES	YES	NO	YES	YES											
	CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO											
	4	015-91-2040	NA	015-91-6040	015-91-0040	NA	015-91-6042	015-91-3040	NA	015-91-6043											
	6	015-91-2060 / 71308-9060	NA	015-91-6060	015-91-0060	NA	015-91-6062	015-91-3060 / 71308-9061	NA	015-91-6063											
E	8	015-91-2080 / 71308-9080	015-91-3087	015-91-6080	015-91-0080	015-91-3086	015-91-6082	015-91-3080	015-91-3088	015-91-6083											
	10	015-91-2100	015-91-3107	015-91-6100	015-91-0100	015-91-3106	015-91-6102	015-91-3100 / 71308-3110	015-91-3108	015-91-6103											
	12	015-91-2120	015-91-3127	015-91-6120	015-91-0120	015-91-3126	015-91-6122	015-91-3120	015-91-3128	015-91-6123											
	14	015-91-2140	015-91-3147	015-91-6140	015-91-0140 / 71308-9140	015-91-3146	015-91-6142	015-91-3140	015-91-3148	015-91-6143											
	16	015-91-2160	015-91-3167	015-91-6160	015-91-0160	015-91-3166	015-91-6162	015-91-3160	015-91-3168	015-91-6163											
	18	015-91-2180	015-91-3187		015-91-0180	015-91-3186		015-91-3180	015-91-3188												
E	20	015-91-2200	015-91-3207	015-91-6200	015-91-0200 / 71308-9200	015-91-3206	015-91-6202	015-91-3200	015-91-3208	015-91-6203											
	22	015-91-2220	015-91-3227		015-91-0220	015-91-3226		015-91-3220	015-91-3228												
	24	015-91-2240	015-91-3247	71308-2240	015-91-0240	015-91-3246		015-91-3240	015-91-3248												
	26	015-91-2260	015-91-3267	015-91-6260	015-91-0260	015-91-3266	015-91-6262	015-91-3260	015-91-3268												
	28	015-91-2280	015-91-3287		015-91-0280	015-91-3286		015-91-3280	015-91-3288												
	30	015-91-2300	015-91-3307		015-91-0300	015-91-3306		015-91-3300	015-91-3308												
D	32	015-91-2320	015-91-3327		015-91-0320	015-91-3326		015-91-3320	015-91-3328												
	34	015-91-2340	015-91-3347		015-91-0340	015-91-3346		015-91-3340	015-91-3348												
	36	015-91-2360	015-91-3367		015-91-0360	015-91-3366		015-91-3360	015-91-3368												
	38	015-91-2380	015-91-3387		015-91-0380	015-91-3386		015-91-3380	015-91-3388												
	40	015-91-2400	015-91-3407	015-91-6400	015-91-0400	015-91-3406	015-91-6402	015-91-3400	015-91-3408	015-91-6403											
	42	015-91-2420	015-91-3427		015-91-0420	015-91-3426		015-91-3420	015-91-3428												
D	44	015-91-2440	015-91-3447		015-91-0440	015-91-3446		015-91-3440	015-91-3448												
	46	015-91-2460	015-91-3467		015-91-0460	71308-0546		015-91-3460	015-91-3468												
	48	015-91-2480	015-91-3487		015-91-0480	015-91-3486		015-91-3480	015-91-3488												
	50	015-91-2500	015-91-3507	015-91-6500	015-91-0500	015-91-3506	015-91-6502	015-91-3500	015-91-3508	015-91-6503											
	52	015-91-2520	015-91-3527		015-91-0520	015-91-3526		015-91-3520	015-91-3528												
	54	015-91-2540	015-91-3547		015-91-0540	015-91-3546		015-91-3540	015-91-3548												
C	56	015-91-2560	015-91-3567		015-91-0560	015-91-3566		015-91-3560	015-91-3568												
	58	015-91-2580	015-91-3587		015-91-0580	015-91-3586		015-91-3580	015-91-3588												
	60	015-91-2600	015-91-3607		015-91-0600	015-91-3606		015-91-3600	015-91-3608												
	62	015-91-2620	015-91-3627		015-91-0620	015-91-3626		015-91-3620	015-91-3628												
	64	015-91-2640	015-91-3647		015-91-0640	015-91-3646		015-91-3640	015-91-3648												
	66	015-91-2660	015-91-3667		015-91-0660	015-91-3666		015-91-3660	015-91-3668												
C	68	015-91-2680	015-91-3687		015-91-0680	015-91-3686		015-91-3680	015-91-3688												
	70	015-91-2700	015-91-3707		015-91-0700	015-91-3706		015-91-3700	015-91-3708												
	72	015-91-2720	015-91-3727		015-91-0720	015-91-3726		015-91-3720	015-91-3728												
	74	015-91-2740	015-91-3747		015-91-0740	015-91-3746		015-91-3740	015-91-3748												
	76	015-91-2760	015-91-3767		015-91-0760	015-91-3766		015-91-3760	015-91-3768												
	78	015-91-2780	015-91-3787		015-91-0780	015-91-3786		015-91-3780	015-91-3788												
B	80	015-91-2800	015-91-3807		015-91-0800	015-91-3806		015-91-3800	015-91-3808												
	90				71308-0190																
	100	71308-0101	71308-0500		71308-0200	71308-0600		71308-0300	71308-0700												
PARTS ON THIS SHEET ARE WITHOUT PEGS WITH 6.10 MATING LENGTH 6.10 NO PEGS											THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS mm SCALE 1:1 GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.13 1 PLACE ± 0.25 0 PLACES ± 0.0 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS CURRENT REV DESC: EC NO: 643267 DRWN: ABABUPS 2020/05/29 CHK'D: MRAMAKRISHNA 2020/08/12 APPR: MRAMAKRISHNA 2020/08/12 INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03 THIRD ANGLE PROJECTION DRAWING B-SIZE SERIES 71308 molex CGRID HEADER ASSY VERTICAL DUAL ROW SMT PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 713080000-SD DOC TYPE PSD DOC PART 000 REVISION A6 MATERIAL NUMBER CUSTOMER SHEET NUMBER 3 OF 10										
DOCUMENT STATUS		P1	RELEASE DATE	2020/08/12	15:54:36																
9		8		7		6		5		4		3		2		1					

[illegible]

10		9		8		7		6		5		4		3		2		1		
PLATING:		124 - BRIGHT TIN		124 - BRIGHT TIN		197 - REFLOW TIN		197 - REFLOW TIN		207 - 0.38 SGOLD		207 - 0.38 SGOLD		206 - 0.76 SGOLD		118 - BRIGHT TIN		118 - BRIGHT TIN		
PACKAGING:		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		T&R 713080000-PK STYLE B		TUBE 713080003-PK		
PICK AND PLACE CAPS		NO		YES		NO		YES		NO		YES		NO		YES		NO		
CKTS:		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO		MATERIAL NO
4		71308-8004								015-91-0048				015-91-5049						
6		71308-8006								015-91-0068				015-91-5069						
8		71308-8008								015-91-0088		A2 71308-6908		015-91-5089						
10		71308-8010								015-91-0108				015-91-5109				71308-5810		
12		71308-8012								015-91-0128				015-91-5129						
14		71308-8014								015-91-0148				015-91-5149						
16		71308-8016				71308-8017		71308-0015		015-91-0168				015-91-5169				71308-5816		
18		71308-8018								015-91-0188				015-91-5189						
20		71308-8020								015-91-0208				015-91-5209						
22		71308-8022								015-91-0228				015-91-5229						
24		71308-8024		71308-8124						015-91-0248				015-91-5249		71308-5724		71308-5824		
26		71308-8026								015-91-0268				015-91-5269						
28		71308-8028								015-91-0288				015-91-5289						
30		71308-8030								015-91-0308				015-91-5309						
32		71308-8032																		
34		71308-8034								015-91-0348				015-91-5349						
36		71308-8036								015-91-0368				015-91-5369						
38		71308-8038								015-91-0388				015-91-5389						
40		71308-8040								015-91-0408				015-91-5409						
42		71308-8042								015-91-0428				015-91-5429						
44		71308-8044								015-91-0448				015-91-5449						
46		71308-8046								015-91-0468				015-91-5469						
48		71308-8048								015-91-0488				015-91-5489						
50		71308-8050								015-91-0508				015-91-5509						
52		71308-8052								015-91-0528				015-91-5529						
54		71308-8054								015-91-0548				015-91-5549						
56		71308-8056								015-91-0568				015-91-5569						
58		71308-8058								015-91-0588				015-91-5589						
60		71308-8060								015-91-0608				015-91-5609						
62		71308-8062								015-91-0628				015-91-5629						
64		71308-8064								015-91-0648				015-91-5649						
66		71308-8066								015-91-0668				015-91-5669						
68		71308-8068								015-91-0688				015-91-5689						
70		71308-8070								015-91-0708				015-91-5709						
72		71308-8072								015-91-0728				015-91-5729						
74		71308-8074								015-91-0748				015-91-5749						
76		71308-8076								015-91-0768				015-91-5769						
78		71308-8078								015-91-0788				015-91-5789						
80		71308-8080								015-91-0808				015-91-5809						
100										71308-1200				71308-1300						

10	9	8	7	6	5	4	3	2	1
PLATING:	124 - BRIGHT TIN	207 - 0.38 SGOLD	206 - 0.76 SGOLD	124 - BRIGHT TIN	207 - 0.38 GOLD	206 - 0.76 GOLD	118 - BRIGHT TIN	118 - BRIGHT TIN	
PACKAGING:	TUBE 713080001-PK	TUBE 713080001-PK	TUBE 713080001-PK	T&R 713080000-PK STYLE C	T&R 713080000-PK STYLE C	T&R 713080000-PK STYLE C	TUBE 713080001-PK	T&R 713080000-PK STYLE C	
PICK AND PLACE CAPS	NO	NO	NO	YES	YES	YES	NO	YES	
CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	
4	015-91-1041	015-91-1042	015-91-1043	015-91-6044	015-91-6045	015-91-6046	71308-6404	71308-6504	
6	015-91-1061	015-91-1062	015-91-1063	015-91-6064	015-91-6065	015-91-6066	71308-6406	71308-6506	
8	015-91-1081	015-91-1082	015-91-1083	015-91-6084	015-91-6085	015-91-6086	71308-6408	71308-6508	
10	015-91-1101	015-91-1102 / 71308-1102	015-91-1103	015-91-6104	015-91-6105	015-91-6106	71308-6410	71308-6510	
12	015-91-1121	015-91-1122	015-91-1123				71308-6412		
14	015-91-1141	015-91-1142	015-91-1143	015-91-6144	015-91-6145	015-91-6146	71308-6414	71308-6514	
16	015-91-1161	015-91-1162	015-91-1163	015-91-6164	015-91-6165	015-91-6166	71308-6416	71308-6516	
18	015-91-1181	015-91-1182	015-91-1183				71308-6418		
20	015-91-1201	015-91-1202	015-91-1203				71308-6420		
22	015-91-1221	015-91-1222	015-91-1223				71308-6422		
24	015-91-1241	015-91-1242	015-91-1243	71308-6901			71308-6424		
26	015-91-1261	015-91-1262	015-91-1263				71308-6426		
28	015-91-1281	015-91-1282	015-91-1283				71308-6428		
30	015-91-1301	015-91-1302	015-91-1303				71308-6430		
32	015-91-1321	015-91-1322	015-91-1323				71308-6432		
34	015-91-1341	015-91-1342	015-91-1343				71308-6434		
36	015-91-1361	015-91-1362	015-91-1363				71308-6436		
38	015-91-1381	015-91-1382	015-91-1383				71308-6438		
40	015-91-1401	015-91-1402	015-91-1403				71308-6440		
42	015-91-1421	015-91-1422	015-91-1423				71308-6442		
44	015-91-1441	015-91-1442	015-91-1443				71308-6444		
46	015-91-1461	015-91-1462	015-91-1463				71308-6446		
48	015-91-1481	015-91-1482	015-91-1483				71308-6448		
50	015-91-1501	015-91-1502	015-91-1503			015-91-6506	71308-6450		
52	015-91-1521	015-91-1522	015-91-1523			71308-5203	71308-6452		
54	015-91-1541	015-91-1542	015-91-1543				71308-6454		
56	015-91-1561	015-91-1562	015-91-1563				71308-6456		
58	015-91-1581	015-91-1582	015-91-1583				71308-6458		
60	015-91-1601	015-91-1602	015-91-1603				71308-6460		
62	015-91-1621	015-91-1622	015-91-1623				71308-6462		
64	015-91-1641	015-91-1642	015-91-1643				71308-6464		
66	015-91-1661	015-91-1662	015-91-1663				71308-6466		
68	015-91-1681	015-91-1682	015-91-1683				71308-6468		
70	015-91-1701	015-91-1702	015-91-1703				71308-6470		
72	015-91-1721	015-91-1722	015-91-1723				71308-6472		
74	015-91-1741	015-91-1742	015-91-1743				71308-6474		
76	015-91-1761	015-91-1762	015-91-1763				71308-6476		
78	015-91-1781	015-91-1782	015-91-1783				71308-6478		
80	015-91-1801	015-91-1802	015-91-1803				71308-6480		
100	71308-4100	71308-4200	71308-4300						

<


[illegible]


10	9	8	7	6	5	4	3	2	1
PLATING:	197 - REFLOW TIN	197 - REFLOW TIN	197 - REFLOW TIN						
PACKAGING:	T&R 713080000-PK STYLE D	TUBE 713080004-PK	TUBE 713080003-PK						
PICK AND PLACE CAPS	YES	YES	NO						
CKTS:	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	MATERIAL NO	
4									
6									
8	71308-8409	71308-8408	71308-8508 (A6)						
10									
12									
14									
16									
18									
20	71308-8421	71308-8420	71308-8520 (A6)						
22									
24									
26	71308-8426								
28									
30									
32									
34									
36									
38									
40									
42									
44									
46									
48									
50									
52									
54									
56									
58									
60									
62									
64									
66									
68									
70									
72									
74									
76									
78									
80									

PARTS ON THIS SHEET HAVE
SHORT PEGS WITH
A MATING HEIGHT OF 8.13

8.13

1.40




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 643267 DRWN: ABABUPS 2020/05/29 CHK'D: MRAMAKRISHNA 2020/08/12 APPR: MRAMAKRISHNA 2020/08/12 INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03				CGRID HEADER ASSY VERTICAL DUAL ROW SMT							
ANGULAR TOL		± °													
4 PLACES		±													
3 PLACES		±													
2 PLACES		± 0.13													
1 PLACE		± 0.25		DOCUMENT NUMBER				713080000-SD		PSD 000 A6					
0 PLACES		± 0.0													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						B-SIZE		71308						9 OF 10	

DOCUMENT STATUS	P1	RELEASE DATE	2020/08/12	15:54:36
-----------------	----	--------------	------------	----------

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---

MATERIAL NO	MADE FROM	NO OF CKTS	VOID LOCATION	PICK AND PLACE CAP	PACKAGING
71308-9210	71308-0010	10	A5	711331000	713080002-PK
71308-9010	71308-0110	10	A2	711331000	713080002-PK
71308-9032	71308-0132	32	A9	711331000	713080002-PK
71308-9110	71308-0110	10	A5	711331000	713080002-PK
71308-9014	71308-0140	14	B5	711331000	713080002-PK
71308-9310	71308-0110	10	B5	711331000	713080002-PK
71308-9311	71308-0110	10	B5	711331000	713080000-PK STYLE A
71308-9312	71308-1504	04	A1	711331000	713080000-PK STYLE A



CIRCUIT IDENTIFICATION FOR VOIDED CKT ONLY

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS mm		SCALE 5:1		CURRENT REV DESC: EC NO: 643267 DRWN: ABABUPS 2020/05/29 CHK'D: MRAMAKRISHNA 2020/08/12 APPR: MRAMAKRISHNA 2020/08/12 INITIAL REVISION: DRWN: KSAMIEC 2017/09/07 APPR: FSMITH 2018/07/03			molex CGRID HEADER ASSY VERTICAL DUAL ROW SMT		
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		± °					PRODUCT CUSTOMER DRAWING		
4 PLACES		±					DOCUMENT NUMBER		
3 PLACES		±					713080000-SD		
2 PLACES		± 0.13		DOC TYPE					
1 PLACE		± 0.25		PSD					
0 PLACES		± 0.0		DOC PART					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		REVISION	
				B-SIZE		71308		A6	
MATERIAL NUMBER				CUSTOMER			SHEET NUMBER		
							10 OF 10		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-91-6067](#)