

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**


**Part Number:** [1120110021](#)  
**Status:** **Active**  
**Overview:** PC Network Interface Cards  
**Description:** SST PB3 Card, PROFIBUS DP Master/Slave, 1 Channel, PCI 3.3/ 5V -DLL/LIB - Control

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Network Interface
Series	<a href="#">112011</a>
Application	IO Control
Approvals	CE certified
Comments	1 channel
Overview	<a href="#">PC Network Interface Cards</a>
Product Name	SST
Protocol	PROFIBUS
Protocol Detail	PROFIBUS DPV0 Master, PROFIBUS DPV0 Slave, PROFIBUS DPV1 Master
Software Downloads	SST-PB3-PCU
Type	PROFIBUS Card
UPC	78678801336
<b>Physical</b>	
Channels	1
Communication Speed	PROFIBUS 9.6 kbps to 12 Mbps
Interface	CommDTM, DLL, OPC DA
Mounting Style	PC Slot
Net Weight	140.000/g
Network Connection Type	PROFIBUS D-Sub Female (9 pin)
Operating System	Windows7, Windows8/8.1, Windows Server 2003, Windows Server 2008, Windows Server 2012, Windows Vista, WindowsXP
Packaging Type	Carton
Processor	ColdFIRE 5272
Slot	Universal PCI 3.3V/5V
Temperature Range - Operating	0°C to +60°C
<b>Electrical</b>	
EMC	EN 61000-3-2, EN 61000-3-3, IEC 61000-6-2
Supply Voltage	3.3/5V
<b>Material Info</b>	
Engineering Number	SST-PB3-PCU



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[112011 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112011-0021](#)