

SA-9-115 - Fume Absorber, 115V - Data Sheet

Smoke Absorber / Fume Absorber - SA-9-115. This SA Series Smoke Absorber features an Aerodynamic hood design which effectively draws irritating soldering fumes away from the work area. Carbon-impregnated filters trap a limited portion of the flux fumes Compact size, low profile and adjustable stand allows convenient placement 6" to 8" (152 to 203mm) from work area.

Specifications

- Input Voltage: 115v / 60Hz
- Max Air Volume: 105 to 126 CFM
- Noise Level: 45-50 dB (A)
- Motor HP: 15-17 Watt
- Motor RPM: 300
- Activated Carbon Wt.: 12g



Specifications	
Activated Carbon Weight	12 grams
Includes	3 Filters
Maximum Air Volume	105 to 126 CFM
Noise Level	45-50 dB (A)
Voltage	115V (60Hz)
Features	Aerodynamic Hood. Compact Size.
Material	Plastic Housing
Dimensions	8-1/2" (H) x 8-1/4" (W) x 4" (D)
Weight	3.510 lbs
UPC No.	811490010130

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[SA-9-115](#)