



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



Dispenser filled with one roll each legend 0 thru 9.  $\triangle$

PART NUMBER	LEGEND	MATERIAL COLOR	LEGEND COLOR
$\triangle$ PMDR-0-9 thru PMDR-90-99	"0" thru "9" thru "99", * SEE NOTE 2.	WHITE	BLACK
$\triangle$ PMDR-0 thru PMDR-9	"0" thru "9", * SEE NOTE 2.	WHITE	BLACK
$\triangle$ PMDR-A thru PMDR-Z	"A" thru "Z", * SEE NOTE 2.	WHITE	BLACK
PMDR-L1	"L1"	WHITE	BLACK
PMDR-L2	"L2"	WHITE	BLACK
PMDR-L3	"L3"	WHITE	BLACK
PMDR-T1	"T1"	WHITE	BLACK
$\triangle$ PMDR-T2	"T2"	WHITE	BLACK
PMDR-T3	"T3"	WHITE	BLACK
PMDR-GRS	$\frac{1}{2}$	WHITE	BLACK
PMDR-MIN	-	WHITE	BLACK
PMDR-PLS	+	WHITE	BLACK
PMDR-BLK	No Legend	BLACK	N/A
PMDR-BL	No Legend	LIGHT BLUE	N/A
PMDR-BRN	No Legend	BROWN	N/A
PMDR-GRY	No Legend	GRAY	N/A
PMDR-GRN	No Legend	LIGHT GREEN	N/A
PMDR-ORN	No Legend	ORANGE	N/A
PMDR-PUR	No Legend	PURPLE	N/A
PMDR-RED	No Legend	RED	N/A
PMDR-WHT	No Legend	WHITE	N/A
PMDR-YEL	No Legend	YELLOW	N/A
PMDR-NEMA	No Legend, * SEE NOTE 3.	BLACK, LIGHT BLUE, BROWN, GRAY, LIGHT GREEN, ORANGE, PURPLE, RED, WHITE, YELLOW	N/A

PART NUMBER	LEGEND	MATERIAL COLOR	LEGEND COLOR
PMD	EMPTY DISPENSER	N/A	N/A
$\triangle$ PMD-0-9	DISPENSER FILLED WITH ONE ROLL EACH LEGEND 0 THRU 9.	WHITE	BLACK
PMO-NEMA	DISPENSER FILLED WITH ONE ROLL EACH OF SOLID NEMA COLORS: BLACK, LIGHT BLUE, BROWN, GRAY, LIGHT GREEN, ORANGE, PURPLE, RED, WHITE AND YELLOW.	BLACK, LIGHT BLUE, BROWN, GRAY, GREEN, ORANGE, PURPLE, RED, WHITE, YELLOW	N/A



PMO - \*



PMO EMPTY DISPENSER



PMO - \* - \*

- NOTES:
1. MILLIMETER ARE IN [ ].
  2. ONE ROLL EACH CHARACTER.
  3. ONE ROLL EACH COLOR.

CAD FILENAME/LAYERS 100619GN\_DC\_C10670/06E

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
PMD, PMO DISPENSER TAPES

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	7/20/12	LEF	VJS	3: REMOVE PART PMO-CYS	C10670	3	RAMI	
2	10/27/09	RVU		"6" AND "9" CHARACTERS TO BE UNDERLINED. UPDATE ON TOL.	5895	2		
1	6/4/09	RVU		UPDATE 2 TABLE. ADD NOTE 2, 3.	5769	1		
0	8/29/08	RVU		DRAWING RELEASED	5366	R		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
(.X) ± .12 (.XXX) ± .025  
(.XX) ± .062 ANGLES ±  $\triangle$

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU

MAT'L:

SCALE NTS

DATE 3/24/08

PMO MARKER

DRAWING NO.

C10670

DWG

A

CHK'D

SIZE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PMDR-6](#) [PMDR-7](#) [PMDR-2](#) [PMDR-3](#) [PMDR-1](#) [PMDR-8](#) [PMDR-4](#) [PMDR-5](#) [PMDR-B](#) [PMDR-C](#) [PMDR-D](#) [PMDR-E](#) [PMDR-F](#) [PMDR-G](#) [PMDR-H](#) [PMDR-I](#) [PMDR-J](#) [PMDR-K](#) [PMDR-N](#) [PMDR-P](#) [PMDR-Q](#) [PMDR-R](#) [PMDR-S](#) [PMDR-T](#) [PMDR-U](#) [PMDR-V](#) [PMDR-W](#) [PMDR-X](#) [PMDR-Y](#) [PMDR-10-19](#) [PMDR-L](#) [PMDR-60-69](#) [PMDR-20-29](#) [PMDR-30-39](#) [PMDR-50-59](#) [PMDR-T3](#) [PMDR-L3](#) [PMDR-L1](#) [PMDR-M](#) [PMDR-70-79](#) [PMDR-T1](#) [PMDR-O](#) [PMDR-80-89](#) [PMDR-L2](#) [PMDR-40-49](#) [PMDR-T2](#) [PMDR-90-99](#)