


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm <sup>2</sup> ]	TAB SIZE in [mm]	HOUSING COLOR	DIMENSIONS in. [mm]					WIRE STRIP LENGTH in [mm] +1/32 [0,8] -0	TOOLS
				L ± .04 [1,1]	W ± .01 [0,3]	C ± .02 [0,4]	M ± .02 [0,6]	MAX. WIRE INSUL. DIA.		
EDV18-250FIB	#22-16 [0.5-1.5]	.250 X .032 [6.4 X 0.8]	RED	.87 [22.0]	.26 [6.6]	.30 [7.5]	.39 [10.0]	.145 [3.7]	9/32 [6.8]	KST2000C
EDV14-250FIB	#16-14 [1.5-2.5]		BLUE	.87 [22.0]	.26 [6.6]	.30 [7.5]	.39 [10.0]	.165 [4.2]	9/32 [6.8]	
EDV10-250FIB	#12-10 [4.0-6.0]		YELLOW	.96 [24.3]	.26 [6.6]	.29 [7.3]	.49 [12.5]	.204 [5.2]	11/32 [8.8]	

NOTES:

- UL LISTED FOR:
  - A. STRANDED COPPER WIRE ONLY - INTERNAL WIRING
  - B. 300V MAX VOLTAGE RATING
  - C. 167°F [75°C] MAX TEMP RATING
- MATERIAL:
  - A. STAMPING: .016" [0.4] THICK BRASS, TIN PLATED
  - B. HOUSING: VINYL
- SEE [www.panduit.com](http://www.panduit.com) FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED  
19X5  
E78522

TITLE <b>STRONGHOLD FEMALE DISCONNECTS (250 SERIES) VINYL FULLY INSULATED #22-10 AWG</b>		CUSTOMER DRAWING	
ITEM REVISION NAME 00123SSE/00		<b>PANDUIT</b> <sup>TM</sup>	
DATASET FILE NAME 00123SSE_DC/00			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54]      .xxx ± .005 [0.127] .xx ± .01 [0.25]      ANGLES ± 5°		MATERIAL: <b>SEE NOTES</b>	
DRAWN BY JHNU		DRAWING NUMBER: 00123SSE - DC	
DATE 2/18	CHK -	SCALE N.T.S.	SHEET 1 OF 1
THIRD ANGLE PROJECTION		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	2/18	JHNU	TMR	RGB	DRAWING RELEASED	00123SS

D10100DA/12

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[EDV14-250FIB-Q](#) [EDV18-250FIB-Q](#)