

description

Our wide assortment of heavy-duty locking and standard power cords are a best in class offer; designed for transferring power from the rack power distribution unit (PDU) to active gear in a data center cabinet or rack. They are available in a variety of colors & lengths. The W-Lock & V-Lock compatible locking cords eliminate accidental disconnects caused by vibration and/or contact. In addition, they feature locking on both ends, G5 PDU side & IT Gear side; for a secure connection.



technical information

Panduit power cords are manufactured to comply with regulatory approvals that are commonly accepted in the US, Europe, and other parts of the world. Various plug configurations and lengths, optimize connection from rack PDUs to common network equipment.

key features and benefits

W-Lock & V-Lock Compatible	Eliminates disconnects caused by vibration and/or accidental contact
Dual-Ended Locking	Cord locks on both ends, G5 PDUs & IT Gear side. G5 PDU side is also V-Lock Compatible
Universal Female Locking Connector	Compatible with all standard IT gear input plugs
Selection of lengths	Allows user to optimize cable management to reduce slack and improve thermal performance
Non-conforming packaging	Prevents cord deformity from bound packaging methods
Selection of colors	Cords available in Red, Blue, Black, Yellow* & Gray*
Selection of configurations	Variety of configurations are available to meet multiple application environments

*Minimum order quantity may apply for non-standard colors or lengths

applications

Panduit power cords are available in a variety of optimal lengths and colors. Optimal lengths prevent slack loops, and clutter; thereby saving energy and allowing increased airflow. Utilize different colors to signify power paths within your data center.

SmartZone™ G5 Locking and Standard IT Power Cords

specifications locking cords

	IEC C14 to IEC C13	IEC C20 to IEC C19
Voltage	250 Volts	
Amperage	10 Amps	16 Amps
Male Plug	IEC60320 C14	IEC60320 C20
Locking Style	W-Lock & V-Lock Compatible	
Female Connector	IEC60320 C13	IEC60320 C19
Locking Style	Universal	
Gauge	17AWG / 1.0mm ²	15AWG / 1.5mm ²
Conductors	3 Wire	
Conductor Color Code	Blue, Brown, Green/Yellow Stripe (ICC)	
Jacket	SJT/H05VV-F	
Jacket Material	PVC	
Jacket Temp. Rating	105° C	
~ Outside Diameter	7.95 - 8.25 mm	9.25 - 9.45 mm
Packaging	1 pc or 10 pk	
Testing	Each cord is tested for dielectric voltage-withstand (Hi-Pot), polarization and continuity.	
Certifications	UL, CE, VDE, TUV Approved	





specifications non locking cords

	IEC C14 to IEC C13	IEC C20 to IEC C19
Voltage	250 Volts	
Amperage	10 Amps	16 Amps
Male Plug	IEC60320 C14	IEC60320 C20
Female Connector	IEC60320 C13	IEC60320 C19
Gauge	18AWG / 0.75mm ² (H05VV-F) / 1.0mm ² (HVCTF) for 2-6 feet 17AWG / 1.0mm ² (H05VV-F) / 1.2mm ² (HVCTF) for 10 feet	15AWG / 1.5mm ² (H05VV-F) / 2.0mm ² (HVCTF)
Conductors	3 wire	
Conductor Color Code	Blue, Brown, Green/Yellow Stripe (ICC)	
Jacket	SJT (N. America) / H05VV-F with RVV (China) / H05VV-F (All except China) / HVCTF (Japan and Taiwan)	
Jacket Material	PVC	
Jacket Temp. Rating	105° C	
~ Outside Diameter	8.3 - 8.5 mm	9.25 - 9.45 mm
Packaging	1 pc or 10 pk	
Testing	Each cord is tested for dielectric voltage-withstand (Hi-Pot), polarization and continuity.	
Certifications	cULus (N.America), VDE (Europe), PSE (Japan), CCC (China), KC (S. Korea), SAA (Australia / New Zealand), CE Approved (Europe)	

SmartZone™ G5 Locking and Standard IT Power Cords

W-Lock and V-Lock Compatible Locking Power Cords (UL, CE, VDE, TUV Approved)





Color	Description	Ratings	Gauge / Cross section area	Jacket	Angle	Length (feet)	Panduit Part Number (1 pc.)	Panduit Part Number (10 pk.)
Red	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	2	LPCA01	LPCA01X
Red	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	3	LPCA02	LPCA02X
Red	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	4	LPCA03	LPCA03X
Red	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	6	LPCA04	LPCA04X
Red	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	LPCA05*	LPCA05X*
Blue	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	2	LPCA06	LPCA06X
Blue	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	3	LPCA07	LPCA07X
Blue	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	4	LPCA08	LPCA08X
Blue	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	6	LPCA09	LPCA09X
Blue	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	LPCA10*	LPCA10X*
Black	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	2	LPCA11	LPCA11X
Black	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	3	LPCA12	LPCA12X
Black	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	4	LPCA13	LPCA13X
Black	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	6	LPCA14	LPCA14X
Black	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	LPCA15*	LPCA15X*
Yellow	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	2	LPCA16*	LPCA16X*
Yellow	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	3	LPCA17*	LPCA17X*
Yellow	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	4	LPCA18*	LPCA18X*
Yellow	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	6	LPCA19*	LPCA19X*
Yellow	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	LPCA20*	LPCA20X*
Gray	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	2	LPCA21*	LPCA21X*
Gray	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	3	LPCA22*	LPCA22X*
Gray	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	4	LPCA23*	LPCA23X*
Gray	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	6	LPCA24*	LPCA24X*
Gray	Locking Power Cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	LPCA25*	LPCA25X*



* non-standard products (500 piece minimum, 16 week lead time)

SmartZone™ G5 Locking and Standard IT Power Cords

Color	Description	Ratings	Gauge / Cross section area	Jacket	Angle	Length (feet)	Panduit Part Number (1 pc.)	Panduit Part Number (10 pk.)
Red	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	LPCB01	LPCB01X
Red	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	LPCB02	LPCB02X
Red	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	LPCB03	LPCB03X
Red	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	LPCB04	LPCB04X
Red	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	LPCB05*	LPCB05X*
Blue	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	LPCB06	LPCB06X
Blue	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	LPCB07	LPCB07X
Blue	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	LPCB08	LPCB08X
Blue	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	LPCB09	LPCB09X
Blue	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	LPCB10*	LPCB10X*
Black	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	LPCB11	LPCB11X
Black	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	LPCB12	LPCB12X
Black	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	LPCB13	LPCB13X
Black	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	LPCB14	LPCB14X
Black	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	LPCB15*	LPCB15X*
Yellow	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	LPCB16*	LPCB16X*
Yellow	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	LPCB17*	LPCB17X*
Yellow	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	LPCB18*	LPCB18X*
Yellow	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	LPCB19*	LPCB19X*
Yellow	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	LPCB20*	LPCB20X*
Gray	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	LPCB21*	LPCB21X*
Gray	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	LPCB22*	LPCB22X*
Gray	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	LPCB23*	LPCB23X*
Gray	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	LPCB24*	LPCB24X*
Gray	Locking Power Cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	LPCB25*	LPCB25X*



* non-standard products (500 piece minimum, 16 week lead time)

SmartZone™ G5 Locking and Standard IT Power Cords

Standard Power Cords (cULus, VDE, ENEC, PSE, CCC, KC, SAA, CE Approved)

Color	Description	Ratings	Gauge / Cross section area	Jacket	Angle	Length (feet)	Panduit Part Number (1 pc.)	Panduit Part Number (10 pk.)
Red	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	2	NPCA01	NPCA01X
Red	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	3	NPCA02	NPCA02X
Red	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	4	NPCA03	NPCA03X
Red	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	6	NPCA04	NPCA04X
Red	Power cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	NPCA05†	NPCA05X†
Blue	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	2	NPCA06	NPCA06X
Blue	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	3	NPCA07	NPCA07X
Blue	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	4	NPCA08	NPCA08X
Blue	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	6	NPCA09	NPCA09X
Blue	Power cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	NPCA10†	NPCA10X†
Black	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	2	NPCA11	NPCA11X
Black	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	3	NPCA12	NPCA12X
Black	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	4	NPCA13	NPCA13X
Black	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	6	NPCA14	NPCA14X
Black	Power cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	NPCA15†	NPCA15X†
Yellow	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	2	NPCA16†	NPCA16X†
Yellow	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	3	NPCA17†	NPCA17X†
Yellow	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	4	NPCA18†	NPCA18X†
Yellow	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	6	NPCA19†	NPCA19X†
Yellow	Power cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	NPCA20†	NPCA20X†
Gray	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	2	NPCA21†	NPCA21X†
Gray	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	3	NPCA22†	NPCA22X†
Gray	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	4	NPCA23†	NPCA23X†
Gray	Power cord, IEC C14 to IEC C13	10A/250V	18AWG / 0.75mm ²	SJT/ H05VV-F	Straight	6	NPCA24†	NPCA24X†
Gray	Power cord, IEC C14 to IEC C13	10A/250V	17AWG / 1.0mm ²	SJT/ H05VV-F	Straight	10	NPCA25†	NPCA25X†



†non-standard products (200 piece minimum, 16 week lead time)

SmartZone™ G5 Locking and Standard IT Power Cords

Color	Description	Ratings	Gauge / Cross section area	Jacket	Angle	Length (feet)	Panduit Part Number (1 pc.)	Panduit Part Number (10 pk.)
Red	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	NPCB01	NPCB01X
Red	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	NPCB02	NPCB02X
Red	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	NPCB03	NPCB03X
Red	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	NPCB04	NPCB04X
Red	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	NPCB05†	NPCB05X†
Blue	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	NPCB06	NPCB06X
Blue	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	NPCB07	NPCB07X
Blue	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	NPCB08	NPCB08X
Blue	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	NPCB09	NPCB09X
Blue	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	NPCB10†	NPCB10X†
Black	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	NPCB11	NPCB11X
Black	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	NPCB12	NPCB12X
Black	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	NPCB13	NPCB13X
Black	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	NPCB14	NPCB14X
Black	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	NPCB15†	NPCB15X†
Yellow	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	NPCB16†	NPCB16X†
Yellow	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	NPCB17†	NPCB17X†
Yellow	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	NPCB18†	NPCB18X†
Yellow	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	NPCB19†	NPCB19X†
Yellow	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	NPCB20†	NPCB20X†
Gray	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	2	NPCB21†	NPCB21X†
Gray	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	3	NPCB22†	NPCB22X†
Gray	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	4	NPCB23†	NPCB23X†
Gray	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	6	NPCB24†	NPCB24X†
Gray	Power cord, IEC C20 to IEC C19	16A/250V	15AWG / 1.5mm ²	SJT/ H05VV-F	Straight	10	NPCB25†	NPCB25X†



IEC320 C20 IEC320 C19



IEC320 C20 IEC320 C19



IEC320 C20 IEC320 C19



IEC320 C20 IEC320 C19



IEC320 C20 IEC320 C19

†non-standard products (200 piece minimum, 16 week lead time)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2018 Panduit Corp.
ALL RIGHTS RESERVED.
PUSP27--WW-ENG
4/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NPCB08](#) [LPCA23](#) [LPCA05](#) [NPCB17](#) [LPCB03X](#) [LPCA22](#) [NPCB17X](#) [NPCB09](#) [LPCB12X](#) [NPCB24X](#) [NPCA08](#)
[NPCB16X](#) [LPCB21X](#) [NPCA25X](#) [LPCB20](#) [NPCA17](#) [LPCA05X](#) [NPCA07X](#) [NPCA24X](#) [NPCB14](#) [LPCA21X](#) [LPCB13](#)
[LPCA24X](#) [NPCA23](#) [LPCB06](#) [NPCB09X](#) [LPCA11X](#) [NPCB19X](#) [NPCA01X](#) [NPCA11X](#) [NPCA14X](#) [LPCB12](#)
[NPCA17X](#) [LPCA06](#) [NPCA16](#) [LPCB20X](#) [NPCB01](#) [LPCA14X](#) [NPCB12X](#) [LPCA17](#) [LPCB18X](#) [LPCB22](#) [NPCB02X](#)
[LPCA07X](#) [LPCB09](#) [LPCA16](#) [LPCB07X](#) [NPCA13](#) [LPCA04X](#) [LPCA01X](#) [LPCB04X](#) [NPCA09](#) [LPCA15X](#) [LPCA20](#)
[NPCA22X](#) [LPCA21](#) [LPCA11](#) [LPCA02X](#) [NPCA10X](#) [LPCB16](#) [LPCB17X](#) [LPCB04](#) [LPCA04](#) [LPCA25X](#) [LPCB21](#)
[NPCB15](#) [LPCB01X](#) [NPCA18X](#) [NPCA07](#) [NPCB10X](#) [LPCA14](#) [LPCB15X](#) [NPCA18](#) [NPCA06X](#) [LPCB02X](#) [NPCB20X](#)
[LPCB11](#) [NPCB23](#) [NPCB12](#) [NPCA04X](#) [LPCA17X](#) [NPCA10](#) [LPCA08X](#) [LPCB05X](#) [NPCA11](#) [LPCB19X](#) [LPCA10](#)
[LPCA19](#) [LPCA10X](#) [LPCB24X](#) [LPCA09X](#) [LPCB25X](#) [LPCA16X](#) [NPCB04X](#) [LPCB11X](#) [NPCA08X](#) [NPCB22](#)
[NPCB23X](#) [NPCA19X](#) [NPCB25](#)