


## Sealed Nickel Cadmium Batteries

Model: PS-SC


### Specifications

Nominal Voltage		1.2 Volt
Rated Capacity		1500 mAh
Dimensions	Diameter in. (mm)	0.87 (22.1)
	Height in. (mm)	1.65 (44.0)
	Height with solder tabs	1.69 (45.0)
	Weight Approx.	44 gm
	Internal Resistance	< 20 mΩ
	Standard Charge (0.1C)	150 mA
	Trickle Charge	(0.03C)~(0.05C)
	Fast Charge ΔV	1500 mA
Recommended Operating Temperature Range	Std/Trickle Charge	20±5°C
	Fast Charge	20±5°C
	Discharge	20±5°C
	Storage	-20°C to 45°C
Standard Discharge (0.2C) Cut Off Voltage		1.0V per cell
High Rate Discharge (1 C) Cut Off Voltage		1.0V per cell


### Dimensions




### Charging and Discharging Characteristics




Discharge



Standard Charge




Fast Charge




Trickle Charge



**▲ Standard Battery Cycle Life ▲**




**▲ Fast Charging Cycle Life ▲**




**▲ Cycle Life Using Trickle Charging ▲**



**▲ Stand-by Battery Life ▲**



**▲ Capacity vs. Temperature ▲**



**▲ Retained Capacity In Storage ▲**

**Corporate Headquarters and Domestic Sales**  
 Power-Sonic Corporation • 7550 Panasonic Way • San Diego, CA 92154 • U.S.A  
 Phone: (619) 661-2020 • Fax: (619) 661.3650  
 Email Sales: [national-sales@power-sonic.com](mailto:national-sales@power-sonic.com)  
 Email Customer Service: [customer-service@power-sonic.com](mailto:customer-service@power-sonic.com)  
 E-mail Technical Support: [technical-support@power-sonic.com](mailto:technical-support@power-sonic.com)

**International Sales**  
 Power-Sonic Corporation • P.O. Box 5242 • Redwood City, CA 94063 • U.S.A.  
 Phone: (650) 364-5001 • Fax: (650) 366-3662  
 Email Sales: [international-sales.com@power-sonic.com](mailto:international-sales.com@power-sonic.com)

**[www.power-sonic.com](http://www.power-sonic.com)**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Power-Sonic:](#)

[PS-SC](#) [PS-SC-T](#)