


RCA AND TS WIRING CHART							
JACKET COLOR	H.S. TUBING MARKER	END "A" RCA PLUG			END "B" TS PLUG		
		RED	BLACK	BARE	RED	BLACK	BARE
BROWN	CHANNEL 1	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
RED	CHANNEL 2	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
ORANGE	CHANNEL 3	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
YELLOW	CHANNEL 4	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
GREEN	CHANNEL 5	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
BLUE	CHANNEL 6	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
PURPLE	CHANNEL 7	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
GRAY	CHANNEL 8	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE



- NOTES:
- CABLE BREAKOUT LENGTH IS 18.00 +/- 0.75 IN.
  - CABLE IS SHIPPED COILED AND PACKAGED IN A BAG.

3. MATERIALS:
- RCA PLUG:  
 WASHER - PHENOLIC  
 CENTER PIN - COPPER ALLOY, NICKEL PLATED  
 PLUG HOUSING - COPPER ALLOY, NICKEL PLATED  
 CLAMP TERMINAL - STEEL, ELECTRO-TINNED  
 HANDLE - COPPER ALLOY  
 CABLE - COPPER, THERMOPLASTIC
- TS PLUG:  
 INSULATING WASHERS - THERMOPLASTIC  
 PLUG BODY AND TIP ROD - COPPER ALLOY, NICKEL PLATED  
 INSULATORS - MYLAR  
 TERMINALS - COPPER ALLOY, ELECTRO-TINNED  
 HANDLE - COPPER ALLOY, NICKEL PLATED

4. THIS PRODUCT IS RoHS COMPLIANT.

PART NUMBER	CABLE LENGTH "X"
RCA05TS	5.00 FT +/- 1.50 IN
RCA10TS	10.00 FT +/- 1.50 IN

**CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
DATE DRAWN		BY	CHKD	APVD			SHEET 1 OF 1		
4/14/08		JGK	RS	TJK			PART No. RCA__TS		REV B
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING				
REVISIONS					NAME: RCA PLUG TO TS PLUG, RoHS				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RCA05TS](#)