

SPECIFICATION CONTROL DRAWING

SCD

55A0822


Title TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED,
GENERAL PURPOSE, 600 VOLT

Date 12-30-16

Revision D

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A0812



CABLE CONSTRUCTION DETAILS

PART NUMBER <u>1/</u>	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
		NOMINAL	MAXIMUM	
55A0822-26-*	26	.080	.084	3.5
55A0822-24-*	24	.090	.094	4.7
55A0822-22-*	22	.100	.104	6.5
55A0822-20-*	20	.116	.120	9.6
55A0822-18-*	18	.140	.146	14.7
55A0822-16-*	16	.154	.160	18.4
55A0822-14-*	14	.188	.194	28.2
55A0822-12-*	12	.222	.228	41.8
55A0822-10-*	10	.268	.276	66.1

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms) at sea level
 DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
 INSULATION FLAWS:
 Spark Test, 5.7 kV (rms) at 3 kHz
 Impulse Dielectric Test, 8.0 kV (peak)

1/ PART NUMBER:
 The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors.
 Example: AWG 20, blue and white component wires:
 55A0822-20-6/9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable
 501 Oakside Avenue
 Redwood City, CA 94063-3800
 Phone: 1-800-522-6752
 Fax: 1-650-361-6297

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[55A0822-20-6/9CS2275](#) [55A0822-16-9/96CS2655](#) [55A0822-12-6/9CS2199](#) [55A0822-22-9/96CS2655](#) [55A0822-18-6/9CS2275](#) [55A0822-18-6/9CS2199](#) [55A0822-20-9/96CS2275](#) [55A0822-12-6/9CS2275](#) [55A0822-24-9/96CS2275](#) [55A0822-26-9/96CS2275](#) [55A0822-12-9/96CS2655](#) [55A0822-22-9/96CS2275](#) [55A0822-20-6/9](#) [55A0822-12-9/96CS2275](#) [55A0822-22-6/9CS2275](#) [55A0822-22-6/9CS2199](#) [55A0822-16-6/9CS2275](#) [55A0822-20-6/9CS2199](#) [55A0822-18-9/96CS2275](#) [55A0822-12-6/9](#) [55A0822-16-9/96CS2275](#)