






- ① MATERIALS AND FINISH
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
 3. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
 4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
 5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
 6. UL RATING: 300V, 15A.



60.48±0.20	12	1-1776141-2
55.40±0.20	11	1-1776141-1
50.32±0.20	10	1-1776141-0
45.24±0.15	9	1776141-9
40.16±0.15	8	1776141-8
35.08±0.15	7	1776141-7
30.00±0.15	6	1776141-6
24.92±0.10	5	1776141-5
19.84±0.10	4	1776141-4
14.76±0.10	3	1776141-3
9.68±0.10	2	1776141-2
A	NO OF POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 07JUN2005 CHK C. RICHARD 07JUN2005 APVD C. RICHARD 07JUN2005		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±.25 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±2 FINISH		NAME TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE, OPEN ENDS, STACKING 5.08mm PITCH	
		PRODUCT SPEC 108-20166 APPLICATION SPEC 114-20079		SIZE CAGE CODE DRAWING NO A2 00779 C-1776141	
MATERIAL  -  -		WEIGHT - CUSTOMER DRAWING		RESTRICTED TO - SCALE 3:1 SHEET OF REV 02	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776141-5](#)