



44A1121-26-6/9-9-US Product Details

[Share](#) | [Print](#) | [Email](#)


44A1121-26-6/9-9-US

TE Internal Number: 382789-000

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, ... \(PDF, English\)](#)
- [TWO CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKE... \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Cable Type](#) = Spec 44
- [Cable Style](#) = Jacketed, Round-Braid Shielded

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Dimensions:

- Conductor Outer Diameter (mm [in]) = 0.50 [0.020]
- Shield (Screen) Diameter (mm [in]) = 2.18 [0.086]

Body Features:

- Wire Size (AWG/CM) = 26 AWG
- Cable Jacket Color = White
- Conductor Type = Tin-Plated Copper
- Wire Color = Blue, White
- Nominal Outside Diameter (mm [in]) = 2.59 [0.102]
- Wire Diameter (mm [in]) = 0.86 [0.034]

Configuration Features:

- Number of Conductors = Twisted Pair

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- Temperature Range (°C) = -65 - +150
- Wire Size - Details = 26 AWG 0.15 mm², 0.00024 in², 19 x 38 AWG

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Features:

- Wire Source = United States

Other:

- Brand = Raychem

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[44A1121-26-6/9-9-US](#)