

Light Line™

led strip light



Light Line™




Light-Line™

making LEDs easy


- 18" (450mm) LED strip light complete with mounting base, screw holes & lens.
- 2 versions Cool white & Warm white
- 12 Volts
- General illumination
- Signage
- Retail lighting
- Furniture lighting
- Fluorescent replacement

**NEW
2008**



Light-Line™ specifications

**RoHS
CoMpliant**



MODEL No.	ILL 6A08A	ILL 6A08B
OUTPUT	400 LUMENS	450 LUMENS
POWER CONSUMPTION	12 WATTS	12 WATTS
CRI	80	80
INPUT VOLTAGE	12V	12V
COLOR TEMPERATURE (TYP)	3000K WARM WHITE	5600K COOL WHITE
CURRENT DRAW	1A	1A
LIFETIME	MIN 50K HOURS @70% LUMENS	MIN 50K HOURS @70% LUMENS
OPERATING CONDITIONS	45 DEG C MAX	45 DEG C MAX



CML Innovative Technologies Inc. 147 Central Ave, Hackensack, NJ 07601
 Tel: 1-201-489-8989 Fax: 1-201-489-6911 email: americas@cml-it.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[ILL 6A08B](#) [ILL 6A08A](#)