


PCI-7853 / PCI-7854

High Speed Link Master Controllers



PCI-7853



Features


- Single/Dual independent network operation
- Programmable timer interrupt
- RJ-45 phone jack for easy installation
- Software selectable transmission speed and mode
- Supports HSL-HUB3 and HSL-Repeater
- Timer interrupt
- DI data transmission interrupt

Supported Serial Devices

- Windows® 7/Vista (32-bit)/XP/2000 libraries
- Linux Driver for Redhat kernel 2.4.x
- MotionCreatorPro 2™
- HSL LinkMaster Utility
- RTX

DI Interrupt Function

- HSL system DI interrupt
- Any channel of every ID can be set interrupt



Ordering Information

- **PCI-7853**
Single HSL master controller with two separate connectors
- **PCI-7854**
Dual HSL master controller with four separate connectors

Specifications

Model Name	PCI-7853	PCI-7854
Max. Slave Index Support	63	126
Transmission Speed	3/6/12 Mbps (software control)	3/6/12 Mbps (software control)
Transmission Mode	Half/duplex mode (software control)	Half/duplex mode (software control)
Max. Distance	300 M at 12 Mbps	300 M at 12 Mbps
Connection Interface	RJ-45 x 2	RJ-45 x 4
LED Diagnostic	√	√
Storage Consumption	+5 V @ 500 MA	+5 V @ 500 MA
Operating Temperature	0°C to +70°C	0°C to +70°C
Storage Temperature	-20°C to +80°C	-20°C to +80°C
Dimensions	122 mm x 107 mm (L x W)	122 mm x 107 mm (L x W)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[PCI-7854](#) [PCI-7853](#)