



REPRESENTATIVE IMAGE

Product: [1311A](#)

Speaker Cable, 2 C #12 Str BC-OFHC, PVC Jkt, CM, DIR BUR, Flexible

Product Description

Speaker Cable, 2 Conductor 12 AWG (168 x 34) Oxygen-Free Bare Copper (High Conductivity), PE Insulation, PVC Jacket, CM, Direct Burial, Flexible

Technical Specifications

Product Overview

Suitable Applications:	Speaker Cable; Direct Burial; Indoor/Outdoor Home Theater; In-Wall Speaker; Outdoor Speaker
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	12 AWG	168x34	BC - Bare Copper (High Conductivity)

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.018 in (0.46 mm)	0.14 in (3.6 mm)	Black, Red

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.036 in (0.91 mm)	0.352 in (8.94 mm)

Overall Cable Diameter (Nominal):	0.352 in (8.94 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Velocity of Prop.	Max. Current
Conductor(s)	1.6 Ohm/1000ft	22.3 pF/ft (73.2 pF/m)	66%	30 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V (CM, CL3)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
3.5 in (89 mm)	3.5 in (89 mm)

Max. Pull Tension:	169 lbs (76.7 kg)
Bulk Cable Weight:	67 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor, Outdoor, Burial
Flammability / Reaction to Fire:	UL 1685 UL loading , IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CL3, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6000UE

Product Notes

Notes:	Jacket has ROOM 1 2 3 4 5 6 7 8 9 0 ZONE A B C D printed on it.
--------	---

History

Update and Revision:	Revision Number: 0.490 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1311A 010500	Black	Reel	500 ft	612825111610	C
1311A 0101000	Black	Reel	1,000 ft	612825111603	C
1311A 008500	Gray	Reel	500 ft	612825111597	C
1311A 0081000	Gray	Reel	1,000 ft	612825111580	C
1311A 1SL500	White 1SL	Reel	500 ft	612825111634	C
1311A 1SL1000	White 1SL	Reel	1,000 ft	612825111627	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1311A 0081000](#) [1311A 0101000](#) [1311A 1SL1000](#) [1311A 008500](#) [1311A 010500](#) [1311A 1SL500](#)