

MultiLog[®] Datalogging MultiMeter

Log and view up to 43,000 data points at capture rates as fast as 20 times per second

View stored data directly on LCD display with quick min/max and trend displays

Features:


- 10 selectable datalogging sample rates from 0.05 second (50ms) to 480 seconds (8 minutes) per sample for high speed data collection or long time studies
- 43,000 data point memory
- Optically isolated RS-232 PC interface with Windows[®] 95/98/NT/2000/ME/XP compatible software (included) allows user to collect, display, plot, save or export data or graphs
- Rugged design with protective holster and water resistant housing
- High basic DC Voltage accuracy of 0.08%
- True RMS measurements for AC Voltage and Current
- Wide AC Voltage bandwidth of 40Hz to 20kHz
- Smart auto power off is disabled if signal is present at test leads
- Temperature function with selectable °F/°C units
- Backlit 5000 count LCD display for high resolution (0.01mV, 0.1µA, 0.01½, 0.01nF, 0.001Hz)
- Hold and low resistance auto-lead zero
- 10 measurement functions including AC/DC Voltage and Current, Resistance, Temperature, Frequency, Capacitance, Diode and Continuity
- Complete system includes multimeter with built-in stand, CAT III test leads, Temperature probe (-58 to 482°F/-50 to 250°C), software, RS-232 cable, protective holster and 9V battery. (AC adaptor not available)

Applications:

- Use logged data collected in the field to generate reports
- Monitor and analyze electrical parameters over time
- Use with multimeter adaptors to perform studies on Airflow, Humidity, Light Level, Large Currents and rpm measurements

Ordering Information:

- ML720MultiLog[™] Datalogger MultiMeter
 ML720-NIST ..MultiLog[™] Datalogger MultiMeter w/ NIST Cert.
 TP872Spare bead wire Temperature Probe
 TL805Spare set of CAT. III - 1000V Test Leads
 TL807Set of Alligator Clips (2pk)
 CA899Vinyl Pouch Carrying Case
 FS880Spare Fuse



Specifications	Range Max.	Resolution	Basic Accuracy (%rdg+digits)
DC/AC Voltage	50mV, 500mV, 5V, 50V, 500V, 1000V	0.01mV	±(0.08%+2d) DC ±(0.5%+3d) AC
DC/AC Current	500µA, 5000µA, 50mA, 500mA, 5A, 10A	0.1µA	±(0.2%+4d) DC ±(0.6%+3d) AC
Resistance (½)	50, 500, 5k, 50k, 500k, 5M, 50M	0.01½	±(0.1%+2d)
Capacitance	50nF, 500nF, 5µF, 0 50µF, 500µF, 9999µF	.01nF	±(0.8%+3d)
Frequency	10Hz to 125kHz	0.001Hz	±(0.01%+2d)
Temperature	-58F to 1832°F (-50 to 1000°C)	1°	±(0.3%+3d)
Dimensions/ Wt	7.32 x 3.42 x 1.39" (186 x 87x 35.5mm) / 0.75lb (340g)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[ML720-NIST](#) [ML720](#) [ML710](#) [ML710-NIST](#)