


THROUGH-HOLE MICRO HEADER

(1.27 mm) .050" PITCH • FTSH SERIES



FTSH

Board Mates:
CLP, FLE

Cable Mates:
FFSD, FFTP

SPECIFICATIONS


Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Sn or Au over 50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C
Current Rating (FTSH/CLP):
3.4 A per pin
(2 pins powered)
Current Rating (FTSH/FLE):
2.9 A per pin
(2 pins powered)
Voltage Rating:
280 VAC/396 VDC

PROCESSING

Lead-Free Solderable:
Yes

LOCKING CLIP

For single mating cycle with the FFSD. Specify -LC after tail option. Lead Style -01 and 10 pins/row minimum. 5-9 pins/row not available in combination with keying shroud (-K).



ALSO AVAILABLE

Contact Samtec

Molded Pick & Place pads
Other platings



Notes:
Severe Environment Testing qualified; aligns with MIL-DTL-55302. Visit samtec.com/set

Some sizes, styles and options are non-standard, non-returnable.

See SFM/TFM for positive alignment feature.

FTSH	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OPTION	TAIL OPTION	OTHER OPTIONS
------	---	------------------	------------	----------------	---	--------	-------------	---------------

02 thru 50

Specify LEAD STYLE from chart

-F
= Gold flash on post, Matte Tin on tail

-L
= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

Leave blank for Right-angle

-"XXX"
= Polarized Position (Specify position of omitted pin) (Not available with -EX options)

Leave blank for straight tail

-RA
= Right-angle


-ES
= End Shroud (Style -02 & -03) 9 pins/row minimum

-EP
= End Shroud with Guide Post (Style -02 & -03) 9 pins/row minimum



-EL
= End Shroud with Board Lock (Style -02 & -03) 9 pins/row minimum

-EJ
= Ejector Shroud (Style -01 only) 10 pins/row minimum 25 pins/row maximum -RA not available

-K
= Keying Shroud for mating with FFSD (Style -01 only, 05 thru 25 pins/row only. 13, 17, 20 & 25 only with -EJ option)




-EX OPTION SHOWN



OPTION	Z
-ES	(1.55) .061
-EJ	(15.77) .621
-EP	(5.87) .231
-EL	((6.53) .257

LEAD STYLE	A	MATES WITH
-01	(3.05) .120	FFSD
-02	(1.91) .075	FLE
-03	(1.65) .065	CLP-D
-04	(3.81) .150	N/A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FTSH-113-01-F-D-K](#) [FTSH-110-01-L-D-K](#) [FTSH-113-01-L-D-K](#) [FTSH-105-01-L-D-K](#) [FTSH-120-04-L-D-RA](#) [FTSH-105-01-L-D](#) [FTSH-105-01-F-D-K](#) [FTSH-105-01-L-D-RA-K](#) [FTSH-130-01-L-D](#) [FTSH-125-04-L-D-RA](#) [FTSH-105-01-F-D](#) [FTSH-106-01-L-D](#) [FTSH-110-01-L-D-EJ](#) [FTSH-113-04-L-D-RA](#) [FTSH-120-03-F-D](#) [FTSH-110-02-L-D-RA](#) [FTSH-111-01-L-D](#) [FTSH-118-01-F-D](#) [FTSH-118-02-F-D-RA](#) [FTSH-118-04-L-D](#) [FTSH-104-01-S-D](#) [FTSH-104-03-F-D](#) [FTSH-106-01-L-D-RA](#) [FTSH-113-01-F-D-RA](#) [FTSH-123-01-L-D](#) [FTSH-139-01-L-D-RA](#) [FTSH-106-01-F-D-K](#) [FTSH-120-01-F-D-K](#) [FTSH-114-01-F-D](#) [FTSH-114-02-F-D](#) [FTSH-104-02-F-D](#) [FTSH-110-01-F-D-RA-K](#) [FTSH-106-02-F-D](#) [FTSH-110-01-F-D-K](#) [FTSH-128-02-L-D](#) [FTSH-106-02-F-D-RA](#) [FTSH-108-01-L-D](#) [FTSH-110-01-L-D-RA](#) [FTSH-112-01-L-D-RA](#) [FTSH-125-01-F-D](#) [FTSH-117-01-L-D](#) [FTSH-116-01-L-D](#) [FTSH-107-01-L-D](#) [FTSH-108-04-F-D](#) [FTSH-113-01-L-D](#) [FTSH-113-01-L-D-EJ-K](#) [FTSH-125-01-F-D-K](#) [FTSH-103-01-F-D](#) [FTSH-105-04-LM-D](#) [FTSH-113-01-F-D](#) [FTSH-113-01-L-D-RA](#) [FTSH-125-01-F-D-RA](#) [FTSH-128-02-F-D-RA](#) [FTSH-117-01-L-D-RA](#) [FTSH-145-02-F-D-RA](#) [FTSH-104-01-L-D-RA](#) [FTSH-102-01-F-D](#) [FTSH-109-01-F-D-RA](#) [FTSH-103-03-F-D](#) [FTSH-110-04-L-D-RA](#) [FTSH-106-04-L-D-RA](#) [FTSH-115-01-L-D-RA](#) [FTSH-115-04-L-D](#) [FTSH-120-01-L-D-EJ-K](#) [FTSH-118-01-L-D-RA](#) [FTSH-120-01-L-D-RA](#) [FTSH-124-04-L-D](#) [FTSH-120-02-L-D](#) [FTSH-102-02-F-D](#) [FTSH-102-04-L-D-RA](#) [FTSH-105-02-L-D-RA](#) [FTSH-110-01-F-D-RA](#) [FTSH-115-01-L-D](#) [FTSH-135-04-L-D-RA](#) [FTSH-103-02-L-D](#) [FTSH-110-01-F-D-007-K](#) [FTSH-109-04-L-D-RA](#) [FTSH-108-01-L-D-K](#) [FTSH-122-02-F-D-RA](#) [FTSH-105-04-F-D](#) [FTSH-107-02-L-D](#) [FTSH-105-01-L-D-RA](#) [FTSH-107-01-L-D-K](#) [FTSH-106-04-L-D](#) [FTSH-110-04-L-D](#) [FTSH-111-01-L-D-RA](#) [FTSH-105-04-F-D-RA](#) [FTSH-118-02-F-D](#) [FTSH-105-01-F-D-007-K](#) [FTSH-125-04-L-D](#) [FTSH-113-01-LM-D-K](#) [FTSH-120-04-L-D](#) [FTSH-124-01-F-D-RA](#) [FTSH-117-04-L-D](#) [FTSH-105-01-FM-D](#) [FTSH-103-04-F-D-RA](#) [FTSH-102-01-L-D](#) [FTSH-103-04-L-D-RA](#) [FTSH-104-01-F-D](#) [FTSH-109-02-F-D](#)