

AX60530

6-slot ShoeBox Chassis

Features

- Compact design for embedded applications
- Supports half-size SBCs
- Exposed one slim CD-ROM & one 3.5" HDD drive bay; internal one 3.5" HDD drive bay
- Equipped with ATX 250W or 300W power supplyn
- Easy-removable cooling fan



Specifications

Standard Color	Beige (PANTONE 414C)
Construction	Heavy-duty steel
Drive Capacity	Exposed 1 x slim CD-ROM and 1 x 3.5" HDD drive bay, internal 1 x 3.5" HDD drive bay
Cooling	1 x 8 cm ball-bearing fan (38.6 CFM/each) with a removable filter
Front Panel Indicators	1 x power, 1 x HDD Front
Panel Controls	1 x system reset; 1 x power on/off
Front Panel Connectors	2 x USB & 1 x PS/2
Pre-punched Panel	2 x 9-pin & 1 x 25-pin
System Board	Half-size SBCs
Expansion Interface	6-slot ISA or PCI backplane
Hold-down Clamp	Rubber cushion
Operating Temperature	0°C to +40°C (+32°F to +113°F)
Dimensions	191 mm (7.5") (W) x 273 mm (10.8") (D) x 195.7 mm (7.7") (H)
Weight (net/gross)	5.4 kg (11.9 lb)/6.8 kg (15 lb)

Ordering Information

AX60530WB/X250P	With ATX 250W power supply
AX60530WB/X300P	With ATX 300W power supply


*Specifications and certifications are based on options and may vary.

Backplane Options

PICMG 1.3

Models	Slots per Segment (ISA/PCI/PCIe/CPU)	Segment
HAB206	0/3/1/1	Single

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[AX60530WB-RC-NP w/o BP,PS](#)