


CAPA313

3.5" Embedded SBC with Intel® Pentium® Processor N4200 & Celeron® Processor N3350, LVDS, HDMI, 2 GbE LAN and Audio

Features

- Intel® Pentium® processor N4200/Celeron® processor N3350
- 1 DDR3L SO-DIMM for up to 8GB of memory
- 2 USB 2.0 and 4 USB 3.0
- 1 PCI Express Mini Card slot
- ZIO connector





Core System

CPU	Intel® Pentium® processor N4200/Celeron® processor N3350 onboard
System Memory	1 x 204-pin DDR3L-1867 SO-DIMM, up to 8GB
Chipset	SoC integrated
BIOS	AMI
SSD	1 x mSATA
Watchdog Timer	65536 levels, 1 to 65535 sec.
Expansion Interface	1 x Full-size PCI Express Mini Card slot 1 x USB, 1 x PCIe x1, 1 x LPC, 1 x SMBus through a ZIO connector
Battery Lithium	Lithium 3V/220mAH
Power Input	2 x 2-pin connector +12V to 24V DC-in AT Auto Power On function supported
Power Requirements	Intel® Pentium® N4200 @1.1 GHz 8GB DDR3L Max. RMS: +24V @ 0.8A Intel® Celeron® N3350 @1.1 GHz 8GB DDR3L Max. RMS: +24V @ 0.7A
Dimensions	146 x 104 mm
Board Thickness	1.6 mm
Operating Temperature	-20°C to +70°C (-4°F to +158°F)
Humidity	10% to 95% relative humidity, non-condensing

I/O

SATA	1 x SATA-600
Hardware Monitoring	Detect CPU/system temperature and voltage
Ethernet	2 x 10/100/1000 Mbps Ethernet with Intel® I210-AT; support Wake-on-LAN, PXE Boot ROM
Audio	HD Codec audio as Mic-in/Line-in/Line-out with Realtek ALC888S
USB	2 x USB 2.0 4 x USB 3.0
Serial	2 x RS-232/422/485
TPM	ST ST33HPTH2X32AHD8 with TPM 2.0 compliant (optional)
SMBus	Yes
Others	1 x I ² C
Digital I/O	8-channel in/out programmable



Display

Chipset	Intel® integrated Gfx graphic engine
Memory Size	Share system memory
Display Interface	1 x HDMI 1 x LVDS; 18/24-bit single/dual channel 1 x VGA (optional)

Ordering Information

Standard	
CAPA313HGGA-N4200-ZIO (P/N: E38E313100)	3.5" embedded SBC with Intel® Pentium® processor N4200 (1.1 to 2.5 GHz, 2MB Cache, 6W), HDMI/LVDS, 2 GbE LAN, audio, ZIO, and heatsink
CAPA313HGGA-N3350-ZIO (P/N: E38E313102)	3.5" embedded SBC with Intel® Celeron® processor N3350 (1.1 to 2.4 GHz, 2MB Cache, 6W), HDMI/LVDS, 2 GbE LAN, audio, ZIO, and heatsink

Optional	
AX93262 (P/N: E393262100)	ZIO module for 2 RS-232/422/485, 2 RS-232, 1 PCI Express Mini Card slot
AX93285 (P/N: E393285100)	ZIO module for 2 RS-232, 32-bit programmable DIO
AX93291 (P/N: E393291100)	ZIO module for 2 RS-232, 2 GbE LAN
AX93295 (P/N: E393295100)	ZIO module for 2 isolated RS-232, 2 USB 3.0
59380880250E	COM port cable DB9-9 x 1-pin, P=1.25 mm, L=250 mm
594E8422800E	2 x USB 2.0 cable with bracket, L= 180 mm
E393A19100	AX93A19, SIM card slot board
59312260020E	Audio cable with bracket, P=1.25 mm, L=450 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[CAPA313HGGA-N3350-ZIO](#) [CAPA313HGGA-N4200-ZIO](#)