



CAPA841

3.5" Embedded SBC with Intel® Atom® Processor E3845/E3827, LVDS/VGA/HDMI, Dual LANs and Audio

Features

- Intel® Atom® processor E3845/E3827 (Bay Trail SoC)
- 1 DDR3L-1066/1333 SO-DIMM, up to 8GB
- 4 USB 2.0 ports
- 4 COM ports
- 2 PCI Express Mini Card and 1 SIM slot
- 2 Gigabit Ethernet ports
- LVDS/VGA/HDMI with dual-view supported




Core System

CPU	Intel® Atom® processor E3845 quad core or E3827 dual core onboard (Bay Trail)
System Memory	1 x 204-pin DDR3L-1066/1333 SO-DIMM, up to 8GB
Chipset	SoC Integrated
BIOS	AMI
SSD	1 x CFast™
Watchdog Timer	255 levels, 1 to 255 sec.
Expansion Interface	1 x Full-size PCI Express Mini Card with mSATA 1 x Half-size PCI Express Mini Card 1 x SIM slot
Battery Lithium	Lithium 3V/220mAH
Power Input	2 x 2-pin connector +12V DC-in only AT Auto Power On function supported
Power Requirements	Intel® Atom® E3845 @ 1.91 GHz, 8GB DDR3L Max. RMS: +12V @ 1.22A Intel® Atom® E3827 @ 1.75 GHz, 8GB DDR3L Max. RMS: +12V @ 0.96A
Size	146 x 104 mm
Board Thickness	1.6 mm
Temperature	-40°C to +80°C (-40°F to +176°F), operation
Relative Humidity	10% - 95% relative humidity, non-condensing

I/O

MIO	2 x RS-232/422/485 (+5V/+12V powered) 2 x RS-232 (5V/+12V powered)
SATA	1 x SATA-300
Hardware Monitoring	Detect CPU/system temperature and voltage
Ethernet	2 x 10/100/1000 Mbps supports Wake-on-LAN, PXE Boot ROM with Intel® i210IT
Audio	HD Codec audio as MIC-in/Line-in/Line-out/Speaker out with Realtek ALC888S
USB	4 x USB 2.0
SMBus	System Management Bus for advanced monitoring/control
Digital I/O	8 channels in/out programmed
TPM	ST ST33ZP24AR28PVSP with TPM 1.2 compliant or Infineon SLB9665 with TPM2.0 compliant (optional)



Display

Chipset	Intel® HD Graphics
Memory Size	Share System Memory
Display Interface	1 x VGA 1 x LVDS; 18/24-bit single/dual channel 1 x HDMI

Packing List

Standard		
Quick installation guide, and cable		
Cable		
Part Number	Description	Qty
59382620000E	1 x COM w/ bracket, P=2.0 mm, L=300 mm	1
59384500100E	Audio cable w/ bracket, P=2.0 mm, L=450 mm	1
594E8422800E	2 x USB 2.0 wafer cable w/ bracket, 180 mm	1

Ordering Information

Standard	
CAPA841VHGGGA-E3845 w/ET (P/N: E38E841109)	3.5" Embedded SBC with Intel® Atom® E3845 (1.91 GHz, 2 MB Cache, 10 W), HDMI, VGA, LVDS, 2 GbE LAN, audio and heatsink
CAPA841VHGGGA-E3827 w/ET (P/N: E38E841110)	3.5" Embedded SBC with Intel® Atom® E3827 (1.75 GHz, 1 MB Cache, 8 W), VGA/LVDS/HDMI, 2 GbE LAN, audio and heatsink
Optional	
CAPA841VHGGGA-E3845 w/heatspreader (P/N: E38E841127)	3.5" Embedded SBC with Intel® Atom® E3845 (1.91 GHz, 2MB Cache, 10W), HDMI, VGA, LVDS, 2 GbE LAN, audio and heatspreader without heatsink

Embedded SBCs >3.5" Capa 0
1
2
3
4
5
6
7



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[CAPA841VHGGGA-E3815](#)