


# CEB94701 NEW

## COM Express Type 7 Development Baseboard

### Features

- Two 10GBASE-KR SFP+ ports
- 2 SATA-600
- VGA
- 4 USB 3.0
- 2 PCI Express Mini Card slots
- 2 RS-232/422/485



### Core System

CPU	On the module
System Memory	On the module
Chipset	SoC integrated
BIOS	On the module
SSD	N/A
Watchdog Timer	On the module
Expansion Interface	2 x Full-size PCI Express Mini Card slot (one for optional) 1 x PCIe x16 1 x PCIe x8 1 x PCIe x4 1 x PCIe x1
Battery Lithium	Lithium 3V/220 mAh
Power Input	1 x 24-pin ATX connector 1 x 4-pin 12V connector (for module power supply)
Dimensions	244 x 305 mm
Board Thickness	1.6 mm
Operating Temperature	-20°C to +70°C (-4°F to +158°F)
Humidity	10% to 95% relative humidity, non-condensing

### I/O

SATA	2 x SATA-600
Hardware Monitoring	Yes
Ethernet	1 x 10/100/1000 Mbps Ethernet 2 x 10GBASE-KR (SFP+)
Audio	Buzzer
USB	4 x USB 3.0/2.0
Serial	2 x RS-232/422/485 2 x TX/RX
TPM	On module
SMBus	Yes
Others	1 x iC
GPIO	4-CH in & 4-CH out
Display	1 x VGA

### Packing List

Quick installation guide; user's manual/utility CD

### Ordering Information

Standard	
CEB94701 (P/N: E394701100)	COM Express Type 7 development board with two 10GBASE-KR Ethernet ports
Compliant Modules	
CEM700-D1577	COM Express Type 7 basic module with Intel® Xeon® D-1577, 10GBASE-KR, USB 3.0 and TPM
CEM700-D1539	COM Express Type 7 basic module with Intel® Xeon® D-1539, 10GBASE-KR, USB 3.0 and TPM
CEM700-D1548	COM Express Type 7 basic module with Intel® Xeon® D-1548, 10GBASE-KR, USB 3.0 and TPM
CEM700-D1527	COM Express Type 7 basic module with Intel® Xeon® D-1527, 10GBASE-KR, USB 3.0 and TPM
CEM700-D1519	COM Express Type 7 basic module with Intel® Pentium® D-1519, 10GBASE-KR, USB 3.0 and TPM
CEM700-D1508	COM Express Type 7 basic module with Intel® Xeon® D-1508, 10GBASE-KR, USB 3.0 and TPM



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[CEB94701](#)