


DSP501-527

Digital Signage Player with 8th Gen Intel® Core™ i5/i3 & Celeron® Processor, DisplayPort++, HDMI, 5 USB and GbE LAN



Features

- 8th gen Intel® Core™ i5/i3 & Celeron® processor
- 2 DDR4-2400 SO-DIMM for up to 32GB of memory
- 1 DisplayPort++ and 1 HDMI 2.0 ports
- 5 USB and 1 GbE LAN ports
- 1 M.2 Key E 2230 for Wi-Fi/BT
- 1 M.2 Key B 3042 slot for 4G LTE



Specifications

CPU	8th gen Intel® Core™ i5-8365UE, i3-8145UE & Celeron® 4305UE processor
System Memory	2 x DDR4-2400 SO-DIMM, up to 32GB
Chipset	N/A
Storage	1x M.2 Key M 2280 (SATA & NVMe)
TPM	TPM 2.0 (optional)
Watchdog Timer	255 levels, 1 to 255 sec./min.
System I/O Outlet	4 x USB 3.0 1 x USB 2.0 1 x GbE LAN 1 x HDMI 2.0 1 x DisplayPort++ 1 x RS-232 1 x Mic-in 1 x Line-out 1 x DC power input (lockable) 1 x SIM card 1 x HDD LED 1 x Power button 1 x Reset switch 4 x Antenna opening
Expansion Interface	1 x M.2 Key E 2230 slot for Wi-Fi/BT 1 x M.2 Key B 3042 slot for 4G LTE 1 x SIM card slot
Battery Lithium	Lithium 3 V/220 mAh
Power Input	+12V DC-in
Dimensions	200mm (7.8") (W) x 160mm (6.2") (D) x 26 mm (1.0") (H)
Weight (net/gross)	1.3kg (2.86 lb)/2.3kg (5.07 lb)
Vibration Endurance	3 Grms with M.2 storage (5 - 500Hz, X, Y, Z directions)
Operating Temperature	0°C to +50°C (+32°F to +122°F), disabling CPU Turbo boost
Humidity	10% - 90% relative humidity, non-condensing
Certifications	CE, FCC class A
EOS Support	Win 10 IoT, Win 10 Pro, Linux
Software Support	AMS.AXView



Packing List

- 1 x Quick installation guide
- 1 x Adapter 12V 60W
- 1 x Wall mount kit
- 4 x Foot pad

Ordering Information


Standard

DSP501-527	Digital signage player with 8th gen Intel® Core™ i3/i5 & Celeron® processor, DisplayPort++, HDMI, GbE LAN and 5 USB
------------	---

Optional

DDR4 SO-DIMM	4GB - 32GB
Wireless LAN Kit	Wi-Fi module and antenna
Storage	M.2 Key M 2280 (SATA & NVMe)

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[DSP501-527-4305UE](#) [DSP501-527-I3-8145UE](#) [DSP501-527-I5-8365UE](#)